

## **SAIL-VSA-10V(0.5)**

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com





Weidmüller can supply valve plugs as connecting lines with M12 plugs and one end without connector. The status of the valve plug is shown by an LED. Every valve plug is fitted with a protective circuit. The Weidmüller range includes valve plugs of type A, B and C to DIN and industry standards. In the plugged condition they achieve IP 67 class of protection. The outlet direction is also a decisive factor: Weidmüller can also supply 0° versions for type B and BD, i.e. the cable outlet direction is located at the PE contact.

#### General ordering data

Version	Valve plug with integral seal, One end without connector - valve plug, A
Order No.	<u>1845131000</u>
Туре	SAIL-VSA-10V(0.5)
GTIN (EAN)	4032248358243
Oty.	1 pc(s).



# **SAIL-VSA-10V(0.5)**

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# **Technical data**

_			
I)ım	ancione	and w	DIMBTE
	ensions	alla vv	cignita

Net weight	419 a

## **Technical specifications for cable**

Cable length	10 m	Core cross-section	0.5 mm <sup>2</sup>
Halogen	No	Number of poles	3
Outside diameter	5 mm ± 0.2 mm	Sheath material	PVC
Sheathing colour	black	Shie <b>l</b> ded	No
Suitable for cable carriers	Yes	Temperature range, moving	-2580 °C
Temperature range, stationary	-5080 °C		

#### General technical data

All valve plugs are fitted with	protective	Coding	
circuits	Suppressor diode	· ·	Design A (18 mm)
Connection thread	Miscellaneous	Contact surface	tinned
LED	Yes	Protection degree	IP67, when screwed in
Rated current	4 A	Rated voltage	24 V
Temperature range of housing	g	Version	One end without
	-25+80 °C		connector - valve plug

#### **Classifications**

ETIM 6.0	EC001855	ETIM 7.0	EC001855
ETIM 8.0	EC001855	ECLASS 9.0	27-06-03-12
ECLASS 9.1	27-06-03-11	ECLASS 10.0	27-06-03-12
ECLASS 11.0	27-06-03-12	ECLASS 12.0	27-06-03-12

#### **Approvals**

Approvals



ROHS	Conform

## **Downloads**

Catalogues	Catalogues in PDF-format	
Brochures	<u>FL FIELDWIRING EN</u>	



# **SAIL-VSA-10V(0.5)**


Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany


www.weidmueller.com

# **Drawings**

## **Dimensioned drawing**



#### Pole scheme



## Wiring diagram

