

P500 Passive Probe Customizable Interconnect Solution

INTRODUCTION

The P500 Passive Probe family is a part of Carlisle Interconnect Technologies' (CarlisleIT) full lineup of customizable interconnect solutions that is a standard, commercial off-the-shelf system engineered to deliver consistent, repeatable and dependable results. It is designed to provide a superior quality "look and feel" for customers who want a cost effective solution with the highest quality, and is fully customizable for color, shape, logos, markings, and attenuation. Accessories can also be custom-designed to your application.

Feature	Customer Benefit	
Miniaturized probe head	 Ideal for probing ne pitch integrated circuits and dense geometry circuit elements common on modern electronics 	
Probe coding	Automatic attenuation scaling via BNC interface when used with compatible oscilloscopes	
Third-party certified, exceeds UL61010-31, IEC61010-31	Superior product quality and safety assured by Underwriter Laboratory certification	
Customizable design	Customizable to match electrical performance and industrial design requirements for probe and probe accessories	



SUGGESTED APPLICATIONS

- » Low power device services
- » Manufacturing
- » Test research and development
- » Low to medium frequency measurement

- » Low frequency computer and telecom measurements
- » Power supplies
- » Inverter design


P500 Passive Probe Customizable Interconnect Solution


SPECIFICATIONS AND PERFORMANCE

Parameter	P500-010 (10X)
Bandwidth	DC to 500 MHz
Attenuation Ratio	10:1
Max Input Voltage (V)	*300 V CAT II
Input Resistance	10 ΜΩ
Input Capacitance (pF)	11 pF
Compensation Range	10 to 35 pF
Rise Time	<0.9 ns
Safety	Conformance to Low Voltage Directive (LVD) 73/23/EEC, amendment 93/68/EEC; IEC-61010-031:2015
Operating Temperature	0 °C to 50 °C, 80% RH
Storage Temperature	-40 °C to 70 °C
Operating Altitude	up to 2,000 m
Storage Altitude	up to 15,000 m

^{*}Max input voltage frequency dependent, see Voltage Derating Curve.

Voltage Derating Curve





ORDERING INFORMATION				
Model	Description			
P500-010	10X Probe Kit			
Kit Includes:	 » Probe » Grabber Hook » Insulating Tip Cap » BNC Adapter » Replacement Tips 	» RF Ground Spring » Adjusting Screw Driver » Alligator Ground Lead » Instruction Manual		















(1) Probe, (2) Grabber Hook, (3) BNC Adapter, (4) Alligator Ground lead, (5) RF Ground Spring, (6) Adjustment Tool, (7) Replacement Tips



See CarlisleIT's line of Test & Measurement products at: CarlisleIT.com/markets/test-measurement

+1 (800) 458.9960 TMSales@CarlisleIT.com