

RUE SAINT-HENRI 11, P.O. BOX 834 - CH-2800 DELÉMONT / SWITZERLAND

Your selected product

Jumpers - PCB Connectors

Series 999 999-11-230-10

2.54 mm, Male Jumpers


Available with or without insulator, and with 2.54, 5.08 or 7.62 mm pin spacing. For use with standard socket connectors.

Technical specs.:

| Insulator: | Black glass filled polyester PBT-GF30-FR | |
|-------------------|--|--|
| Flammability: | UL 94V-O | |
| Contact: | Brass CuZn36Pb3 (C36000) | |
| Connecting pin Ø: | 0.56 mm | |
| Mechanical life: | Min. 100 cycles | |

- Rated current: 3 A
- Contact resistance: Max. 10 m Ω

Dielectric strength: Min. 1000 V RMS



Ordering information RoHS-compliant parts

P Plating code

1 Gold 0.25 µm

Option

Jumpers without insulator with wire Ø 0.50 mm instead of 0.56 mm. Part numbers:

B = 2.54 mm 999-51-110-10

B = 5.08 mm 999-51-112-10

B = 7.62 mm 999-51-113-10

General technical specs. View CAD

Advanced information:

| Order Codes | | |
|---------------|------------|--|
| 999-11-230-10 | View Image | |

999-11-110-10


Jumpers for socket connectors, B = 2.54 mm, not insulated




Jumpers for socket connectors, B = 2.54 mm, with black insulator

999-11-210-11

Jumpers for socket connectors, B = 2.54 mm, with red insulator





Jumpers for socket connectors,

B = 5.08 mm, not insulated

999-11-220-10

Jumpers for socket connectors, B = 5.08 mm, with black insulator

999-11-220-11

Jumpers for socket connectors, B = 5.08 mm, with red insulator

999-11-113-10

Jumpers for socket connectors, B = 7.62 mm, not insulated

999-11-230-10

Jumpers for socket connectors, B = 7.62 mm with black insulator

999-11-230-11

Jumpers for socket connectors, B = 7.62 mm with red insulator

999-11-110-10

Jumpers for socket connectors,

B = 2.54 mm, not insulated

999-11-210-10

Jumpers for socket connectors, B = 2.54 mm, with black insulator

999-11-210-11

Jumpers for socket connectors, B = 2.54 mm, with red insulator

999-11-112-10

Jumpers for socket connectors, B = 5.08 mm, not insulated

999-11-220-10

Jumpers for socket connectors, B = 5.08 mm, with black insulator

999-11-220-11

Jumpers for socket connectors, B = 5.08 mm, with red insulator

999-11-113-10

Jumpers for socket connectors, B = 7.62 mm, not insulated

999-11-230-10

Jumpers for socket connectors, B = 7.62 mm with black insulator

999-11-230-11

Jumpers for socket connectors, B = 7.62 mm with red insulator