

### TKG-107-TOUCH-IP68-WHITE

InduProof® Smart Touch



#### SPECIAL FEATURES

- Silicone keyboard with 107 keys incl. num block
- Integrated capacitive touchpad
- IP68 protection, can be submerged into liquids
- Can be cleaned with soapy water, disinfectants or other cleaning agents
- Flat key profile for easy cleaning
- KeyLock function to disable the keys while cleaning the keyboard
- Ergonomic design
- Comfortable typing

#### SPECIFICATION

Number of keys: 107  
 Housing type: desktop housing  
 Housing material: silicone  
 Colour: white  
 Keyswitch technology: carbon contacts  
 Switching cycles: approx. 1 mill. (per key)  
 Operating force: 1.5 N  
 Switch travel: 1.3 mm  
 Protection level: IP68  
 Interface: USB  
 USB compatibility: compatible with USB 2.0

Cable length: 2 m  
 Operating temperature: 0 °C to +70 °C  
 Storage temperature: -30 °C to +70 °C  
 Dimensions: 377 x 157 x 15 mm  
 Weight: 913 g  
 Certifications: CE, RohS, REACH, EMV, FCC  
 Guarantee: 3 years on the electric function

#### TOUCHPAD SPECIFICATION


Operating principle: capacitive  
 Dimensions: 60 x 42 mm

#### ORDER INFORMATION

Cat.No.	Product description	Layout
KG22204	TKG-107-TOUCH-IP68-WHITE-USB-DE	German
KG22205	TKG-107-TOUCH-IP68-WHITE-USB-US/EU	US / EU
KG23204	TKG-107-TOUCH-IP68-WHITE-USB-CH	Switzerland
KG23202	TKG-107-TOUCH-IP68-WHITE-USB-SKAN	Scandinavian
KG23220	TKG-107-TOUCH-IP68-WHITE-USB-UK	UK English


Other language versions / Interfaces / configurations available on request.


Subject to modifications and errors



### SPECIAL KEYBOARD FUNCTIONS

#### Keylock / Clean Mode:

To activate or deactivate the clean mode, hold this key  down for 2 seconds. This deactivates the key function and the touchpad. You can then clean the keyboard without triggering any incorrect commands.



#### Touchpad-Tapping:

Touchpad tapping allows you to use different functions by typing the touchpad surface once or several times (e.g. in word processing: single tap to position the cursor, double tap to select paragraphs)



You can find operating instructions and hints on cleaning and disinfecting at:

[www.gett-group-service.com](http://www.gett-group-service.com)