

## **FEATURES**

- Able to be used at wide temperature from -25°C to 85°C
- Long life Endurance : 1,000 hours at +85°C
- RoHS directive compliant / No Explosion Safety

## APPLICATIONS


• Memory back-up for Video, Audio, Cameras, CCTV, Printer, Camcorder, Telephones, Car stereo, E-meter, Toy, Computer, Notebook PC, Rice cooker, Home network etc.

# **GENERAL SPECIFICATIONS / DIMENSIONS**



PART NUMBER SYSTEM									
<u>cw</u>	<u>5R5</u>	<u>105</u>	<u>C</u>	E	**				
Series	Rated Voltage	Capacitance	Туре	RoHS	Special Code				

Item	Performance					
Operating temperature	-25°C to +85°C					
Capacitance range	0.47F to 1.0F					
Capacitance tolerance	- 20% to + 80% (at 25℃)					
Rated voltage	5.5 VDC					
	Nominal capacitance (F)	0.47	0.68	1.0		
Nominal capacitance & Resistance	Nominal resistance (Ω)	50	50	30		
Towns and we also and side	Capacitance change: Within ±30% of initial measured value at +25°C					
Temperature characteristics	Internal resistance: Within ±500% of initial measured value at +25°C					
Endurance	Endurance After 1000 hours:					
(At rated voltage & max. operating	Capacitance change: ±30% of initial rated value	itial rated value				
temp) Internal resistance: Within 4 times of initial specified value						
Shelf life	After 2 years at 25°C without load, the capacitor shall meet the specified endurance limits.					



### STANDARD PRODUCTS

Part Number	Working Voltage (V DC)	Rated Cap. (F)	C type(mm)		
			ΦD	н	Р
CW5R5474CF-ZJ	5.5	0.47	21.5	10.5	5.0
CW5R5684CF-ZJ	5.5	0.68	21.5	10.5	5.0
CW5R5105CF-ZJ	5.5	1.0	21.5	10.5	5.0

#### Precautions

- Please do not apply external force to the product or the terminal due to stress such as twisting, bending, pushing, knocking down, etc., which may cause the product or terminal to fall off, resulting in an open circuit, short circuit, or liquid leakage.
- Please do not overheat the capacitor with respect to heating in an adhesive curing furnace, etc. For details, see Precautions for Using Electric Double Layer Capacitors.

No. 4, Jifeng Road, Wufeng District, Taichung City, Taiwan. TEL:+86-852-51245795 www.cda-cap.com E-MAIL: zfw@cda-cap.tw Specifications are subject to change without notice.Should a safety or technical concern arise regarding the product, please be sure to contact our sales offices or agents immediately. Spec. Date:2023-04-20



**CW Series**