

3M[™] Heat Resistive Polyimide Tape 7414

Product Description

3M[™] Heat Resistive Polyimide Tape 7414 is a single coated tape with 0.025 mm polyimide film backing and acrylic adhesive for high temperature applications.

Key Features

- Excellent abrasion resistance
- Very low coefficient of friction with self-lubricating characteristics
- Adhesive applied on back side shows strong adhesion to metals and plastics
- · Leaves virtually no silicone residue
- Little or no cleaning needed
- Dimensionally stable high temperature backing

Product Construction/Material Description

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

3M [™] Heat Resistive Polyimide Tape 7414		
Property	Value	
Color	Amber	
Backing	Polyimide film	
Adhesive	Thermally cross-linkable acrylic adhesive	

Applications

• Masking or protecting residue sensitive areas on printed circuit boards during high temperature operations such as wave soldering and solder reflow.

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

3M™ Heat Resistive Polyimide Tape 7414			
Property	Method	Value	
Adhesion to Copper	D-3330, 90° Peel	7.7 oz/in width (8.4 N/100 mm)	
Backing Thickness	D-3652	1.0 mil (0.025 mm)	
Total Tape Thickness	D-3652	1.8 mil (0.046 mm)	
Temperature Use Range*	-	2 min at 260°C	

^{*} Temperature use range is defined as the maximum time at the stated temperature after which the 3M tape 7414 may be removed cleanly, without staining, from a copper substrate.

3M™ Heat Resistive Polyimide Tape 7414

Storage and Shelf Life

The shelf life of 3M[™] Heat Resistive Polyimide Tape 7414 is 12 months from the date of manufacture when stored in the original packaging and stored under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity.

Certificate of Analysis (COA)

The 3M Certificate of Analysis (COA) for this product is established when the product is manufactured and deemed commercially available from 3M. The COA contains the 3M test methods, specifications limits and test results for the product's performance attributes that the product will be supplied against. Contact your local 3M representative for this product's COA.

3M™ Heat Resistive Polyimide Tape 7414

Regulatory: For regulatory information about this product, contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.



Electronics Materials Solutions Division 3M Center, Building 224-3N-11 St. Paul, MN 55144-1000 1-800-251-8634 phone 651-778-4244 fax www.3M.com/electronics 3M is a trademark of 3M Company. Please recycle. ©3M 2021. All rights reserved. 60-5005-0275-6

CONTACT US