


Heat Sink for NVIDIA® Jetson Orin Nano™ / Jetson Orin™ NX



ATS Part#: **ATS-NVP-3281-C2-R0**
Description: 63 x 40 x 8 mm high-performance heat sink with leaf spring attachment
Component: NVIDIA Jetson Orin Nano / Jetson Orin NX
Heat Sink Type: Straight fin heat sink
Heat Sink Attachment: Leaf spring with screws



Features & Benefits

- » Designed to fit the NVIDIA® Jetson Orin Nano™ and Jetson Orin™ NX modules
- » Leaf spring with screws for mounting heat sink - see Fig. 1
- » Included mounting hardware kit: ATS-HK510-R0
(leaf spring with M2 x 0.4mm shoulder screws - drive: Torx T8)
- » Provided with pre-assembled Thermal Interface Material (TIM) on base
- » Recommended through hole size in PCB is 3.20 mm (PCB thickness: 1.2 mm)

Image for illustration purposes only.




Fig. 1 - Leaf spring with screws for mounting heat sink

Heat Sink Part Number	L (mm)	W (mm)	H (mm)	Total Thermal Resistance (°C/W)	Heat Sink Weight (g)	Thermal Interface Material
ATS-NVP-3281-C2-R0	63	40	8	1.6	36.2	Chomerics T766

Product Details

SCHEMATIC IMAGE	Dimension A	Dimension B	Dimension C	Dimension D	Dimension E	Material	Finish
	63 mm	40 mm	8 mm	43.2 mm	28.8 mm	Aluminum 6063	Black Anodized



*All Images are for illustration purposes only.

NOTES:

- 1) Dimensions A and B refer to heat sink size.
- 2) Dimension C is the heat sink height from the bottom of the base to the top of the fin field.
- 3) Dimensions D and E refer to the mounting hole pattern C-C (center to center)
- 4) Thermal performance data are provided for reference only. Actual performance may vary by application.
- 5) ATS reserves the right to update or change its products without notice to improve the design or performance.
- 6) ATS certifies that this heat sink assembly is RoHS-6 and REACH compliant.
- 7) Contact ATS to learn about custom options available.

Heat Sinks for NVIDIA® Jetson™ Products



	NVIDIA® Product	Heat Sink Part Number	L (mm)	W (mm)	H (mm)	Weight (g)	Total Thermal Resistance
	Jetson Nano™	ATS-NVA-2780-C1-R0	60	40	8	35.5	1.6 °C/W
		ATS-NVP-2780-C2-R0	60	40	8	32.3	1.6 °C/W
	Jetson Xavier™ NX	ATS-NVA-2781-C1-R0	63	40	8	36.8	1.6 °C/W
		ATS-NVP-2781-C2-R0	63	40	8	34.2	1.6 °C/W
	Jetson AGX Xavier™	ATS-NVA-3275-C1-R0	100	87	16	164.3	0.21 °C/W
	Jetson AGX Orin™	ATS-NVP-3275-C3-R0	100	87	16	167.7	0.21 °C/W
	Jetson Orin Nano™	ATS-NVA-3281-C1-R0	63	40	8	38.3	1.6 °C/W
	Jetson Orin™ NX	ATS-NVP-3281-C2-R0	63	40	8	36.2	1.6 °C/W
	Jetson™ TX2 NX	ATS-NVA-3353-C1-R0	63	40	8	37.4	1.6 °C/W
		ATS-NVP-3353-C2-R0	63	40	8	34.3	1.6 °C/W

R6_0723