

NOTES:

- 1. MATERIALS:
 HOUSING ZINC ALLOY, SEE TABLE FOR FINISH
 RETAINING NUT BRASS, NICKEL PLATED
 3.5mm PHONE JACK:
 JACK HOUSING BRASS, NICKEL PLATED
 SPRINGS NICKEL SILVER
 INSULATORS THERMOPLASTIC
 INSERT OVERMOLD THERMOPLASTIC
- 2. SHIPPED ASSEMBLED WITHOUT PANEL MOUNTING HARDWARE. ADD "PKG" SUFFIX TO INCLUDE MOUNTING SCREWS AND INDIVIDUAL PACKAGING.
- 3. THESE PRODUCTS ARE RoHS COMPLIANT.

PART NUMBER	DESCRIPTION	E SERIES HOUSING FINISH		
EH35MMMSC	EH SERIES 3.5mm JACK, 2-CONDUCTOR MONO	NICKEL		
EH35MMMSCB	EH SERIES 3.5mm JACK, 2-CONDUCTOR MONO	BLACK CHROME		
EH35MMSSC	EH SERIES 3.5mm JACK, 3-CONDUCTOR STEREO	NICKEL		
EH35MMSSCB	EH SERIES 3.5mm JACK, 3-CONDUCTOR STEREO	BLACK CHROME		
EH35MMSNSC	EH SERIES 3.5mm JACK, 5-CONDUCTOR STEREO NORMALED	NICKEL		
EH35MMSNSCB	EH SERIES 3.5mm JACK, 5-CONDUCTOR STEREO NORMALED	BLACK CHROME		

CUSTOMER DRAWING

							THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.								
						UNLESS OTHERWISE SPECIFIED	SIZE	W	IDTH	MULT		LBS/M		TEMPE	R
						1. ALL DIMENSIONS IN INCHES	FINISH				MATERIAL				
						- TWO PLACE DECIMALS +0.02	SPEC No.	SPEC No.							
						- THREE PLACE DECIMALS ±0.005	FIRST USED ON			SCALE 1.5:1			TEMERATI®		
							DATE DRAWN	BY	CHKD	APVD					
H							10/17/05	PNK	RS	TJK					
	Α	25459	10/20/06	RS	TJK		10/1//05	FINE	6/24/09	8/27/09		SHEET	1	OF	1
	REV	ECO NUMBER	DATE	BY	APVD		NAME	E EH SERIES			PART No				REV
	REVISIONS					DO NOT SCALE DRAWING	3.5		PHONE JA	ACK	El	H35MM	1 SE	RIES	A