
## MicroSD Card





4GB, 8GB, 16GB, 32GB, 64GB, 128GB, 256GB, 512GB

CL4, CL6, CL10

# Keep your important memories safe & sound

#### Highlights:

- Up to 100MB/s Read Speed to save data transfer time for HD Images and Videos
- Up to 60MB/s Write speed for faster data transfer
- Full HD Ready with variants U1, U3, V10, V30
- Built for and tested in harsh conditions temperature proof, water proof, shock proof & X Ray proof
- With Adaptor for compatibility with full size SDXC & SDHC





Get faster speeds for fast transfer, performance and HD Media files. Ideal for your Android smartphone, action/digital cameras, CCTV's, Drone etc all. This high performance Micro SD card handles 4K UHD video recording, full HD Videos and high resolution photos. Sahasra Micro SD Cards reads upto 100MB/s and writes upto 60MB/s.

#### Good for Capturing and storage of HD Videos

Perfect for recording, storage and data transfer during outdoor adventures, weekend trips, or sporting events without skipping frames. With upto 512GB Sahasra Micro SD Card lets you store uninterrupted HD Videos & Pictures with its variants UHS Speed class U1, U3 & videos class V10, V30 etc.

#### Write Speeds of upto 100MB/s

Capture fast action photos or shoot full HD Videos with write speeds of up to 100MB/s. Sahasra Micro SD Card lets you shoot and store more and faster.

#### **Durable Design for use in extreme environments**

Sahasra Micro SD Cards are shockproof, temperature proof, waterproof and x-ray proof. So you can enjoy your adventures without worrying about the durability of your memory card.



### **Technical Specifications:**

Specifications:		
Available Capacities:	4GB, 8GB, 16GB, 32GB, 64GB, 128GB, 256GB, 512GB	
Speed (R &W):	100MB/s & 60MB/s	
Color:	Black	
mSD Dimension (L x W x H):	14.99 x 10.92 x 1.02 mm	
Adapter Dimension (L x W x H):	24 x 32 x 2.1 mm	
Weight:	2 g	
Operating Temperature:	-25°C to 85°C	
Storage Temperature:	-40°C to 85°C	
Compatibility:	Compatible with microSDHC & microSDXC UHS-I Support Host Devices	
Devices Supported:	Smartphone, CCTV, Drones, iOT Devices etc.	
Durability:	Water & Dust Resistance	
Warranty:	5 Years Limited Warranty	

### **Ordering Information:**

Capacity	Part Code	UPC Code
4GB	CA227-023	753569703300
8GB	CA227-014	631576355111
16GB	CA227-015	631576355128
32GB	CA227-016	631576355135
64GB	CA227-004	631576355142
128GB	CA227-005	753569649448
256GB	CA227-006	753569677113
512GB	CA227-017	753569792601

#### For More Information:

Sahasra Electronics Pvt. Ltd.

129-G, Noida Special Economic Zone Noida-201305, Uttar Pradesh, India

Email: memory@sahasraelectronics.com

Tel: +91-120-2462782/83









<sup>\*</sup> Read/Write Speed is based on internal testing, Performance may be lower depending on drive capacity, Host device, Usages conditions & other factors