

# Prototyping Box + Board Kits

Box with custom fit breadboard

## Product highlights

- Custom fit prototyping projects

## Specifications

<b>Box Material:</b>	ABS Plastic
<b>Breadboard Specs</b>	
- <b>Pitch:</b>	0.1" x 0.1" grid (2.54mm)
- <b>Material:</b>	FR4 Laminate
- <b>Thickness:</b>	0.062" (1.57mm)
<b>Packaging:</b>	Shrink wrap
<b>Shipped with:</b>	Box, lid, protoboard, and hardware

## Options:

PART NUMBER	BOX COLOR	LENGTH	WIDTH	DEPTH	HOLE SIZE	PLATING	SCREW SPECS
<a href="#">DKS-PB03-75</a>	Black	3.00	1.90	1.10	0.042	Non-plated holes	M2.5 x 8L
<a href="#">DKS-PB03-87</a>	Black	3.00	1.90	1.10	0.037	Plated holes	M2.5 x 8L
<a href="#">DKS-PG310-87</a>	Gray	2.60	1.80	1.40	0.037	Plated holes	M2.5 x 12L
<a href="#">DKS-PG10-75</a>	Gray	2.60	1.80	1.40	0.042	Non-plated holes	M2.5 x 12L
<a href="#">DKS-PB05-87</a>	Black	4.40	2.20	0.90	0.037	Plated holes	M2.5 x 8L
<a href="#">DKS-PB07-75</a>	Black	4.40	2.20	0.90	0.042	Non-plated holes	M2.5 x 8L
<a href="#">DKS-PB10-75</a>	Black	4.50	2.30	1.70	0.042	Non-plated holes	M3 x 25L
<a href="#">DKS-PB10-87</a>	Black	4.50	2.30	1.70	0.037	Plated holes	M3 x 25L
<a href="#">DKS-PB20-75</a>	Black	4.50	2.30	1.70	0.042	Non-plated holes	M3 x 25L
<a href="#">DKS-PG20-75</a>	Gray	3.50	3.50	2.20	0.042	Non-plated holes	M3 x 25L
<a href="#">DKS-PB20-87</a>	Black	5.30	2.90	1.90	0.037	Plated holes	M3 x 25L
<a href="#">DKS-PB30-87</a>	Black	6.30	3.70	2.40	0.037	Plated holes	M3 x 25L
<a href="#">DKS-PB10-75</a>	Gray	6.70	4.30	3.10	0.042	Non-plated holes	M3 x 25L
<a href="#">DKS-PG30-87</a>	Gray	6.70	4.30	3.10	0.037	Plated holes	M3 x 25L
<a href="#">DKS-PB40-87</a>	Black	7.70	4.30	2.90	0.037	Plated holes	M4 x 50L