

**Ethernet Cable, Cat7 Patch Cable,
Strain Relief, SSTP, 2.1336m, 7 ft,
Black**

**RoHS
Compliant**

Stock No.: CAT7-0031

FEATURES

- Strain Relief
- SSTP
- 26 AWG
- Stranded Copper




Product Description

Cat6 Snagless Network Patch Cable offers universal connectivity to computers and network components, such as routers, switch boxes, network printers, network-attached storage (NAS) devices, VoIP phones, and PoE devices.

General Specifications

Attribute	Value
Terminated/Unterminated	Terminated
Connector Type	RJ45
Cable Type	Ethernet
Length	2.1336m
Gauge	26 AWG
Conductor	Bare Copper
Shield/Unshielded	Shielded
Voltage Rating	30V
1.0 - 1000MHz Impedance (Ω)	100 \pm 15
Maximum Operating Frequency	1000MHz
Operating & Storage Temp.	-40°C to 60°C -40°F to 140°F
Installation Temp.	-20°C to 60°C -4°F to 140°F
Jacket Color	Black

Product Drawing



Dimensions: Millimeters (Inches)

Part Number Table

Part Number	Description
CAT7-0011	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 0.3048m, 1 ft, Black
CAT7-0021	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 0.9144m, 3 ft, Black
CAT7-0031	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 2.1336m, 7 ft, Black
CAT7-0041	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 3.048m, 10 ft, Black
CAT7-0051	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 4.2672m, 14 ft, Black
CAT7-0071	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 7.62m, 25 ft, Black
CAT7-0151	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 15.24m, 50 ft, Black
CAT7-0231	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 22.86m, 75 ft, Black
CAT7-0301	Ethernet Cable, Cat7 Patch Cable, Strain Relief, SSTP, 30.48m, 100 ft, Black

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.