


**Cabtite (cable entry system)  
CABTITE FR 16/8 BK SET**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

**General ordering data**

Type	CABTITE FR 16/8 BK SET
Order No.	<a href="#">2583740000</a>
Version	Frame, Cabtite (cable entry system), Polyamide, glass fibre-reinforced, Deep black, Height: 19.6 mm, Width: 70 mm, Depth: 19.6 mm, -40 °C...120 °C, IP54, IP65, IP66
GTIN (EAN)	4050118617146
Qty.	1 pc(s).

**Cabtite (cable entry system)  
CABTITE FR 16/8 BK SET**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Length	126 mm	Length (inches)	4.961 inch
Width	70 mm	Width (inches)	2.756 inch
Height	19.6 mm	Height (inches)	0.772 inch
Height of lowest version	19.6 mm	Depth	19.6 mm
Depth (inches)	0.772 inch	Mounting dimension - width	32 mm
Mounting dimension - height	103 mm	Net weight	42.48 g
Diameter	5.5 mm		

**General information**

Tightening torque	3 Nm	Opening width	46 mm
Opening length	91 mm	UL 94 flammability rating	V-0
Sealing element	2 large sealing elements or 4 small sealing elements or 1 large sealing element and 4 small sealing elements or 8 small sealing elements	Halogen	No
Silicone	No	Sealing	TPE
Material	Polyamide, glass fibre- reinforced		

**Classifications**

ETIM 6.0	EC002624	eClass 6.2	27-14-92-01
eClass 9.1	27-18-92-65		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Cabtite Installation Instructions</a>
--------------------	---

**Cabtite (cable entry system)  
CABTITE FR 16/8 BK SET**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

Drawings

