


REV.	ECN NO.	DATE	SIGN	DESCRIPTION
D	LEN1630103~107	2016/02/18	Ruru	Change Logo
E	C210636	2021/04/23	Vicky	△X8
F	C221881	2022/12/07	Vicky	△X1

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



- △ Note:
- * RoHS Compliant
 - * @C Important dimension
 - △ * Waterproof rate: IP67, mated Connector
 - Housing: Thermoplastic, Black
 - Pin: Copper alloy, Gold plated
 - Nut: Metal
 - O-Ring: Rubber, Green
 - Outer mold: Thermoplastic, Black
 - * Cable: UL2464, PVC Jacket, Black
 - △ * Cable length tolerance:

1M < L ≤ 3M:	+50/-0 mm
3M < L ≤ 5M:	+100/-0 mm
5M < L ≤ 10M:	±100 mm
10M < L ≤ 20M:	±200 mm
20M < L ≤ 30M:	±300 mm
30M < L ≤ 99M:	±500 mm

UNIT: mm		TITLE	O SEN, M8		ITEM NO	DRAWN BY	DATE
TOLERANCE	±0.5 mm	CABLE W/SR, F, F, MOLDING		Amphenol LTW	8-XXAFFM-SL7AXX	Ruru	2016/02/18
		SCALE	Free	SHEET 1 OF 2	安費諾亮泰企業股份有限公司	CHECKED BY	DATE
		REV.	F	SIZE A4		Rita	2016/02/18
		@C : Inspection Item			CUSTOMER	APPROVED BY	DATE
					ALTW	Lisa	2016/02/18
1	2	3	4	5	6	7	8 W0814-03-表單01A2



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

4P	5.0	22	8-04AFFM-SL7AXX
3P			8-03AFFM-SL7AXX
Contacts	Cable OD	AWG	Item No.

△ 8-XXAFFM-SL7AXX

XX: No. Of Pin

↑
 XX: 01~99Meters
01: 01Meter
02: 02Meters
 :
 :
99: 99Meters
 Cable Length(L): 01~99Meters

Pin Out	4	Black	黑	4	Black	黑
	3	Blue	藍	3	Blue	藍
	1	Brown	棕	2	White	白
				1	Brown	棕
	Pin #	Wire		Pin #	Wire	
Conn.	 <p>△ 3P</p>			 <p>△ 4P</p>		

△ Pin Assignments Front View

UNIT: mm	TITLE	
TOLERANCE ±0.5 mm	O SEN, M8 △△	
	CABLE W/SR, F, F, MOLDING	
	SCALE Free	SHEET 2 OF 2
REV. F	SIZE A4	QC: Inspection Item

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG. NO	CHECKED BY	DATE
CUSTOMER	APPROVED BY	DATE
	Ruru	2016/02/18
△ 8-XXAFFM-SL7AXX	Rita	2016/02/18
ALTW	Lisa	2016/02/18