


ZW 15 RS OR 1665**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

The RS 70 profile is supplied in fixed lengths. The desired length is obtained by connecting the individual pieces together. The PCB is pushed into the side of the profile. End cover plates close off the sides of the profile.. Elements for terminal rails and direct mounting are available here. The clip-on feet are permanently attached to the profile. Marking options are integrated into the side pieces.

General ordering data

Version	Electronics housings, RS 70 orange, Intermediate part, Width: 15 mm
Order No.	0119860000
Type	ZW 15 RS OR 1665
GTIN (EAN)	4008 190049898
Qty.	20 pc(s).

Creation date February 5, 2024 10:58:50 AM CET

Catalogue status 27.01.2024 / We reserve the right to make technical changes.

ZW 15 RS OR 1665

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	20.6 mm	Depth (inches)	0.811 inch
Height	70 mm	Height (inches)	2.756 inch
Width	15 mm	Width (inches)	0.591 inch
Net weight	3.704 g		

Material data

Comparative Tracking Index (CTI)	600 ≤ CTI	UL 94 flammability rating	V-2
----------------------------------	-----------	---------------------------	-----

General data

Colour	orange	Colour chart (similar)	RAL 2000
Encapsulation option	No	Protection degree	IP00

Classifications

ETIM 6.0	EC002779	ETIM 7.0	EC002779
ETIM 8.0	EC002779	ETIM 9.0	EC002779
ECLASS 9.0	27-18-27-90	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-27-92	ECLASS 11.0	27-18-27-92
ECLASS 12.0	27-18-27-92	ECLASS 13.0	27182792

Important note

Product information	<p>Height: TS 32 = 33.5 mm, TS 35x7.5 = 29 mm</p> <p>Dimensions of the PCB:</p> <p>PCB thickness: 1.6 (±0.2) mm</p> <p>PCB length: 67.8 (-0.2) mm</p> <p>Intermediary piece width = PCB width minus 2 x 9 mm (clip-in foot)</p> <p>Example:</p> <p>PCB width = 68 mm, intermediary piece width = 50 mm, intermediary pieces 2x ZW 25 RS or ZW 45 RS + ZW 5 RS</p>
---------------------	---

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL ANALO.SIGN.CONV. EN
	MB DEVICE MANUF. EN
	FL MACHINE SAFETY EN
	FL 72H SAMPLE SER EN
	PO OMNIMATE EN
	PO OMNIMATE EN