Search Products:

Home About Us Contact Us My Account View Cart/Checkout

Daburn Wire & Cable
Wire - Single Conductor
Cable - Multi-Conductors Braid Tubing & Sleeving
Lacing Tape, Cord, Wrap Litz Wire

Insulators
Hardware, Fasteners
Cross Reference Guides

EMSE SICO Systems Control Piping Solutions
Polytron Power Supplies
Precise Circuits
Electronic Components
New Products Newsletters
Quality & Certifications Technical Blog



Shop by Category

Home > Daburn Wire & Cable > Hardware, Fasteners > #10-58 Series Porcelain Feed-Thru Insulators

#10-58 Series Porcelain Feed-Thru Insulators



Price (Each): \$44.24 Available to Order

Product Options

Catalog Number: 10-52

Quantity: 25 Add to Cart

Share|

Quantity Discounts

,						
Quantity	Amount					
25 to 249	\$44.24					
250 to 2499	\$35.39					
2500 to 4999	\$28.31					
5000 or more	\$23.59					

nn: These are quality porcelain feed-thru insulators with a smooth glaze on the exteriors. They come with heavy nickel plated brass hardware plus cushioning washers. The corrugated constructions (III. 'B') provide twice the leak path of the straight (III.

DABI Cat.		Ш	HT. H	В	H1	H2		Mounting Hole	Hardware	Std. Pkg
10-	58	Α	5/8"	11/16"	1/4"	9/16"	5/32"	5/16"	6-32	50
10-	78	A	1"	13/16"	5/16"	11/16"	7/32"	7/16"	10-32	25
10-1	25	A	1 1/4"	7/8"	3/8"	7/8"	7/32"	7/16"	10-32	25
10-2	:34	A	2 3/4"	2 1/32"	1"	2 5/16"	9/32"	1 1/4"	1/4-20	10*
10-	79	В	1 3/8"	1 1/4"	11/16"	1 3/8"	7/32"	9/16"	10-32	25
10-	76	В	2 3/4"	1 5/8"	1"	2 1/4"	9/32"	3/4"	1/4-20	10*
10-	52	В	4 1/2"	2 1/8"	1 1/2"	2"	9/32"	1"	1/4-20	5*

Related Products



#10-205 Series Steatite Feed-Thru Insulators

More Info

Feedthrus come thru with top and bottoms for chassis, panel, shields, rack mounting. No hardware included. Made of L5 glazed Steatite. This series is RoHS compliant.



#10-215 Daburn Fish Spine Beads

More Info

Suitable for buss and heavy lines insulation. Beads follow bends and curves because of ball and socket style interlocks. Made of Steatite.



#10-06 Antenna Insulator

More Info

Antenna Insulator - Glazed White porcelair



#10-30 Series Steatite Cone Insulators



#10-40 Series Steatite Standoffs

nsulators have a smooth glaze white. They come complete with brass nickel pilated screws and cushion washers. This series is RoHS compliant.

These threaded Stealite pillars are made of L5 glazed Stealite with threaded holes on both sides, and have one hole mounting. This series is RoHS compliant.

These threaded Stealite pillars are made of L5 glazed Stealite with threaded holes on both sides, and have one hole mounting. This series is RoHS compliant.



#10-67 Series Metal Base Insulators

More Info



#10-68 Series Antenna Strain Insulators

More Info

Porcelain glazed to prevent moisture absorption. All have long leakage path-small cross section strength under continuos tension.



#10-73 Series Daburn Airplane Insulators

More Info

Suitable for mobile or aircraft or guy wire application. Compression type strain insulators. Nos. 10-73, 10-74 made of white glazed for absorption porcelain. No. 10-72 made of dry process porcelain.

Product Reviews Login to rate or review this product (0 Ratings, 0 Reviews)

Home | About Us | Contact Us | My Account | Shipping Policy | Return Policy | Privacy Policy | Sitemap | Cart Help

^{*} Please call to order less than 25.