



Item (Detail view)

End and intermediate plate; 2.5 mm thick

Item no.	281-326	GTN / EAN	4017332295543
Content	1 piece	Order unit	piece
Order quantity	25 piece	Increase in order quantity	(25, 50, 75, 100, ...)
Customer item no.		Customs Tariff no.	8538909990
Customs duty for the country of origin	CN	Available	-
List price	On request	Net price	On request
Availability	On request		



Note: Some items may not be available from your local WAGO company. Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS Compliant



Article details Approvals Downloads/Certificates

Description		End and intermediate plate; 2.5 mm thick																																				
Remarks																																						
Item properties		<table border="1"> <thead> <tr> <th colspan="3">Miscellaneous</th> </tr> <tr> <th>Name</th> <th>Value</th> <th>Unit</th> </tr> </thead> <tbody> <tr> <td>Width</td> <td>2.5 mm / 0.098 in</td> <td></td> </tr> <tr> <td>Height</td> <td>29 mm / 1.142 in</td> <td></td> </tr> <tr> <td>Depth</td> <td>73.2 mm / 2.882 in</td> <td></td> </tr> <tr> <td>Color</td> <td>orange</td> <td></td> </tr> <tr> <td>Fire load (MJ)</td> <td>0.126</td> <td>MJ</td> </tr> <tr> <td>Weight (g)</td> <td>4.2</td> <td>g</td> </tr> <tr> <td>Packaging</td> <td>BOX</td> <td></td> </tr> <tr> <td>Type</td> <td>2.5</td> <td>mm</td> </tr> <tr> <td>Main product function</td> <td>End plate</td> <td></td> </tr> <tr> <td>Product type</td> <td>Accessories</td> <td></td> </tr> </tbody> </table>	Miscellaneous			Name	Value	Unit	Width	2.5 mm / 0.098 in		Height	29 mm / 1.142 in		Depth	73.2 mm / 2.882 in		Color	orange		Fire load (MJ)	0.126	MJ	Weight (g)	4.2	g	Packaging	BOX		Type	2.5	mm	Main product function	End plate		Product type	Accessories	
Miscellaneous																																						
Name	Value	Unit																																				
Width	2.5 mm / 0.098 in																																					
Height	29 mm / 1.142 in																																					
Depth	73.2 mm / 2.882 in																																					
Color	orange																																					
Fire load (MJ)	0.126	MJ																																				
Weight (g)	4.2	g																																				
Packaging	BOX																																					
Type	2.5	mm																																				
Main product function	End plate																																					
Product type	Accessories																																					

Upwards