


Data sheet | Item number: 870-568

End and intermediate plate; 2 mm thick; gray

www.wago.com/870-568



Data

Physical data

Width	2 mm / 0.079 inches
Height	106 mm / 4.173 inches
Depth	52.5 mm / 2.067 inches

Material Data

Note (material data)

[Information on material specifications can be found here](#)

Color	gray
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.159 MJ
Weight	5.3 g

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Commercial data








Product Group	16 (Rail Mounted Terminal Blocks with CCC)
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 8.0	EC000886
ETIM 7.0	EC000886
PU (SPU)	50 (25) pcs
Packaging type	box
Country of origin	CN
GTIN	4017332529594
Customs tariff number	8538909990

Environmental Product Compliance


RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Required accessories

End plate

Through terminal block		
	Item no.: 870-951 Triple-deck terminal block; Through/through/through terminal block; L/L/L; suitable for Ex e II applications; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®; 2,50 mm ² ; light gray	www.wago.com/870-951
	Item no.: 870-957/999-950 Triple-deck terminal block; Ground conductor/through/through terminal block; 2.5 mm ² ; PE/L/L; suitable for Ex e II applications; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm ² ; light gray	www.wago.com/870-957/999-950
	Item no.: 870-551 Triple-deck terminal block; Through/through/through terminal block; L/L/L; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®; 2,50 mm ² ; gray	www.wago.com/870-551
	Item no.: 870-556 Triple-deck terminal block; 6-conductor through terminal block; L; internal commoning; conductor entry with violet marking; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®; 2,50 mm ² ; gray	www.wago.com/870-556
	Item no.: 870-558 Triple-deck terminal block; Shield/through/through terminal block; 2.5 mm ² ; Shielding/N/L; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm ² ; gray	www.wago.com/870-558
	Item no.: 870-553 Triple-deck terminal block; Through/through/through terminal block; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm ² ; CAGE CLAMP®; 2,50 mm ² ; gray	www.wago.com/870-553
	Item no.: 870-559 Triple-deck terminal block; Shield/through/through terminal block; 2.5 mm ² ; Shielding/L/L; white conductor entry; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm ² ; gray	www.wago.com/870-559
Diode terminal block		

Subject to changes. Please also observe the further product documentation!



Item no.: 870-590/281-676

Component terminal block; triple-deck; with diode 1N4007; Anode, top; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-590/281-676



Item no.: 870-590/281-411

Component terminal block; triple-deck; with diode 1N4007; anode, right side; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-590/281-411



Item no.: 870-590/281-675

Component terminal block; triple-deck; with diode 1N4007; Anode, bottom; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-590/281-675



Item no.: 870-596/281-673

Component terminal block; triple-deck; with 3 diodes 1N4007; Right-side anode; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray


www.wago.com/870-596/281-673



Item no.: 870-590/281-410

Component terminal block; triple-deck; with diode 1N4007; anode, left side; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-590/281-410




Item no.: 870-596/281-674

Component terminal block; triple-deck; with 3 diodes 1N4007; Left-side anode; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-596/281-674


LED terminal block



Item no.: 870-593/281-434

Component terminal block; triple-deck; LED (red); 24 VDC; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-593/281-434



Item no.: 870-593/281-413

Component terminal block; triple-deck; LED (red); 24 VDC; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-593/281-413

Ground terminal block



Item no.: 870-557

Triple-deck terminal block; 6-conductor ground terminal block; 2.5 mm²; PE; without marker carrier; internal commoning; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm²; green-yellow

www.wago.com/870-557



Item no.: 870-567

Triple-deck terminal block; Ground conductor/through/through terminal block; 2.5 mm²; PE/N/L; without marker carrier; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-567



Item no.: 870-577

Triple-deck terminal block; Ground conductor/through/through terminal block; 2.5 mm²; PE/L/L; without marker carrier; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/870-577

Downloads

Documentation

Bid Text

870-568	Feb 19, 2019	xml	Download
---------	--------------	-----	----------

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



X81 - Datei			2.6 kB	
870-568 doc - Datei	May 31, 2017	doc	24.1 kB	Download
Additional Information				
		pdf	2.2 MB	Download

CAD/CAE-Data

CAD data

2D/3D Models 870-568		URL		Download
----------------------	--	-----	--	----------

CAE data

WSCAD Universe 870-568		URL		Download
------------------------	--	-----	--	----------

ZUKEN Portal 870-568		URL		Download
----------------------	--	-----	--	----------

EPLAN Data Portal 870-568		URL		Download
---------------------------	--	-----	--	----------

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 870-568 End and intermediate plate; 2 mm thick; gray		URL		Download
--	--	-----	--	----------

Installation Notes

Subject to changes. Please also observe the further product documentation!