


Data sheet | Item number: 752-8303/8000-002

Edge Controller; 2 x ETHERNET, 2 x USB, 1 x USB-C, HDMI, CAN, DI/DO, RS-232/485, Audio; Control


www.wago.com/752-8303_8000-002



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Data

Technical data

Communication

- Web browser
- Web browser (HTML5)
- Modbus TCP master/slave
- Modbus (UDP), WagoAppPlcModbus Library
- Modbus (RTU), WagoAppPlcModbus Library
- ETHERNET
- EtherNet/IP™ Adapter (slave)
- EtherNet/IP™ Scanner
- CANopen
- EtherCAT® Master
- OPC UA Server/Client
- OPC UA Pub/Sub (can be installed later)
- MQTT
- RS-232 serial interface
- RS-485 interface
- BACnet/IP, **requires an additional license**
- Telecontrol protocols, **requires an additional license**
- MicroBrowser (including visualization of CODESYS V2.3), requires an additional license

ETHERNET protocols

- DHCP
- DNS
- FTP
- FTPS
- HTTP
- HTTPS
- SSH

Visualization

- Web-Visu
- Web Visu

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



	Target Visu
Operating system	Real-time Linux (with RT-Preempt patch)
Processor	ARM [®] Cortex [®] A9 Quadcore 1.0 GHz
Programming environment	CODESYS V3.5, Firmware Release 24 or higher <i>e!COCKPIT</i> (based on CODESYS V3) up to Firmware Release 22
Baud rate (communication/fieldbus 1)	10/100 Mbit/s
Baud rate (communication/fieldbus 2)	1 MBd
Baud rate	ETHERNET: 10/100 Mbit/s; CAN: 1 MBd
Main memory (RAM)	2 GB, DDR3 SDRAM
Internal memory (flash)	4096 MB
Internal memory (flash)	4 GB, eMMC
Non-volatile hardware memory	128 Kbytes
Interfaces (USB)	2 x USB 2.0 socket, type A; 1 x USB OTG socket, type C
Onboard I/Os	4 x DIO, configurable
Indicators	3-color LED – red, green, blue; 4 x red/green LED
Supply voltage	24 VDC, SELV (18 ... 31.2 V); LPS; with reverse voltage protection
Input current (max.) (24 V)	120 mA
Operating power	2.9 W, without USB load; 9.4 W, with USB load

Connection data

Connection technology: communication/fieldbus	ETHERNET: 2 x RJ-45; CANopen: 1 x D-sub 9 plug; RS-232/-485 interface: 1 x D-sub 9 socket
---	---

Physical data

Width	65 mm / 2.559 inches
Height	123 mm / 4.843 inches
Depth	115 mm / 4.528 inches

Mechanical Data

Weight	600 g
Housing material	Aluminum, powder-coated

Environmental requirements

Ambient temperature (operation)	-20 ... +60 °C
Ambient temperature (storage)	-20 ... +80 °C
Protection type	IP20
Relative humidity (without condensation)	90 %

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



Mounting type	DIN-35 rail
---------------	-------------



Commercial data

ETIM 8.0	EC001413
Recupel Type	
PU (SPU)	1 pcs
Packaging type	BOX
Country of origin	DE
GTIN	4066966108996
Customs tariff number	84714100000


Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates**General approvals**

Logo	Approval	Additional Approval Text	Certificate name
	KC National Radio Research Agency	Article 58-2, Clause 3	R-R-W43-EDGE752
	UL Underwriters Laboratories Inc. (ORDINARY LOCATIONS)	UL 61010-2-201	E175199

Declarations of conformity and manufacturer's declarations

Logo	Approval	Additional Approval Text	Certificate name
	EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-

Downloads**Documentation****Manual**

Migration Guide	V 1.3.0 Jul 3, 2023	pdf 5.1 MB	Download
-----------------	------------------------	---------------	----------

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



Migration from e!COCKPIT projects to CODESYS V3.5

Product Manual WAGO Edge Controller 2 x ETHERNET, 2 x USB, 1 x USB-C, HDMI, CAN, DI/DO, RS-232/485, Audio; Control	V 1.3.0 May 24, 2022	pdf 1.8 MB	Download
Product Manual OPC UA Mapping Editor	V 1.1.0 Mar 11, 2022	pdf 3.4 MB	Download
OPC_UA Mapping Editor Online Help HTML		URL	Download
Migrationsleitfaden von e!COCKPIT-Projekten zu CODESYS V3.5 Online Hilfe (HTML)		URL	Download

Bid Text

752-8303/8000-002 X81 - Datei		xml 5.7 kB	Download
752-8303/8000-002 docx - Datei		docx 30.7 kB	Download
ausschreiben.de 752-8303/8000-002		URL	Download

System Description

Edge Computing; General Product Information		pdf 224.4 kB	Download
---	--	-----------------	----------

Engineering-Software

WAGO Solution Builder

WAGO Solution Builder		URL	Download
-----------------------	--	-----	----------

WAGO Solution Builder is a software solution that enables holistic and efficient building automation project engineering and can be used throughout the entire building life cycle. With WAGO Solution Builder, you can organize all of your own building automation projects on a web interface and, thanks to integrated device management, ensure that your project-specific WAGO controllers are always updated.

Once downloaded, the software can be used for free during the launch phase until October 2023. After that, you can activate WAGO Solution Builder by purchasing a license key.

Configuration and Commissioning Software

WAGOupload	1.16.1.0 Feb 2, 2022	zip 12.4 MB	Download
------------	-------------------------	----------------	----------

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



WAGOupload is a stand-alone PC software for transferring, backing up and restoring PLC applications on WAGO 750 Series controllers.

CODESYS V3 with WAGO DSP

CODESYS Development System V3 including WAGO Device Support Package

[URL](#)

[Download](#)

Have you not yet installed CODESYS Development System V3? Would you like to program WAGO controllers? Then you've come to the right place!

With CODESYS Development System V3, you program according to the IEC 61131-3 standard. The software enables graphical and textual programming. Create visualizations with the integrated visualization editor.

You benefit from several WAGO libraries that support your application.

You can find it in our WAGO Download Center:

- CODESYS V3.5.x, 64-bit
 - WAGO-Plugins
 - WAGO libraries
 - Device firmware
 - Device description for WAGO controllers
 - ...as well as other WAGO tools and add-ons
-

WAGO DSP for CODESYS V3

WAGO Device Support Package for CODESYS Development System V3

[URL](#)

[Download](#)

Have you already installed CODESYS Development System V3 (min. V3.5.17.3) and only need WAGO libraries and device descriptions for the WAGO controllers? Then you've come to the right place!

Use your CODESYS Development System V3 and expand it with the device descriptions of the WAGO controllers and several WAGO libraries.

You can find it in our WAGO Download Center:

- WAGO-Plugins
 - WAGO libraries
 - Device firmware
 - Device descriptions for WAGO controllers
 - ...sowie weitere WAGO-Tools und Add-ons
-

Runtime Software

Firmware

Image Update (SD Karte) Edge Controller

V 22 SP1

zip

[Download](#)

WAGO_FW0752-8303_V031010_IX22_SP1_I

Dec 14, 2022

220.8 MB

WUP Update (WAGOuploadTool) Edge Controller

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.



WAGO_FW0752-8303_V031010_IX22_SP1_W

V 22 SP1
Dec 14, 2022

zip
218.8 MB

[Download](#)

Edge Controller Codesys V3.5 Firmware
Edge Controller Codesys V3.5 Firmware

[URL](#) [Download](#)

CAD/CAE-Data

CAD data

2D/3D Models 752-8303/8000-002

[URL](#) [Download](#)

CAE data

ZUKEN Portal 752-8303/8000-002

[URL](#) [Download](#)

EPLAN Data Portal 752-8303/8000-002

[URL](#) [Download](#)

Asset Administration Shell

Asset Administration Shell 752-8303/8000-002

[URL](#) [Download](#)

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 752-8303/8000-002

[URL](#) [Download](#)

Edge Controller; 2 x ETHERNET, 2 x USB, 1 x USB-C, HDMI, CAN, DI/DO, RS-232/485,
Audio; Control

Installation Notes

Subject to changes. Please also observe the further product documentation!