# Data Sheet | Item Number: 207-1331

Gelbox; Branch; for cables; with gel; 221, 2x73 Series; max. 4 mm² connectors; wi-

thout splicing connectors; Size 1; gray

https://www.wago.com/207-1331















## Data Sheet | Item Number: 207-1331

https://www.wago.com/207-1331



Note on Packaging Unit (PU) and Subpackaging Unit (SPU):

If you order a full PU, you will receive our eco-friendly, sustainable cardboard blisters packed in a shelf-ready box.

If you order a quantity smaller than a full PU, you will receive the eco-friendly, sustainable cardboard blisters without a shelf-ready box.

Please refer to the system description for the splicing connectors that can be used.

#### Your benefits:

- Easy, fast and safe to use
- · Can be used immediately and accessed again later
- · Silicon-free
- Label-free
- · Suitable for indefinite storage
- The complete system consisting of WAGO's gelboxes and splicing connectors has been VDE-tested and IPX8-certified.

## Connection data

#### Connection 1

Actuation type Locking system

/sica	

Width	32 mm / 1.26 inches
Height	17.8 mm / 0.701 inches
Depth	33.6 mm / 1.323 inches

#### Mechanical data

Design	Size i
Mounting type	Flying leads

Suitable for 4 mm² splicing connectors

#### Material data

Note (material data)

<u>Information on material specifications can be found here</u>

Color gray
Housing material Polypropylene
Fire load 0 MJ
Weight 12 g

#### **Environmental requirements**

Ambient temperature (operation)	-55 +85 °C
Ambient temperature (storage)	0 +40 °C

^-	nm			: _ I	۔ ا۔	
<b>.</b>	m	me	, LC	ıaı	n:	на

ETIM 8.0	EC001170
ETIM 7.0	EC001170
PU (SPU)	48 (4) pcs
Country of origin	DE
GTIN	4055143997799
Customs tariff number	85389099990

https://www.wago.com/207-1331



#### **Environmental Product Compliance**

RoHS Compliance Status Compliant, No Exemption

#### Approvals / Certificates

#### General approvals



rungsinstitut

Approval	Standard	Certificate Name
VDE VDF Prüf- und Zertifizie-	EN 60998	400051938

#### Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
UK-Declaration of Conformity WAGO GmbH & Co. KG	-	-

## Downloads

#### **Environmental Product Compliance**

#### Compliance Search

**Environmental Product** 

Compliance 207-1331



#### Documentation **System Description System Description** 207 Series Gel boxes 1156.45 System Description pdf 207 Series Gel boxes . 1191.37

КВ	$\overline{\downarrow}$
' KB	<u>↓</u>

Bid Text		
207-1331	xml 3.58 KB	$\overline{\downarrow}$
207-1331	docx 20.35 KB	$\overline{\downarrow}$

## CAD/CAE-Data

CAD data

2D/3D Models 207-1331

CAE data **ZUKEN Portal** 207-1331



### **Installation Notes**

## Installation



Open the Gelbox at the side latches.



Place the wired connector in the Gelbox.



Place the wired connector in the Gelbox.



Close the Gelbox.

## Data Sheet | Item Number: 207-1331

https://www.wago.com/207-1331

#### Installation





Close latch securely.

Re-accessible:

- Open the Gelbox.
- Remove the gel.Rewire with new components.







Lift the flap and pull the cover perforation forward.

Press in the perforation on the sides.

Tear off the cover from the perforation.

As a counter display: Bend the rear flap at the fold, straighten it and fix it in the card-



If the flap is not required, tear off from the perforation.

Subject to changes. Please also observe the further product documentation!