





Europe Middle East Africa 2019



Fibre Optic Cleaners

When you need perfectly clean splices & connectors™

Sticklers[™] Fibre Optic Splice & Connector Cleaner Cleaning Fluid Improves the cleaning efficiency of wipes, swabs and cleaning tools



- Nonflammable cleaning fluid specifically engineered for cleaning ceramic and composite ferrule faces; glass & plastic lenses
- · Dissipates electrostatic charge and removes dust, dirt, fingerprints & moisture
- Ultra-pure, fast-drying formula leaves no residues
- Non-hazardous for easy storage & shipping
- RoHS & REACH compliant
- NSN 6850-01-592-9381
- NSN 6850-01-592-9440

DESCRIPTION	WEIGHT	SIZE	PART NUMBER	CLEANS
Fibre Optic	85 g	58 mL	MCC-POC03M	650+ Cleans/Can
Splice & Connector Cleaner	284 g	196 mL	MCC-POC10M	2500+ Cleans/Can
	1.14 kg	1 L	MCC-POC03GL	Variable to Application
	4.54 kg	3.8 L	MCC-POC03GG	Variable to Application



Sticklers[™] MultiTask Surface Cleaner Presaturated Wipes & Refills



Refills reduce costs & waste!

- Strong lint-free fabric wipes won't shred, lint or pill-ideal for pre-cleaning
- Removes fingerprints, grime, dust, lint, waterproofing gels, oils and grease
- from cabinets and equipment in fibre optic and networking environment
- Water and high-purity alcohol for safe cleaning
- Unique "slam-shut" package for extra long service life

DESCRIPTION	PART NUMBER	PACKAGING	
Presaturated Wipes	MCC-SMSCW	100 wipes, 12.7 cm x 20.32 cm	
Presaturated Wipe Refills	MCC-SMSCWR	100 wipes, 12.7 cm x 20.32 cm	

Sticklers[™] Adhesive & Gel Remover Pen

- Convenient pen dispenser quickly and safely removes adhesives, buffer tube gel (i.e. icky-pic) labels, tape residue, grease, oils and some inks
- Dispenses fluid when pressed onto a surface, ensuring fluid is always used effectively with no waste, spills or odours
- Ideal for datacom, enterprise centres and repair centres

Packaging: Individial Pen; 10 mL each

DESCRIPTION	PART NUMBER
Adhesive & Gel Remover Pen	MCC-SAGR

Optical-Grade Dust & Particle Remover Cleans dust & connector wear debris from

inaccessible areas



- High-pressure abrasion-free cleaning
- Safe on energised equipment
- High-purity, optical-grade duster
- Extension spray tube included
- Leaves no residue
- RoHS & WEEE compliant

DESCRIPTION		SIZE	PART NUMBER	
Optical Grade	Nonflammable	280 g (231 mL)	MCC-DST107	
Dust & Particle Remover	Flammable	250 g (455 mL)	MCC-DST147	

STICKLERS

Sticklers[™] Clean Wipes Optical Grade Wipes Lint-free wipes for connectors and bare fibres

- Optical-grade, 5.08 cm x 10.08 cm lint-free wipes engineered for cleaning fibre for splicing and cleaning fibre optic connector end-faces
- · Exclusive electrostatic dissipating cleaning surface
- Resists tearing and shredding
- · High-modulus wipes with high absorbency
- · Makes "wet/dry" cleaning simple and cost-effective



For best results, use with: Sticklers™ Fibre Optic Splice & Connector Cleaner





to clean both end-faces on duplex connectors with one swipe.




- A. Clean Wipes 640 optical-grade wipes are packaged in an inner box with eight colour-coded cleaning slots. Slots allow for multiple cleans with no cross-contamination. Inner box has a dissipative lining to remove triboelectric charging to eliminate static caused contamination. Highly-visible plastic outer box keeps wipes clean and dry. Slots accept LC and SC duplex.
- B. Clean Wipes 600 optical-grade wipes in portable cleaning box is perfect for your tool box. Box features six colour-coded cleaning slots for multiple cleans per wipe.
 Slots accept LC and SC duplex.
- **C. Outdoor Clean Wipes** single wipes provide fast, consistent and convenient end-face cleaning even in harsh environments. Each wipe is protected in a hermitically-sealed package that keeps it clean and dry until opened.
- D. Clean Wipes 90 optical-grade wipes in convenient mini-tub ideal for the benchtop. Engineered for use on bare fibre before splicing and also for cleaning fibre optic jumpers. NSN: 7920-01-547-6547

	DESCRIPTION	PART NUMBER	CLEANS	
А	Clean Wipes 640	MCC-WCS640	640 Cleans/Box	
В	Clean Wipes 600	MCC-WCS100	600 Cleans/Box	
С	Clean Wipes Singles	MCC-FA1	50 Packets/Bag	
D	Clean Wipes 90	MCC-WFW	90 Wipes/Tub	
-	Clean Wipes Flat Pack	MCC-WF44	50 Wipes/Bag	



Sticklers[™] Cassette CleanClicker[™] Fibre Optic Connector Cleaner Clean multiple end-faces before advancing the cleaning ribbon for fast, money-saving cleaning



Sticklers[™] MPO CleanClicker[™] 600 Fibre Optic Connector Cleaner

Keyless cleaning tip allows operator to insert cleaner up or down for hard to reach connectors



Sticklers[™] CleanClicker[™] 400 Fibre Optic Connector Cleaner Compact size for cleaning in confined spaces



- 1.25mm cleans LC, MU, ODC, ARINC801, NGCON, CS and other hardened 1.25mm connector systems
- Optimised for carrier networks, ideal for OSP and premises applications, enterprise applications, field installation kits, OEM assembly and research labs

DESCRIPTION	PART NUMBER	CLEANS
1.25mm CleanClicker™ 400 Cleaner	MCC-CCM125	400+



Sticklers[™] CleanClicker[™] 750 Fibre Optic Connector Cleaners Self-aligning clicker for cleaning both ends of a connector pair

- · Click-to-clean dust particulate and oil contamination
- High purity cleaning strand delivers perfect cleanings with a single click
- Uses super-smooth activation with light tip forces to deliver great cleaning with no risk of damaging the end-face
- Long barrel length to operate in high fibre-count panels without disrupting adjacent connectors
- · Money-saving refills sold in pack of two cartridges







2.5 CleanClicker[™] 750

Refill Cartridge

	1.25 CLEANCLICKER™ 750	2.5 CLEANCLICKER™ 750
Ferrule Services	1.25mm	2.5mm
Label Colour Code	Green	Blue
Connector Systems Serviced	 LC/UPC LC/APC Hardened LC MU/UPC MU/APC Some hardened 1.25mm* 	 SC/UPC SC/APC ST FC/APC FC/UPC E2000/UPC E2000/APC Some hardened 2.5mm* OptiTip
Cleaning Capacity	750+ (Refillable)	750+ (Refillable)

*Please contact the manufacturer or Sticklers™ for information on use with proprietary connector systems

DESCRIPTION	PART NUMBER	CLEANS
1.25mm CleanClicker™ 750 Cleaner	MCC-CCU125	750+
1.25mm CleanClicker™ 750 Refill Cartridge (2)	MCC-CCR125	1500+
2.5mm CleanClicker™ 750 Cleaner	MCC-CCU250	750+
2.5mm CleanClicker™ 750 Refill Cartridge (2)	MCC-CCR250	1500+



CLEANSTIXX[™] CONNECTOR CLEANING STICKS





Sticklers[™] CleanStixx[™] Connector Cleaning Sticks Versatile sticks cleans all connector types, sizes or configurations

MCC-S16


MCC-S12

- · Patented sintered polymer fibres for consistent high-purity cleaning
- · Precisely molded to clean the entire end-face
- Ultra-clean construction does not contain fabric, foam or glue
- Packaging: high-purity, self-sealing bags 5 packages of 10 sticks per box



For best results, use with: Sticklers™ Fibre Optic Splice & Connector Cleaner

CleanStixx[™] Connector Cleaning Sticks Deliver Fast & Consistent Results



DESCRIPTION	PART NUMBER	CLEANS
1.6mm CleanStixx™ - Red <i>NSN: 6070-01-553-2262</i>	MCC-S16	MIL PRF 29504/5, MIL PRF 29504/15, MIL DTL 38999, MIL DTL 28876, SMPTE304 Jack
1.25mm CleanStixx™ - Green <i>NSN: 6070-01-553-2267</i>	MCC-S12	LC, MU, SFP+, ODC, ARINC801, NGCON, LUXCIS, CS
2.5mm CleanStixx™ - Blue <i>NSN: 6070-01-553-2263</i>	MCC-S25	SC, ST, FC, E2000, MIL DTL 83526, OptiTap
MT CleanStixx™ - Pink	MCC-XMT	MPO, OptiTip, HFMOC, MT Ferrules
Pin Termini CleanStixx™ - Yellow NSN: 6070-01-553-2258	MCC-P25	MIL PRF 29504/4, MIL DTL 29504/14, MIL PRF 28876, MIL DTL 83526, MIL DTL 38999, ARINC801, ODC, SMPTE 304 Plug, NGCON
EB CleanStixx™ - Purple	MCC-EB12	1.2mm Lensed Termini for MIL 38999
Combo Pack - Includes 10 of each: 1.6mm, 1.25mm, 2.5mm, Pin Termini, MT CleanStixx™	MCC-VM	Military and Commercial Connectors
Combo Pack - Includes: 10 of S12, 20 of S25 and 20 of P25 CleanStixx™	MCC-VS	Commercial Connectors

Sticklers[™] Fibre Optic Cleaning Kits

Optimised for general installations & enterprise environments Everything you need for fast, reliable fibre optic cleaning Ship anywhere without hazardous material fees





Kits Contain:

Rugged Carrying Bag with Extra Pockets Fibre Optic Splice & Connector Cleaners Variety of Sticklers CleanClickers[™] Optical Grade Clean Wipes Multiple-sized CleanStixx[™] Handy LED Inspection Flashlight

PART NUMBER		MCC-FK03	MCC-FK05	MCC-FK08	MCC-FK-FTTA	MCC-FK-FTTH
KIT CONTAINS	PAGE	Standard	Military Ready	High Volume	1.25mm FTTA	2.5mm FTTH
CLEANS		800+	800+	2300+	1500+	1800+
1.25mm CleanClicker 750	5	-	-	1	-	-
2.5mm CleanClicker 750	5	-	-	1	-	1
1.25mm CleanClicker 400	4	-	-	-	1	-
Cassette CleanClicker	4	-	-	-	1	1
Cleaning Fluid (85 g / 58mL Can)	2	2	2	2	1	1
Optical Grade Wipes (640 /Box)	3	-	-	-	1	1
Optical Grade Wipes (600 /Box)	3	1	1	1	-	-
Optical Grade Wipes (90 /Tub)	3	1	1	1	1	1
Optical Grade Wipes (Singles)	3	25	25	25	-	-
1.25mm Cleaning Sticks	6	20	10	20	50	-
2.5mm Cleaning Sticks	6	30	10	30	-	50
Pin Termini Cleaning Sticks	6	-	10	-	50	-
1.6mm Cleaning Sticks	6	-	10	-	-	-
MT Cleaning Sticks	6	-	10	-	-	-
Bag Color	-	Orange	Black	Orange	Orange	Orange

STICKLERS™ FIBRE INSPECTION KITS

ST/CKLERS





INSPECT, CLEAN, INSPECT

CleanStixx[™] Connector Cleaning Sticks

Optical-Grade Clean Wipes 90

Fibre Optic Splice & Connector Cleaner Cleaning Fluid

VIAVI FiberChek[™] Probe Microscope, Accessories & Case

Select The Kit that Best Meets Your Needs:

PART NUMBER	MCC-FK17	MCC-FK18	MCC-FK19	MCC-FK20
KIT CONTAINS	CleanKit LC/MPO - NS	LC Kit 1.25mm FTTA	SC Kit 2.55mm FTTH	Field Inspection & Clean
CleanClicker [™] 750 - 1.25mm (PN: MCC-CCU125)	1	2	-	1
CleanClicker [™] 750 - 2.5mm (PN: MCC-CCU250)	-	-	2	1
MPO CleanClicker [™] 600 (PN: MCC-CCMPO)	1	-	-	-
Fibre Optic Splice & Connector Cleaner Cleaning Fluid (PN: MCC-POC03M)	2	2	2	2
Cassette CleanClicker [™] (PN: MCC-WRC)	1	-	-	-
Optical Grade Clean Wipes (90) (PN: MCC-WFW)	1	1	1	1
CleanStixx [™] - 1.25mm (50) (PN: MCC-S12)	2	2	-	1
CleanStixx [™] - 2.5mm (50) (PN: MCC-S25)	-	-	2	1
VIAVI FiberChek [™] Probe Microscope & Case	-	1	1	1
VIAVI FiberChek [™] Accessory Package Universal 1.25mm & 2.5mm connector, LC & SC Adapter Tips and Case, Cords	-	1	1	1
Rugged Heavy Duty Protective Case With custom foam insert & lid accessory holder 526mm x 437mm x 213mm	1	1	1	1

SticklersCleaners.com

MicroCare Corporation

595 John Downey Drive New Britain, CT 06051 USA CAGE: OATV9 Tel: +1 860 827 0626 Toll Free: 1 800 638 0125 Email: TechSupport@MicroCare.com

MicroCare Europe BVBA

Vekestraat 29 B11 Industriezone 't Sas 1910 Kampenhout, Belgium Tel: +32 2 251 95 05 Email: EuroSales@MicroCare.com MicroCare U.K. Ltd Seven Hills Business Park, Morley, Leeds, West Yorkshire, UK LS27 8AT Tel: +44 (0) 113 3501008 Email: mcceurope@microcare.com

Follow Us!

MicroCare Asia Pte Ltd

102E Pasir Panjang Road #03-01 Citilink Warehouse Complex Singapore 118529 Tel: +65 6271 0182 Email: TechSupport@MicroCare.sg

ISO 9001:2015 Registered

© 2019 MicroCare. All Rights Reserved. MicroCare, the MicroCare logo, Sticklers, When you need perfectly clean splices & connectors, CleanStixx and CleanClicker are trademarks or registered trademarks of MicroCare Corporation. FiberChek^{*} is a trademark of VIAVI Solutions Inc. The information set forth herein is based on data believed to be reliable. MicroCare makes no warranties express or implied as to its accuracy and assumes no liability arising out of its use by others. This publication is not to be taken as a license to operate under, nor infringe upon, any patents not herein expressly described.

CAT-STKEU20

Rugged, Heavy-Duty Protective Case

MPO CleanClicker[™] 600 Fibre Optic Connector Cleaner

CleanClicker[™] 750 Fibre Optic Connector Cleaners