

Accessories
G 20/0.50A/F

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Product image

Similar to illustration

Klippon® Connect with clamping yoke Technology

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

General ordering data

Type	G 20/0.50A/F
Order No.	043060000
Version	Active components, Fuse
GTIN (EAN)	4008190046835
Qty.	10 pc(s).

Accessories

G 20/0.50A/F

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Width	5 mm	Width (inches)	0.197 inch
Height	20 mm	Height (inches)	0.787 inch
Net weight	0.9 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Material data

Colour	Light Grey
--------	------------

System specifications

Version	Fuse accessories
---------	------------------

Fuse cartridges

Cartridge fuse	G-Si. 5 x 20	Characteristics	quick-acting
Colour	Light Grey	Current	0.5 A
Melting integral	0.23 A ² s	Power output (@ 1.5 In)	1 W
Rated breaking capacity	1.5 kA	Version	Fuse accessories
Voltage drop	600 mV		

Rating data

Rated voltage	250 V	Rated current	0.5 A
---------------	-------	---------------	-------

Classifications

ETIM 3.0	EC000035	ETIM 4.0	EC000035
ETIM 5.0	EC000035	ETIM 6.0	EC000035
UNSPSC	30-21-18-14	eClass 5.1	27-14-20-07
eClass 6.2	27-14-20-07	eClass 7.1	27-14-20-90
eClass 8.1	27-14-20-90	eClass 9.0	27-14-20-90
eClass 9.1	27-14-20-01		

Product information

Descriptive text ordering data	(M) = medium time-lag; (F) = quick-acting
Descriptive text technical data	<ol style="list-style-type: none"> 1) The company SIBA supplies G-type fuse cartridges 5 x 25 with indicator, also available in marine engineering version for 450 V~. 2) Fuse cartridges 5 x 30 (500 V~) for SAKS 3 are available from the company WICKMANN. 3) The company LINDNER supplies Neozed fuse cartridges, also available in marine engineering version for 440 V~. 4) Fuse cartridges with the dimensions 1" x 1/4" (25.4 x 6.35 mm) and 13/32" x 1 1/2" (10.3 x 38.1 mm) are not included in the product range. 5) Only for SAKS 1 and SAKS 7.

Approvals

ROHS	Conform
------	---------

Data sheet**Accessories
G 20/0.50A/F**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data**Downloads**

Brochure/Catalogue	CAT 1 TERM 16/17 EN
Engineering Data	WSCAD
