

**SAIB-VSA-3P/250/9-OB**
**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmuller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

**General ordering data**

Type	SAIB-VSA-3P/250/9-OB
Order No.	<a href="#">1873070000</a>
Version	Valve plug, Socket, angled
GTIN (EAN)	4032248495344
Qty.	1 pc(s).

**SAIB-VSA-3P/250/9-OB****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

**Technical data****Dimensions and weights**

Net weight 25 g

**Temperatures**

Operating temperature range, max. 85 °C Operating temperature range, min. -25 °C

**Technical data customisable plug-in connectors**

Cable diameter, max.	8 mm	Cable diameter, min.	6 mm
Cable gland	PG 9	Coding	Design A (18 mm)
Connection cross-section, max.	1.5 mm <sup>2</sup>	Connection cross-section, min.	0.34 mm <sup>2</sup>
Contact surface	Ni	Housing main material	PA 6 GF
Insulation resistance	10 <sup>8</sup> Ω	No. of poles	3
Pollution severity	3	Protection degree	IP65
Rated current	10 A	Rated voltage	250 V
Temperature range of housing	-25...+85 °C	Type of connection	Screw connection

**Classifications**

ETIM 3.0	EC002062	ETIM 4.0	EC002636
ETIM 5.0	EC002636	ETIM 6.0	EC002062
UNSPSC	30-21-18-10	eClass 5.1	27-26-07-01
eClass 6.2	27-26-07-03	eClass 7.1	27-44-01-01
eClass 8.1	27-44-01-01	eClass 9.0	27-44-01-01
eClass 9.1	27-06-03-12		

**Approvals**

Approvals



ROHS Conform

**Downloads**Brochure/Catalogue [CAT 8 SAI 15/16 EN](#)  
[FL FIELDWIRING EN](#)