1801 Morgan Street Rockford, Illinois 61102 800-435-2931 www.molexkits.com



Datasheet for 76650-0155

General Information

Part Number:

76650-0155

Manufacturer:

Molex / Waldom

Title:

Solderless Terminal Kit

PVC and Nylon Insulated Bullet Snap Plug and Receptacle,

Description:

and Non-Insulated Bullet Snap Plug and Receptacle

Product Family:

Snap Bullet

Certificates:

(Molex Parts within this kit) - EU RoHS Compliant, UL and CSA

Country of Origin: Kit assembled in U.S.A.

Specifications

Design

Configuration:

Wire-to-Wire

Terminal Type:

Plug and Receptacle

insulation:

PVC, Non-insulated and Nylon

Diameter:

3.96mm (.156")

Wire:

16-14 AWG

Product Highlights

Snap Solderless Terminals are easier and quicker to connect / mate. These are suitable for blind / hidden mating applications. These do not have to mate planarily like Quick Connects, but radially 360 deg.

Features and Benefits

- · Can be connected and disconnected repeatedly
- Designed to SAE specifications
- Features a PVC sleeve to protect against vibration damage by preventing wire flex at the crimp point
- Funnel entrance into the electrical barrel (on insulated) eliminates wire strand fold back and increases crimping rate
- · Splices two male snap plugs

Applications

- MRO (Maintenance Repair and Operations)
- Automotive



Datasheet for 76650-0155

Bill of Materials for Part No. 76650-0155

| | in Description | Kit |
|---------------|---|-----|
| 19033-0007 US | .156" Non-insulated Male Snap Bullet Connector, (16-14) AWG | 50 |
| 19034-0009 US | .156" PVC Male Snap Bullet Connector, (16-14) AWG | 30 |
| 19035-0009 US | .156" Dia, Male Snap Plug (16-14) AWG, Nylon Insulated | 30 |
| 19037-0004 US | .156" Dia, Female Snap Plug (16-14) AWG, Non-Insulated | 50 |
| 19038-0007 US | .156" PVC Female Snap Bullet Connector, (16-14) AWG | 15 |

Recommended Molex Tool(s) for Part No. 76650-0155*

Country

| Molex Part No. | of Origin | Description | |
|----------------|-----------|----------------------------|--|
| 64001-0100 * | USA | Hand Crimp Tool (RHT-1990) | |
| 64001-1400 * | USA | Hand Crimp Tool (RHT-2100) | |
| 64001-2100 * | USA | Hand Crimp Tool (RHT-8765) | |
| 64003-1200 * | USA | Hand Crimp Tool (RHT-1752) | |
| 64003-0100 * | USA | Hand Crimp Tool (RHT-1992) | |

^{*}Tool(s) not included in kit. Tool(s) ordered separately.