

1m Black SuperSpeed USB 3.0 (5Gbps) Cable - Right Angle A to B - M/M

Product ID: USB3SAB1MRA



The USB3SAB1MRA 1m Black USB 3.2 Gen 1 A to B cable features a right-angled USB 'A' male connector, enabling you to connect your USB 3.2 Gen 1 Type 'B' peripherals to your PC, laptop, or server, even in hard to reach areas and tight spaces.

The right-angled USB 'A' connector positions the cable nearly flush against a wall or other surface, and eliminates the space typically required to accommodate a 'straight' connection from the cable into the USB port.

Harnessing the full capabilities of the SuperSpeed USB 3.2 Gen 1 standard when used with a USB 3.2 Gen 1 host and device, the 1m cable offers a bandwidth of 5Gbps.

Plus, this right angle USB 3.2 Gen 1 cable also features high quality Shielded Twisted Pair (STP) construction, which helps prevent electro-magnetic interference and ensure reliable data communication.

The USB3SAB1MRA USB 3.2 Gen 1 A to B cable is backed by StarTech.com's Lifetime Warranty, for guaranteed quality and dependability.

Certifications, Reports and Compatibility



Applications

- Connect a SuperSpeed USB 3.0 Type B peripheral (hard drive enclosure, card reader, docking station, video capture device, etc.) to a USB 3.0 capable desktop, laptop, or server, even in hard to reach areas and tight spaces

Features

- 1x Right-angled USB 3.2 Gen1 'A' male connector
- 1x USB 3.2 Gen1 'B' male connector
- Designed and constructed to SuperSpeed USB 3.2 Gen1 Specifications
- High quality Shielded Twisted Pair (STP) construction
- Data transfer rates up to 5Gbps
- Molded connectors with strain relief
- Backward compatible with USB 2.0

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Foil shielded twisted pair

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	28 AWG
Cable Length	3.3 ft [1 m]
Product Length	3.3 ft [1 m]
Product Width	0.4 in [1.1 cm]
Product Height	0.6 in [1.4 cm]

Weight of Product	1.7 oz [48 g]
-------------------	---------------

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.8 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.7 in [1.8 cm]
Shipping (Package) Weight	2.1 oz [60.0 g]

What's in the Box

Included in Package	1 - 1m Black SuperSpeed USB 3.0 Cable Right Angle A to B - M/M
---------------------	--

**Product appearance and specifications are subject to change without notice.*