



Sign-up EN

[Products](#)

[Where to Buy](#)


[Media Center](#)

[Support](#)

[About Klein](#)

[Careers](#)

Home » [Catalog](#) » [Headlamps and Flashlights](#) » [Headlamps](#)



# Wide-Beam Headlamp with Mount for Hard Hat

## KHH56308

★★★★★ 5.0 (1) [Write a review](#)



- Rechargeable Wide-Beam Headlamp easily mounts directly to Klein Hard Hat and Safety Helmet accessory mounts
- Wrap around low-profile design for use in tight spaces
- FL1 rated All-on-High: 770 lumens, 5 hr; All-on-Medium: 540 lumens, 8 hr; All-on-Low: 270 lumens, 10 hr; Focus-High: 400 Lumens, 8 hr; Focus-Low: 150 Lumens, 12 hr
- 1300-Foot beam distance coverage on All-on High setting
- Wide and focus beam modes for large area coverage or narrow area working near others
- Removable rechargeable battery (Cat. No. 29025) with LED gauge car replaced with a spare to extend run time
- Headlamp can mount onto magnetic battery for use as a work light
- Headlamp pivots to allow use in different lighting angles
- Drop and ingress protection tested for use in outdoor and demanding jobsite environments
- Marker/Pencil holder included for quick and convenient access to mark tools

[BUY NOW](#)

[FIND RETAILER](#)

[PRODUCT MEDIA](#)

[SPECIFICATIONS](#)

[WARNINGS](#)

[REPLACEMENT PARTS](#)

[ACCESSORIES](#)

[RELATED ITEMS](#)

[REVIEWS](#)

### DOWNLOADS

- [Brochure](#)
- [Instructions](#)
- [Safety Data Sheet](#)

### IMAGES

**High-Res JPG:** [khh56308\\_photo.jpg](#)

**PNG:** [khh56308.png](#)

Klein Tools Rechargeable Hard Hat Wide-Beam Headlamp and modular battery attaches directly onto Klein Hard Hats and Safety Helmets via Klein mounts; Offering up to 770 lumens of bright light, this unique headlamp features tilt adjustment and easy mounting to magnetic battery for use as worklight for added versatility.

### Specifications

Type:	Rechargeable Wide-Beam Headlamp with Hard Hat Mount	Battery Life:	Center High: 8 hr; Center Low: 12 hr; All On High: 5 hr; All On Med: 7 hr; All On Low: 10 hr
Application:	Headlamp and Worklight	Batteries:	Lithium-Ion
Special Features:	Wide LED Array, Tilt Adjustment, Magnet	Temperature Range:	Operating Temperature: -4° to 122°F (-20° to 50°C); Charging Temperature: 32° to 113°F (0° to 45°C); Storage Temperature: -4° to 122°F (-20° to 50°C)



Products

Where to Buy

Media Center

Support

About Klein

Careers

Overall Height:	2.02" (5.1 cm)	Standard:	NR Can, REACH, RoHS, CEC/DOE
Overall Width:	1.84" (4.7 cm)	Included:	Rechargeable Battery
Material:	ABS	Weight:	1.9 oz (54 g)
Bulb Type:	LED	UPC:	092644563096
Lumens:	Center High: 400; Center Low: 150; All-On High: 770; All-On Med: 540; All-On Low: 270		

Additional Information

WARRANTY

COMPLIANCE

WARNINGS

- See instructions for a list of warnings.

REPLACEMENT PARTS



29025  
 Modular Battery for Klein Tools  
 Cat. No. 60155 Hard Hat  
 Cooling Fan

★★★★★ 1.5 (2)

ACCESSORIES



Products

Where to Buy

Media Center

Support

About Klein

Careers



56412 Rechargeable LED Flashlight with Worklight

★★★★★ 4.1 (7)



56403 Rechargeable Personal Work Light

★★★★★ 4.6 (21)



AEPJS3 Bluetooth® Jobsite Speaker with Magnet and Hook

★★★★★ 4.2 (14)

RELATED ITEMS



56308 Wide-Beam Headlamp with Strap

★★★★★ 5.0 (4)



56062 Rechargeable Headlamp and Work Light, 300 Lumens All-Day Runtime

★★★★★ 2.8 (5)



60470 Professional Full-Frame Gasket Safety Glasses, Clear Lens

★★★★★ 4.6 (5)



60345 Hard Hat, Premium KARBN™ Pattern, Non-Vented Full Brim, Class E

★★★★★ 5.0 (1)



60626 Hard Hat, Premium KARBN™ Pattern, Vented Full Brim, Class C

★★★★★ 4.5 (2)

★★★★★ 5.0 | 1 Review

1 out of 1 (100%) reviewers recommend this product

Search topics and reviews



Reviews

Write a review

Rating Snapshot Select a row below to filter reviews.

5 ★	1
4 ★	0
3 ★	0
2 ★	0
1 ★	0

Average Customer Ratings

Overall	★★★★★	5.0
Quality of Product	★★★★★	5.0
Value of Product	★★★★★	5.0

Beekeeper

non, TX  
s 2  
Vote 1  
Age 35 to 44  
Gender Male

★★★★★ · a month ago  
Plenty of light to work with in any space  
A friend has this and I am getting one next week when I get paid  
Received an incentive for this review No  
Recommends this product ✓ Yes

Quality of Product  
Value of Product

Products

Where to Buy

Media Center



Support

About Klein

Careers

**Products**

- New Products
- By Category
- By Industry
- Most Popular

**Where to Buy**

- Distributor Locator
- Online Retailers
- Klein Gear

**Media Center**

- Blog
- Interactive / PDF Catalogs
- Videos
- Industry Links

**Support**

- Warranty
- Contact Us
- Distributor Locator
- Partner Support
- Replacement Parts
- Search
- Product Registration
- Product Recalls
- Battery Tools
- Warranty/Repair

**About Klein**

- News
- Companies
- Our Mission
- American Manufacturing
- History
- Events
- Klein Leadership
- Transparency & Coverage

**Careers**


- Careers
- Grads / Internships

**International**

- Australia
- Brazil
- Germany
- Ireland
- Korea
- Mexico
- New Zealand
- United Kingdom



**Interactive Catalog**



[Privacy Policy](#) [Terms & Conditions](#) [Accessibility](#) [Contact Us](#)

©2024 Klein Tools, Inc. • All Rights Reserved