

# P | Cabling

## Data sheet

### FO extension set for module and keystone surface mounted housing

Page 1/5

P/N


130861-MSK-E

EAN 4250184133490


2024/08/19

Version: T

## Illustrations



Dimensional drawing



See enlarged drawings at the end of document

## Product specification

- fiber optic extension set for Modul and Keystone surface-mount housings
- included in delivery: splice tray with crimp splice holder for 12 splices, cable ties, Kevlar bracket and fastening screws
- suitable for all sizes
- max. number for 3, 4 and 6 port housings: 1 extension set, for 8 and 12 port housings: 2 extension sets, for 24 port housings: 3 extension sets

# P | Cabling

## Data sheet

Page 2/5

## FO extension set for module and keystone surface mounted housing

P/N

130861-MSK-E

EAN 4250184133490

2024/08/19

Version: T

### Technical Data

#### General Data

Design	Extension set
Mounting style	Accessories
Color	metallike
Dimensions	
Dimension (L x W x H)	88.5 mm x 77.6 mm x 7.1 mm
Dimension (L x W x H)	3.484 in. x 3.055 in. x 0.28 in.

#### Materials and material properties

Halogen free	yes
RoHS	compliant

#### Classifications

ETIM 7.0	EC002328
ETIM 8.0	EC002328
ETIM 9.0	EC002328

#### Packing details

Type of packaging	1 pc(s) / plastic bag
Packaging unit - Weight (gram)	108 g
Packaging unit - Weight (pound)	0.24 lb
Packaging dimension	160 mm x 100 mm x 380 mm
Packaging dimension	6.299 in. x 3.937 in. x 14.961 in.

#### Application note

This product is a standard product of METZ CONNECT. METZ CONNECT is not aware of the specific intended use of the goods by the Customer or any customers of the Customer. The Customer guarantees that it has fully and sufficiently tested the use of the goods and any product modifications, product changes or product enhancements with regard to the specific intended use in accordance with the state of the art or in any other way. At METZ CONNECT's request, the Customer shall submit and make available meaningful evidence (e.g. test and laboratory protocols, certifications, etc.).



# P | Cabling

Data sheet

Page 3/5

## FO extension set for module and keystone surface mounted housing

P/N

130861-MSK-E

EAN 4250184133490

2024/08/19

Version: T

### Accessories

P/N	Designation
15090301-I	OpDAT splice protection cover for 12 crimp splices
15090302-I	OpDAT splice protection cover for 6 shrink splices

# P | Cabling

Data sheet

Page 4/5

## FO extension set for module and keystone surface mounted housing

P/N

130861-MSK-E

EAN 4250184133490

2024/08/19

Version: T

### Accessories from

P/N	Designation
130861-0302-E	Modul surface mount housing 3 port pure white, unequipped
130861-0302KE	Keystone surface mount housing 3 port pure white, unequipped
130861-0402-E	Modul surface mount housing 4 port pure white, unequipped
130861-0402KE	Keystone surface mount housing 4 port pure white, unequipped
130861-0602-E	Modul surface mount housing 6 port pure white, unequipped
130861-0602KE	Keystone surface mount housing 6 port pure white, unequipped
130861-0802-E	Modul surface mount housing 8 port pure white, unequipped
130861-0802KE	Keystone surface mount housing 8 port pure white, unequipped
130861-0802KE85	AP Patchfeld unbestückt für 8xRJ45 RAL 9010 Keystone AP-Geh 8 Port ZATEC
130861-1202-E	Modul surface mount housing 12 port pure white, unequipped
130861-1202KE	Keystone surface mount housing 12 port pure white, unequipped
130861-1602-E	Modul surface mount housing 16 port pure white, unequipped
130861-1602KE	Keystone surface mount housing 16 port pure white, unequipped
130861-2402-E	Modul surface mount housing 2x12 port pure white, unequipped
130861-2402KE	Keystone surface mount housing 2x12 port pure white, unequipped

# P | Cabling

Data sheet

Page 5/5

## FO extension set for module and keystone surface mounted housing

P/N

130861-MSK-E

EAN 4250184133490

2024/08/19

Version: T

### Illustrations

Dimensional drawing

