



(<https://corstat.com/>)

Standard Component Handling

Please allow 1-2 weeks for production. No tooling – any quantity.



(tel: +17
63-527-
2090)

CP kitting trays - All sizes

- Conductive styrene
- Organizes components
- Permanent properties for a low cost with no tooling

Call For Quote: 763-537-2090

CCI P/N	DESCRIPTION
1230-5	9-1/4 X 7-3/8 X 1-1/8"
1230-10	9-1/4 X 7-3/8 X 1-1/8"
13025	9-1/4 X 7-1/4 X 1-3/4"
13030	10-1/2 X 8-3/4 X 1-1/2"
13035	13-1/4 x 13-1/4 x 1-3/16"
13040	14 X 10 X 1-3/4"
13045	18-3/8 x 16-3/8
13050	14 X 10 X 1-3/4"
13055	10-1/2 X 8-3/4 X 1-3/16"
13060	16-1/4 X 10-1/2 X 2"
13080	14-3/8 X 10-1/8 X 1-7/8
13090	8-1/4 X 6-1/4 X 1-5/8
2015CT	Cond. Cafeteria Tray
13026	D/C COVER FOR 13025
13031	D/C COVER FOR 13030 & 13055
13036	D/C COVER FOR 13035
13041	D/C COVER FOR 13040
13046	D/C COVER FOR 13045
13051	D/C COVER FOR 13050
13061	D/C COVER FOR 13060
13081	D/C COVER FOR 13080
13091	D/C COVER FOR 13090





TIPS

Organize Component Storage

Ask us about custom sizes



Kleanstat Injection Molded Boxes

- Kleanstat Static Dissipative case
- Same sizes as all injection molded boxes
- Ask CCI to design a custom thermoformed or tacki insert

Call For Quote: 763-537-2090

CCI P/N	DESCRIPTION
KS2020	2 x 2 x 1/4"
KS2525	2-9/16 x 2-9/16 x 1/2"
KS2820	2-7/8 x 2 x 1/2"
KS2820-75	2-7/8 x 2 x 3/4"

CCI P/N	DESCRIPTION
KS2820-100	2-7/8 x 2 x 1"
KS2535	3-1/2 x 2-9/16 x 1/2"
KS2535-75	3-1/2 x 2-9/16 x 3/4"
KS2535-1	3-1/2 x 2-9/16 x 1"
KS3545	4-5/8 x 3-1/2 x 1/2"
KS3545-625	4-5/8 x 3-1/2 x 5/8"
KS3545-75	4-5/8 x 3-1/2 x 3/4"
KS4545-50	4-9/16 x 4-9/16 x 1/2"
KS4545-125	4-9/16 x 4-9/16 x 1-1/4"
KS4545-200	4-9/16 x 4-9/16 x 2"
KS7035	7 x 3-1/2 x 1/2"




TIPS

Call CCI for pricing at any quantity. Ask about interior options

Pick from antistatic or permanent foams

CCI will design custom thermoformed inserts for one or multiple components





Tacki Pak

- Static safe retention of fragile components
- Durable case with Tacki retention bottom
- One package fits many component designs
- IPA cleanable

Call For Quote: 763-537-2090

CCI P/N	DESCRIPTION
TP2020	2 x 2 1/4"
TP2525	2-9/16 X 2-9/16 X 1/2"
TP2535	2-9/16 X 3-1/2 X 1/2"
TP3545	3-1/2 X 4-5/8 X 1/2"





TIPS

Permanent ESD properties

Reusable and cleanable

Choose a “tack level” – I, II, III to match your need



- No touch handling system for components with fragile leads
- Corstat® shielding, dissipative plastic tray and cover with dissipative adhesive
- Pick up, place and release component all with no hands touching device

Call For Quote: 763-537-2090

CCI P/N	DESCRIPTION
SM5025	2-3/4 X 2-3/4 X 15/16"
SM5045	5-3/4 X 2-3/4 X 15/16"
SM5055	5-3/4 X 5-3/4 X 15/16"
SM5060	14-3/4 X 5-3/4 X 15/16"
SM5025P	1 Dissipative tray & cover
SM5045P	2 Dissipative tray & cover
SM5055P	4 Dissipative tray & cover
SM5060P	10 Dissipative tray & cover



TIPS

Choose from 1 pack to 10 packs. Call CCI for pricing in any quantity

Eliminate lead damage

One package fits many sizes with no tooling





Pedestal pak

- CCI's Tacki Pak technology on a thermoformed pedestal
- Fits fragile leaded hybrids and difficult to handle components
- Durable conductive injection molded case with foam top pad

Call For Quote: 763-537-2090



CCI P/N	DESCRIPTION
PTP2525-200	2-9/16 X 2-9/16 X 1/2" Box w/.20 dia Ped.
PTP2525-375	2-9/16 X 2-9/16 X 1/2" Box w/.375 dia Ped.
PTP2525-500	2-9/16 X 2-9/16 X 1/2" Box w/.50 dia Ped.
PTP2525-750	2-9/16 X 2-9/16 X 1/2" Box w/.75 dia Ped.
PTP3545-750	4-5/8 X 3-1/2 X 1/2" Box w/.75 dia Ped.



- Choose “tacki level” and pedestal size to match your component
- ESD safe Tacki surface to retain component without tooling costs
- Avoid touching and damaging fragile leads in storage and handling





Corstat drawer cabinet

- Organize CCI kitting trays
- Static shielding Corstat® construction
- Available in CFP- conductive fluted plastic

Call For Quote: 763-537-2090



CCI P/N	DESCRIPTION
DC1230	10 X 7-5/8 X 7-7/8"
DC1231	10 X 7-5/8 X 7-7/8"
DC1330	11-3/8 X 9 X 9-1/4"
DC1340	15-1/4 x 10-3/4 x 11-1/4
DC1350	15-1/4 x 10-3/4 x 11-1/4



- Customize to fit your system
- Choose number of drawers and kitting tray option
- Consult CCI for pricing and design assistance



Terms and Conditions (/terms-and-conditions-cage-code/) | Privacy Policy (/privacy-policy-2/) | Contact CCI
(https://corstat.com/map/) | ROHS Certificate (/rohs-and-reach-certificate/) | Returns & Refunds
(https://corstat.com/refund_returns/)
Proudly manufactured in the United States
Proud member of the Static Discharge Association



www.w.ceb.ook.com
www.w.y.out.ube.com
www.w.li.nke.din.ace

com .co /co
fCo n/u inmp
ndu ser/ any/
ctiv Con con
eCo duct duct
ntai ive ive-
ner Con cont
slnc tain aine
/) ers) rs-
inc)

