


E-SCREWDRIVER speedE® ELECTRIC





speed

MADE IN GERMANY



















- Protects your material Electric fastening with a protective function to prevent damage to materials (max. 0.4 Nm = 3.5 in/lbs.)
- Increases your control Fixing by hand with full sensitivity
- Increases your efficiency Electronic ratchet for rapid fastening without any re-gripping
- Increases your efficiency 100% compatible with the Wiha slimLine blade system
- Maximum freedom of choice Open system with a rechargeable standard battery
- Offers you full protection slimLine blades tested at 10,000 V AC & approved for 1,000 V AC




E-SCREWDRIVER speedE® ELECTRIC

Patent Pending




LED Light glows after releasing the switch, blinks when battery is low



Handle special fiber glass reinforced

Lithium Battery rechargeable with integrated and overload protection (Replaceable 18500 Lithium Battery w/Chip)

Axial bearing to prevent gear & motor from being damaged during tightening & dropping



Long life motor specially optimized for the application

Shock absorbing silicone casting compound to hermetically seal the critical components against Environmental influences (Dirt, Dust, Liquids - IP44)







E-SCREWDRIVER speedE[®] ELECTRIC

13 Piece Set



• **Storage Box** L-Boxx mini storage solution for tradesmen and service professional that are always on the move. Perfect for holding the speedE screwdriver and all the speedE accessories.



• **speedE Handle** electric fastening with protective functions to prevent damage to materials. One speed rotation for maximum of 0.4 Nm torque to assist with screw fastening.



- SlimLine Blades 1000 Volt Insulated SlimLine blades, 33% narrower insulation diameter then standard insulated tools.
 - Slotted 3.5, 5.5mm
 - **Phillips** #1, #2
 - **O** Square #1, #2
 - Terminal Xeno #1, #2



- Adapter Plug 110 Volt adapter wall plug included. Easy to use and practical for traveling.
- **Battery Charger & Batteries** Li-lon battery charges off USB power source. The charger level indicator will light up red when batteries are charging and then green when the batteries are fully charged.



E-SCREWDRIVER speedE® ELECTRIC

speedE that works for you _



speedE Electric 13 Piece Set



32480

13 Pc. speedE Electric Screwdriver With SlimLine Blades

Certified to EN ISO, BS EN, ASME. Set includes speedE electric 0.4 Nm handle,

8 Insulated SlimLine blades, 2 Li-Ion rechargeable batteries & wall plug adapter/charger.

Item	speedE Screwdriver: Handle Range 0.4 Nm	
No.	Insulated SlimLine Blades Include:	
32480	SlimLine Slotted: 3.5, 5.5mm	lbs.
	SlimLine Phillips: #1, #2	2.14
	SlimLine Square: #1, #2	List
	SlimLine Terminal Xeno SI/Ph: #1, #2	\$249.96

1 Year Warranty

Within 30 days of purchase register your speedE at:

USA / MEXICO / SOUTH AMERICA www.wihatools.com/register

CANADA www.wihatools.ca/register



Wiha Tools, Ltd. 1348 Dundas Circle Monricello, MN 55362

Tel 800.494.6104 Fax 763.295.6598 Cservice@wihatools.com

www.wihatools.com