


Push-in type jumper bar; insulated; 5-way; Nominal current 41 A

Item no.	2006-405	GTIN / EAN	4050143701433
Content	1 piece	Order unit	piece
Order quantity	25 piece	Increase in order quantity	(25, 50, 75, 100, ...)
Customer item no.		Customs Tariff no.	8536690090
Customs duty for the country of origin	DE	Available	-
List price		Net price	On request
Availability	On request		



Note: Some items may not be available from your local WAGO company.
Please note that the quantities ordered in the shopping cart are rounded up to the PU (SPU).

RoHS ✓
Compliant



Article details	Approvals	Downloads/Certificates																																							
Description	Push-in type jumper bar; insulated; 5-way; Nominal current 41 A																																								
Remarks																																									
Item properties	Miscellaneous <table><tr><th>Name</th><th>Value</th><th>Unit</th></tr><tr><td>Rated current (I_N x I_{th}) [A]</td><td>33</td><td>A</td></tr><tr><td>Width</td><td>35.3 mm / 1.39 in</td><td></td></tr><tr><td>Height</td><td>19 mm / 0.748 in</td><td></td></tr><tr><td>Depth</td><td>4.1 mm / 0.161 in</td><td></td></tr><tr><td>Color</td><td>light gray</td><td></td></tr><tr><td>Fire load [MJ]</td><td>0.02</td><td>MJ</td></tr><tr><td>Weight [g]</td><td>5.58</td><td>g</td></tr><tr><td>[mm]</td><td>35.3</td><td>mm</td></tr><tr><td>Product Family</td><td>TOPJOB® S</td><td></td></tr><tr><td>Main product function</td><td>Jumper</td><td></td></tr><tr><td>Auxiliary product function</td><td>Push-in type jumper bar</td><td></td></tr><tr><td>Product type</td><td>Accessories</td><td></td></tr></table>		Name	Value	Unit	Rated current (I _N x I _{th}) [A]	33	A	Width	35.3 mm / 1.39 in		Height	19 mm / 0.748 in		Depth	4.1 mm / 0.161 in		Color	light gray		Fire load [MJ]	0.02	MJ	Weight [g]	5.58	g	[mm]	35.3	mm	Product Family	TOPJOB® S		Main product function	Jumper		Auxiliary product function	Push-in type jumper bar		Product type	Accessories	
Name	Value	Unit																																							
Rated current (I _N x I _{th}) [A]	33	A																																							
Width	35.3 mm / 1.39 in																																								
Height	19 mm / 0.748 in																																								
Depth	4.1 mm / 0.161 in																																								
Color	light gray																																								
Fire load [MJ]	0.02	MJ																																							
Weight [g]	5.58	g																																							
[mm]	35.3	mm																																							
Product Family	TOPJOB® S																																								
Main product function	Jumper																																								
Auxiliary product function	Push-in type jumper bar																																								
Product type	Accessories																																								