

UCS SB M2,5X20 - Distance bolts



1494990

<https://www.phoenixcontact.com/pc/products/1494990>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacer bolt for fixing the PCB to the heatsink, wrench size: AF5, length: 20 mm, material: steel, surface: galvanized



Commercial data

Item number	1494990
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	ACFCAZ
GTIN	4063151943370
Weight per piece (including packing)	66.8 g
Weight per piece (excluding packing)	66.8 g
Customs tariff number	73181552
Country of origin	CN

UCS SB M2,5X20 - Distance bolts



1494990

<https://www.phoenixcontact.com/pc/products/1494990>

Technical data

Notes

Assembly note	Vibration-resistant due to self-locking male thread.
General	Please observe the application note in the download area.
Recommendation	Further information and detailed dimensions are available in the download area.

Product properties

Product type	Mounting material
Housing type	Universal housings
Housing series	UCS
Ventilation openings present	no

Dimensions

Dimensions	M2.5 x 7 mm
	x 20 mm (Distance between heatsink and PCB)
	5 mm (Wrench size)
	M3 x 3.55 mm

Material specifications

Color	silver-colored
Housing material	Steel
Surface characteristics	galvanized
	galvanized

Mounting

Mounting type	Screw thread
Tightening torque / speed	SW5: 0.8 - 1 Nm / 500 - 1000 rpm

Packaging specifications

Type of packaging	PE bag
-------------------	--------

UCS SB M2,5X20 - Distance bolts

1494990

<https://www.phoenixcontact.com/pc/products/1494990>



Classifications

ECLASS

ECLASS-13.0	27190605
-------------	----------

ETIM

ETIM 9.0	EC002779
----------	----------

UCS SB M2,5X20 - Distance bolts

1494990

<https://www.phoenixcontact.com/pc/products/1494990>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com