

Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

A0335015 Faceplates and Panels - FiberExpress Splice Tray 8 inches



For more Information
please call

1-800-Belden1

General Description:

FiberExpress 8 inches Splice Tray

Usage (Overall)

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers
Related Parts:	FiberExpress Rack Mount And Wall Mount Patch Panels

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	Up to 24 Splices
----------------	------------------

Dimensions

Dimensions:

Height (mm)	Width (mm)	Length (mm)
17.780	119.380	203.200

Materials

Materials:

Description	Material	Color
Splice Tray	Plastic - UL94V-0	White

Weight

Weight:	0.113 kg
---------	----------

Packaging

Packaging:	Individually packaged in a plastic bag, Shipped in cardboard box (25/box)
------------	---

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +80°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For additional information about this product refer visit our web site at <http://www.belden.com>.

Product Family

Part Numbers:

Description	Item Number
FiberExpress Splice Tray 8 inches	A0335015
FiberExpress Splice Tray 12 inches	A0316446

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
A0335015	1 EA	0.557 LB			TRAY:ORGANIZER 8IN.

Revision Number: 0 Revision Date: 05-11-2010

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.