

PART NUMBER	SIZE	POWER RATING	TOLERANCE
SAFC-CAPKIT	1808 - 2220		±5% - ±10%

SERIES DATASHEET

[SAFC Series Datasheet](#)

NEED A RESTOCK?

1. Scan the QR Code
or visit <https://venkel.com/kit-refill>
2. Enter the parts that need to be restocked
3. Wait for your parts to come!



PART NUMBERS

PART	DESCRIPTION
SAFC1808COG502-180JNE	Safety Cap,1808,COG,X1/Y2,18pF,±5%
SAFC1808COG502-330JNE	Safety Cap,1808,COG,X1/Y2,33pF,±5%
SAFC1808X7R202-331KNE	Safety Cap,1808,X7R,X2,330pF,±10%
SAFC1808X7R202-471KNE	Safety Cap,1808,X7R,X2,470pF,±10%
SAFC1808X7R502-471KNE	Safety Cap,1808,X7R,X1/Y2,470pF,±10%
SAFC1808X7R502-681KNE	Safety Cap,1808,X7R,X1/Y2,680pF,±10%
SAFC1808X7R202-102KNE	Safety Cap,1808,X7R,X2,1000pF,±10%
SAFC1808X7R502-102KNE	Safety Cap,1808,X7R,X1/Y2,1000pF,±10%
SAFC1808X7R202-152KNE	Safety Cap,1808,X7R,X2,1500pF,±10%
SAFC1812X7R202-222KNE	Safety Cap,1812,X7R,X2,2200pF,±10%
SAFC1812X7R202-472KNE	Safety Cap,1812,X7R,X2,4700pF,±10%
SAFC2211X7R502-471KNE	Safety Cap,2211,X7R,X1/Y2,470pF,±10%
SAFC2211X7R502-681KNE	Safety Cap,2211,X7R,X1/Y2,680pF,±10%
SAFC2211X7R502-102KNE	Safety Cap,2211,X7R,X1/Y2,1000pF,±10%
SAFC2211X7R502-222KNE	Safety Cap,2211,X7R,X1/Y2,2200pF,±10%
SAFC2220X7R502-102KNE	Safety Cap,2220,X7R,X1/Y2,1000pF,±10%
SAFC2220X7R502-222KNE	Safety Cap,2220,X7R,X1/Y2,2200pF,±10%
SAFC2220X7R502-472KNE	Safety Cap,2220,X7R,X1/Y2,4700pF,±10%

ENVIRONMENTAL INFORMATION

 RoHS Status 10 of 10 Compliant	 REACH Status Compliant	 Halogen Status Halogen Free	 Conflict Mineral Status Conflict Mineral Free
--	--	--	---