


Customer No.:	No.:1
---------------	-------

P2



	P/N	COLOUR
10	AC - 12 - 192xx	Black
11	AC - 1920 - xx - BIJ	Blue
12	AC - 1920 - xx - R0	Red
13	AC - 1920 - xx - GN	Green
	AC - 1920 - xx - OR	Orange
	AC - 1920 - xx - WH	White
	AC - 1920 - xx - YE	Yellow

⚠ MARKING: (UL) SJT 3/C 12AWG(3.31MM²) VW-1 105°C 300V E204978


⚠ C(UL) SJT 3/C 3.31MM²(12AWG) FT2 105°C 300V E204978 MSL-VN-

29

PACKING A: $\leq$ IFT

PACKING B: ≤ 2 FT

PACKING C: >2FT



119120B2F12A(FP212-00)

P1

P2

BLACK L _____ L
WHITE N _____ N
GREEN E _____ E

 P1,P2: U_{us} E210037-VN

* NOTE: All relevant materials are complied with RoHS directive .
THE MARKING IS PROTRUDING LETTERING MOULD

3	UL SJT 12AWG x 3C, OD 11.0mm, JACKET BLACK, DRAWING No.EPSJT011203C-158	H5TC41-0304K09	L-20mm	M304
2	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304		M304
	BRACKET: YST-038	A1QC79-0767K09	1Set	M767
	TERMINAL: 97607BS-1	A1QB35-0257	1	M257
	TERMINAL: 97606BS-1	A1QB34-0257	2	M257
1	MOLDED PVC 35P, COLOR BLACK	H1BC02-0304	1	M304
	BRACKET: YST-037	A1QC36-0767K09	1Set	M767
	TERMINAL: 98739ABS-0	A1QB33-0257	3	M257
No.	DESCRIPTION		Q'TY	Supplier

12	REV.12	2025.06.16	MODIFY GUEST NUMBER TABLE	13	REV.13	2025.06.25	MODIFY ITEM TABLE
11	REV.11	2024.09.29	MODIFY THE CONTENT OF THE TABLE AND MOLDED SIZE				
9	REV.9	2024.07.17	MODIFY ITEM NO AND PACKING	10	REV.10	2024.07.29	ADD P/N
7	REV.7	2023.05.31	MODIFY P2 MOLDED LOGO	8	REV.8	2023.06.06	MODIFY P2 MOLDED LOGO
5	REV.5	2017.07.20	MODIFY CABLE	6	REV.6	2021.11.15	MODIFY MARKING
3	REV.3	2015.01.29	MODIFY MOLDED	4	REV.4	2015.10.12	MODIFY MOLDED
1	REV.1	2012.10.19	MODIFY MOLDED	2	REV.2	2012.10.30	MODIFY PACKING

NOTE: Cable Length Unless Otherwise Spec. Tolerances: Under 6FT $\pm 25\text{mm}$; Another $\pm 50\text{mm}$

APPROVED

1 CHECKED

DESINGER

DRAWING

DATE _____

HU

IM

WFI

25/JUN/25

ITEM NO.

AC-12-192XX & AC-1920-XX-XX

Cable Length	
Unless Other Spec.	
Tolerances:	
0 ~200mm	±10mm
201~1000mm	±20mm
1001 ~1500mm	±25mm
1501~2100mm	±30mm
2100mm↑	±40mm

UNIT:mm	
---------	---