



Figure similar

MAINS CHOKE F.FU; PHASES:3; UN1(V):480; ITHMAX 1(A) /
F1(HZ):400 /60; I LN (A):360; UK(%):2; LN(MH):0,0352;
TA/ISOKL:40 /H; IP00; TYPE OF TERMINALS:FLAT-TYPE
TERMINAL; EN 61558-2-20 >UL/CSA-RECOGNIZED< >CHOKE<

General technical data		
product designation		Netzdrossel f. FU
phase number		3
type of voltage		AC
operating voltage rated value	V	400, 480
operating frequency rated value	Hz	50 ... 60
• — operational current at AC rated value — current at AC maximum	A	360
	A	400
inductivity rated value	H	3.5E-5
relative inductive drop in voltage for rated value of the current, voltage and frequency	%	2
power loss [W] of the coil	W	172
power loss [W] of the iron core	W	87
Mechanical data		
type of electrical connection for main current circuit		flat connector
width	m	0.27
height	m	0.248
depth	m	0.208
Ambient conditions		
thermal class according to IEC 60085		H
ambient temperature rated value	°C	40
protection class IP		IP00
Certificates/ approvals		
General Product Approval	other	



[Confirmation](#)

Further information	
Siemens has decided to exit the Russian market (see here). https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business	
Siemens is working on the renewal of the current EAC certificates. Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).	
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875	
Information- and Downloadcenter (Catalogs, Brochures,...)	

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4EU2752-8UA00-0AA0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU2752-8UA00-0AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EU2752-8UA00-0AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU2752-8UA00-0AA0&lang=en

last modified:

2/12/2021 