





SERPAC I602HL

Electronic Enclosures



4 Mounting Brackets included.
See Sheet 2 for dimensions.

Aluminum Panel Kits are available
as options, see sheets 3-5.
The aluminum panel options are:
Bottom Panel Kit p/n 73000B
Top Panel Kit p/n 73040T
Hinged Top Panel Kit p/n 73020TH

- UL listed to UL 508A 4/4X standard (UL file E519183).
- Material: UV stabilized Polycarbonate
Flammability V0, F1 rated material.
- Watertight enclosure meets or
exceed Nema 4 and or IP67.


PARTS INCLUDED		
P/N	Qty.	Description
I652HLT	1	I652 Hinge Latch Top
I600HLB	1	I600 Hinge Latch Bottom
8650	1	650 Perimeter O-ring
7011PCM	1	I-series latch modified (PC)
7011PC	1	I-series safety latch (PC)
8000	1	Purge valve O-ring
1355	4	Corner Mounting Bracket
6028	4	SS #10 X 5/8" Pan H/L Screw

SERPAC

Electronic Enclosures

I602HL Mounting Bracket Dimensions

TOP & LATCHES REMOVED
FOR CLARITY FROM ALL VIEWS




INCLUDED STANDARD
1355 FLANGE KIT



Parts Included in kit number 1355		
P/N	Qty.	Description
1355	4	Mounting Corner Bracket
6028	4	SS #10 X 5/8" PH Pan H/L Screw

OPTIONAL 1306 CORNER FEET KIT

Parts Included in kit number 1306		
P/N	Qty.	Description
1306	4	Mounting Corner Feet
6028	4	SS #10 X 5/8" PH Pan H/L Screw




7300T Aluminum Top Panel Kit for I602HL, I622HL, I632 and I652





Parts Included in kit number 7300T		
P/N	Qty.	Description
73040	1	Aluminum Top Panel
6029	4	SS #10 X 3/8" PH Pan HL Screw

73040 Aluminum Top Panel for I602HL, I622HL, I632 and I652




7300B Bottom Panel Kit for I602HL, I622HL, I632 and I652



Parts Included in kit number 7300B		
P/N	Qty.	Description
73000	1	Aluminum Bottom Panel
6029	9	SS #10 X 3/8" PH Pan HL Screw



73000 Aluminum Bottom Panel for I602HL, I622HL, I632 and I652



SERPAC

Electronic Enclosures

7300TH Aluminum Hinged Top Panel Kit
for I602HL, I622HL, I632 and I652



Parts Included in kit number 7300TH		
P/N	Qty.	Description
73020	1	Aluminum Hinged Top Panel
6029	2	SS #10 X 3/8" PH Pan HL Screw
6030	2	SS #10-32 X 3/8" Pan Combo Screw
6105	2	SS #10-32 X 1/8" Nut

73020 Aluminum Hinged Panel for I602HL, I622HL, I632 and I652

