



## Product Highlights

- Maximum Labels per Day: 750
- Maximum Label/Tape Width: 2 in
- Print Technology: Thermal Transfer
- Color Printing Capability: Single Color
- Print Resolution: 300 dpi
- Device Connectivity: PC connected, Stand-alone
- Software Package: Basic Design Suite



## Overview

Get the durability your work demands: military-grade shock resistance, below freezing operating temps and the widest range of data entry options. Kit includes a hard case.

- Design and print labels using a keypad or desktop software
- Work longer with an enhanced Gen3 Li-ION battery – print 4,500 labels on a full charge
- Easily import and export label files, lists and graphics to the printer through USB 2.0 port (Type A and B) or USB flash drive
- Print labels at 2" per second print speed
- Get added durability with a printer that is resistant to military-grade shocks (MIL-STD-810G) and 6-foot drops
- Operate your printer in 0°-115°F temperatures
- NOTICE: Brady North America is not authorized to ship this item via air or to Alaska or Hawaii. Please contact your local distributor.

## Specifications

Key Characteristics	Product Number
	UPC
	UOM
	Trade Name
	Brand Name
Dimensions	Dimensions
	Height
	Width
	Depth
	Display Size
	Weight
Material Characteristics	Color

Product Features	<a href="#"><u>Application</u></a>
	Shipped With Battery
	How Is Battery Shipped
	Battery mAh Rating
	Battery Weight
	Built-In Label Wizards
	<a href="#"><u>Connectivity Options</u></a>
	Cutter Type
	<a href="#"><u>Device Connectivity</u></a>
	Device Drop Test & Durability
	Display Type
	Keyboard Type
	Memory
	Number of Symbols
	On Screen Indicators
	Plug Type
	Power Supply Voltage
	Auto Shut-Off / Power Conserve
	<a href="#"><u>Recharge Time</u></a>
	Special Characters Quantity
	User Interface Type

Battery Type	
Printing Specifications	Barcode Symbologies - 2D
	Barcode Symbologies - Linear
	<a href="#">Calibration Required?</a>
	Color Printing Capability
	Font Sizes
	Font Styles
	<a href="#">Label Retention Feature</a>
	<a href="#">Maximum Labels per Day</a>
	<a href="#">Maximum Label/Tape Width</a>
	<a href="#">Minimum Label Length</a>
	Maximum Print Speed
	Maximum Printed Label Length
	Print Resolution
	Print Technology
Compatibility	<a href="#">Compatible Media</a>
	Label Material Types

	Materials Supported
	Custom Labels Available
	Maximum Print Width
	Phones & Tablets Supported
	Software Compatibility
	Languages Available
What's Included	Software Package
	Includes
	Model
	Warranty
Compliance	<a href="#">California Prop 65</a>
	REACH SVHC Status
	REACH Candidate List Date
	<a href="#">Country of Origin</a>
	<a href="#">ECCN (Export Commodity Control</a>
	<a href="#">HTS Code (Harmonized Tariff Sche</a>
	RoHS Compliance Status

UNSPSC

---