




REV	ECN	DESCRIPTION	DATE	MODIFIED
3		UPDATE TECHNICAL DATA	2019.04.23	
4		ADD NEW SPECIFICATIONS	2019.8.12	
5	R4118N	Correct drawing size	2020.2.21	



安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen
受控文件
2020年3月4日











HVPT 1 X XX

- A: CODING A 25: FOR 25mm² Shielded WIRE;OD=11.9±0.4mm
 B: CODING B 35: FOR 35mm² Shielded WIRE;OD=14.2±0.4mm
 C: CODING C 50: FOR 50mm² Shielded WIRE;OD=16.5±0.4mm
 D: CODING D 70: FOR 70mm² Shielded WIRE;OD=19.0±0.4mm
 E: CODING E
 F: CODING F
 G: CODING G
 N: CODING N


TECHNICAL DATA	
OPERATING TEMPERATURE	-40 ~ 125 °C
SHIELDING	YES
WATERPROOF(MATED CONDITION)	IP67&IP69K
AMBIENT TEMPERATURE	-40 ~ 70 °C

DIMENSIONS ANSI Y14.5M UNITS: MM Pro/E FILE	TOLERANCES .X ±0.5 .XX ±0.05 ANGLES ±0.5°	PROJECTION ENGR	TITLE		REV
			12-Aug-19	HVPT 1XXX PASS-THRU CABLE SEAL GLAND	
ORIGINAL	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN	CHKD		SIZE A3	DWG NO. C-HVPT1XXX
		APPD		CODE: 58982	SCALE: 1:2


C-HVPT1XXX



安费诺精密连接器(深圳)有限公司
Amphenol PCD Shenzhen
受控文件
2020年3月4日



RECOMMENDED LAYOUT FOR 2 INDIVIDUALS




RECOMMENDED LAYOUT FOR 3 INDIVIDUALS

SIZE	DWG NO.	C-HVPT1XXX		REV
A3				5
CODE: 58982		SCALE: 1:2	SHEET 2 OF 3	

受控文件

2020年3月4日

2020年3月4日



HVPT1F25	5	C310003642	1	SHELL
	4	C2000036633	1	OUT FERRUL
	3	HVPT1N	1	HOUSING
	2	C2700036043	1	SEAL
	1	C2200037253	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION
HVPT1F35	5	C310003643	1	SHELL
	4	C2000036632	1	OUT FERRUL
	3	HVPT1N	1	HOUSING
	2	C2700036042	1	SEAL
	1	C2200037252	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION
HVPT1F50	5	C310003644	1	SHELL
	4	C2000036631	1	OUT FERRUL
	3	HVPT1N	1	HOUSING
	2	C2700036041	1	SEAL
	1	C2200037251	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION
HVPT1F70	5	C310003645	1	SHELL
	4	C2000036630	1	OUT FERRUL
	3	HVPT1N	1	HOUSING
	2	C2700036044	1	SEAL
	1	C2200037254	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

HVPT1A25	5	C310003642	1	SHELL
	4	C2000036633	1	OUT FERRULE
	3	HVPT1A	1	HOUSING
	2	C2700036043	1	SEAL
	1	C2200037253	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION
HVPT1A35	5	C3100036431	1	SHELL
	4	C2000036632	1	OUT FERRULE
	3	HVPT1A	1	HOUSING
	2	C2700036042	1	SEAL
	1	C2200037252	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION
HVPT1A50	5	C310003644	1	SHELL
	4	C2000036631	1	OUT FERRULE
	3	HVPT1A	1	HOUSING
	2	C2700036041	1	SEAL
	1	C2200037251	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION
HVPT1A70	5	C310003645	1	SHELL
	4	C2000036630	1	OUT FERRULE
	3	HVPT1A	1	HOUSING
	2	C2700036044	1	SEAL
	1	C2200037254	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION
HVPT1B25	5	C310003642	1	SHELL
	4	C2000036633	1	OUT FERRULE
	3	HVPTB1	1	HOUSING
	2	C2700036043	1	SEAL
	1	C2200037253	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

HVPT1G25	5	C310003642	1	SHELL
	4	C2000036633	1	OUT FERRUL
	3	HVPT1N	1	HOUSING
	2	C2700036043	1	SEAL
	1	C2200037253	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

HVPT1G35	5	C310003643	1	SHELL
	4	C2000036632	1	OUT FERRUL
	3	HVPT1N	1	HOUSING
	2	C2700036042	1	SEAL
	1	C2200037252	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

ITEM	P/N	QTY	DESCRIPTION
HVPT1B35	5	C310003643	SHELL
	4	C2000036632	OUT FERRUL
	3	HVPTB1	HOUSING
	2	C2700036042	SEAL
	1	C2200037252	END CAP

	ITEM	P/N	QTY	DESCRIPTION
HVPT1B50	5	C310003644	1	SHELL
	4	C2000036631	1	OUT FERRUL
	3	HVPTB1	1	HOUSING
	2	C2700036041	1	SEAL
	1	C2200037251	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

	ITEM	R/N	QTY	DESCRIPTION
HVPT1B70	5	C310003645	1	SHELL
	4	C2000036630	1	OUT FERRUL
	3	HVPTB1	1	HOUSING
	2	C2700036044	1	SEAL
	1	C2200037254	1	END CAP
	ITEM	R/N	QTY	DESCRIPTION

ITEM	P/N	QTY	DESCRIPTION
HVPT1C35	5	C310003643	SHELL
	4	C2000036632	OUT FERRUL
	3	HVPT1C	BODY
	2	C2700036042	SEAL
	1	C2200037252	END CAP
	ITEM	P/N	QTY

ITEM	P/N	QTY	DESCRIPTION
HVPT1C50	5	C310003644	SHELL
	4	C2000036631	OUT FERRUL
	3	HVPT1C	HOUSING
	2	C2700036041	SEAL
	1	C2200037251	END CAP
ITEM	P/N	QTY	DESCRIPTION

HVPT1G50	5	C310003644	1	SHELL
	4	C2000036631	1	OUT FERRULE
	3	HVPT1N	1	HOUSING
	2	C2700036041	1	SEAL
	1	C2200037251	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

ITEM	P/N	QTY	DESCRIPTION	
HVPT1G70	5	C310003645	1	SHELL
	4	C2000036630	1	OUT FERRULE
	3	HVPT1N	1	HOUSING
	2	C2700036044	1	SEAL
	1	C2200037254	1	END CAP

HVPT1D35	5	C310003643	1	SHELL
	4	C2000036632	1	OUT FERRULE
	3	HVPT1D	1	HOUSING
	2	C2700036042	1	SEAL
	1	C2200037252	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

ITEM	P/N	QTY	DESCRIPTION
HVPT1N25	5	C310003642	SHELL
	4	C2000036633	OUT FERRULE
	3	HVPT1N	HOUSING
	2	C2700036043	SEAL
	1	C2200037253	END CAP
	ITEM	P/N	QTY

ITEM	P/N	QTY	DESCRIPTION
HVPT1N35	5	C310003643	SHELL
	4	C2000036632	OUT FERRUL
	3	HVPT1N	HOUSING
	2	C2700036042	SEAL
	1	C2200037252	END CAP
ITEM	P/N	QTY	DESCRIPTION

ITEM	P/N	QTY	DESCRIPTION
HVPT1N50	5	C310003644	1
	4	C2000036631	1
	3	HVPT1N	1
	2	C2700036041	1
	1	C2200037251	1
ITEM	P/N	QTY	DESCRIPTION

	ITEM	P/N	QTY	DESCRIPTION
HVPT1N70	5	C310003645	1	SHELL
	4	C2000036630	1	OUT FERRULE
	3	HVPT1N	1	HOUSING
	2	C2700036044	1	SEAL
	1	C2200037254	1	END CAP
	ITEM	P/N	QTY	DESCRIPTION

C-HVPT1XXX

211

3

SIZE
A3

DWG NC

C-HVPT1XXX

REVIEW 5

CODE: 589

SCALE 1:2

SHEFF

3 OF 3