

### P/N: VSS-20

#### Copyright

© 2014, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

#### Document identity

Publ. No.: VSS-20  
 Release: -  
 Commit: 14345  
 Language:  
 Modified: 2014-05-26  
 Formatted: 2014-05-27

#### Corporate Headquarters

FLIR Systems, Inc.  
 27700 SW Parkway Ave.  
 Wilsonville, OR 97070  
 USA  
 Telephone: +1-503-498-3547

#### Website

<http://www.flir.com>

#### Customer support

<http://support.flir.com>

#### Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to [exportquestions@flir.com](mailto:exportquestions@flir.com) with any questions.



Part No.	VSS-20
<b>General information</b>	
Short description	20 m (66') plumbing spool (no camera, need VSC25 or VSC28)
Compatible main unit	VS70
Integrated handset	No
Wireless capabilities	N/A
Compatible wireless handset	With optional VST
Compatible detachable cameras	VSC25 or VSC28
Warranty	2 years
<b>Camera specifications</b>	
Articulation	No
Diameter	N/A
Resolution	N/A
Probe length	20 m (66')
Focal length	N/A
Field of view	N/A
Imaging sensor	N/A
Video format	N/A
Brightness control	N/A
Lamp type	N/A
<b>Power system</b>	
Power requirements	N/A
<b>Environmental data</b>	
Operating temperature	-10 to 50°C (14-122°F)
Operating humidity	80% maximum
Storage temperature	-40 to 80°C (-40 to 176°F)
<b>Physical data</b>	
Weight	See shipping information
Dimensions (H x W x L)	See shipping information
Material	PC-ABS, rubber hand grip, nylon strap
Color	Gray, black



## 20 m (66') plumbing spool (no camera, need VSC25 or VSC28)

**P/N: VSS-20**

© 2014, FLIR Systems, Inc.

#VSS-20; r. -/14345;

<b>Shipping information</b>	
Packaging type	Brown box with shipping labels
Packaging contents	Brown box, hard case, spool
Packaging weight	4 kg
Packaging dimensions (H x W x L)	45 cm x 37 cm x 17 cm
Carton weight	9 kg
Carton dimensions (H x W x L)	46 cm x 32 cm x 40 cm
Carton quantity	2
EAN-13	7332558007792
UPC-12	793950406144
Country of origin	TW
Tariff code	9013909000
<b>Technical support</b>	
Website	<a href="http://support.flir.com">http://support.flir.com</a>
E-mail	<a href="mailto:T&amp;Msupport@flir.com">T&amp;Msupport@flir.com</a>
Phone	855-499-3662
Repairs	<a href="mailto:repair@flir.com">repair@flir.com</a>