




SERPAC

Electronic Enclosures


I342HL



2 Mounting Brackets included, see sheet 2 for dimensions and for optional mounting Corner Feet and Brackets.



Aluminum and Plastic Panel Kits are available as options, see sheets 3-6. The aluminum panel options are:
Bottom Panel Kit p/n 7200B
Top Panel Kit p/n 7200T
Hinged Top Panel Kit p/n 7200TH
The plastic panel option is:
Hinged Panel Kit p/n 7200HP



- UL listed to UL 508A 4/4X standard (UL file E519183).
- Material: UV stabilized Polycarbonate Flammability V0, F1 rated material.
- Watertight enclosure meets or exceeds Nema 4 and or IP67.


PARTS INCLUDED		
P/N	Qty.	Description
I352 HLT	1	I352 Hinged Latch Top
I340 HLB	1	I340 Hinge Latch Bottom
8350	1	350 Perimeter O-ring
7011PCM	1	I-series latch modified (PC)
7011PC	1	I-series safety latch (PC)
8000	1	Purge valve O-ring
1305	2	Mounting Bracket
6028	4	SS #10 X 5/8" Pan H/L

SERPAC I352/I342 Mounting Bracket Dimensions


Electronic Enclosures

TOP & LATCHES REMOVED
FOR CLARITY FROM ALL VIEWS

OPTIONAL 1356 POLE MOUNTING BRACKET KIT




Part included in Kit number 1305		
P/N	Qty.	Description
1305	2	Flange
6028	4	SS #10 X 5/8" Pan Combo H/L Screw



Part included in Kit number 1356		
P/N	Qty.	Description
1356	2	Pole Mounting Bracket
6028	4	SS #10 X 5/8" Pan Combo H/L Screw


OPTIONAL 1306 CORNER FEET KIT

Part included in Kit number 1306		
P/N	Qty.	Description
1306	4	Mounting Corner Foot
6028	4	SS #10 X 5/8" Pan Combo H/L Screw






OPTIONAL 1355 CORNER BRACKETS KIT

Part included in Kit number 1355		
P/N	Qty.	Description
1355	4	Mounting Corner Bracket
6028	4	SS #10 X 5/8" Pan Combo H/L Screw




7200T Aluminum Top Panel Kit for 352HL, 342HL, 352HS, 342HS, 352S and 342S



Part included in Kit number 7200T		
P/N	Qty.	Description
72040	1	Aluminum Top Panel
6029	4	SS #10 X 3/8" Pan HL Screw

72040 Aluminum Top Panel



352HL, 342HL, 352HS, 342HS, 352S and 342S



SERPAC

Electronic Enclosures

7200B Aluminum Bottom Panel Kit for
352HL, 342HL, 352HS, 342HS, 352S and 342S




Kit number
7200B



Part included in Kit number 7200B		
P/N	Qty.	Description
72000	1	Aluminum Bottom Panel
6029	4	SS #10 X 3/8" Pan HL Screw

72000 Aluminum Bottom Panel


352HL, 342HL, 352HS, 342HS, 352S and 342S





7200TH Aluminum Hinged Top Panel Kit for 352HL, 342HL, 352HS, 342HS, 352S and 342S





Part included in Kit number 7200TH		
P/N	Qty.	Description
72020	1	Aluminum Hinged Top Panel
6029	2	SS #10 X 3/8" Pan H/L Screw
6030	2	SS #10-32 X 3/8" PH-PN Combo Screw
6105	2	SS #10-32 Hex Nut Plain
6028	2	SS #10 X 5/8" Pan H/L Screw
1307	2	Hinge Pin
1308	1	Panel Hinge A
1309	1	Panel Hinge B



7200HP Plastic Hinged Top Panel Kit for 352HL, 342HL, 352HS, 342HS, 352S and 342S



**SECTION
A-A**





**SECTION
B-B**


Parts Included in kit number 7200HP		
P/N	Qty.	Description
72021	1	Plastic Hinged Top Panel
1310	1	Panel Hinge Left
1311	1	Panel Hinge Right
6028	4	SS #10 X 5/8" Pan H/L Screw

72021 Plastic Hinged Top Panel

352HL, 342HL, 352HS, 342HS, 352S and 342S



**SECTION
E-E**



**SECTION
F-F**