

Electronic Enclosures



PARTS INCLUDED


P/N	Qty.	Description
I652HLT	1	I652 Hinge Latch Top
I650HLB	1	I650 Hinge Latch Bottom
8650	1	650 Perimeter O-ring
7011PCM	1	I-Series Latch modified (PC)
7011PC	1	I-Series Safety Latch (PC)
8000	1	Purge Valve O-ring
1355	4	Corner Mounting Bracket
6028	9	SS #10 X 5/8" Pan H/L Screw

2009 Wright Ave. La Verne, CA 91750
Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com

SERPAC

I652HL Mounting Bracket Dimensions

Electronic Enclosures




INCLUDED (4)
1355 CORNER BRACKETS KIT

Parts Included in kit number 1355		
P/N	Qty.	Description
1355	4	Mounting Corner Bracket
6028	4	SS #10 X 5/8" Pan Combo H/L Screw

TOP & LATCHES REMOVED
FOR CLARITY FROM ALL VIEWS


OPTIONAL 1306 CORNER FEET KIT

Parts Included in kit number 1306		
P/N	Qty.	Description
1306	4	Mounting Corner Feet
6028	4	SS #10 X 5/8" Pan Combo H/L Screw




SERPAC
Electronic Enclosures

7300T Aluminum Top Panel Kit for
I602HL, I622HL, I632 and I652






Parts Included in kit number 7300T		
P/N	Qty.	Description
73040	1	Aluminum Top Panel
6029	4	SS #10 X 3/8" Pan HL Screw

73040 Aluminum Top Panel for I602HL, I622HL, I632 and I652




SERPAC
Electronic Enclosures

7300B Aluminum Bottom Panel Kit for
I602HL, I622HL, I632 and I652




Parts Included in kit number 7300B		
P/N	Qty.	Description
73000	1	Aluminum Bottom Panel
6029	9	SS #10 X 3/8" Pan HL Screw


73000 Aluminum Bottom Panel for I602HL, I622HL, I632 and I652



7300TH Aluminum Hinged Top Panel Kit for I602HL, I622HL, I632 and I652



Optional kit
pn 7300TH



Parts Included in kit number 7300TH		
P/N	Qty.	Description
73020	1	Hinged Top Aluminum Panel
6029	2	SS #10 X 3/8" Pan HL Screw
6030	2	SS #10 X 3/8" Pan Combo H/L Screw
6105	2	SS #10-32 X 1/8" Nut
6028	2	SS #10 X 5/8" PH HD H/L Screw
1307	2	Hinge Pin for Hinge Panel
1308	1	Hinge A for Hinge Panel
1309	1	Hinge B for Hinge Panel

73020 Aluminum Hinged Panel for I602HL, I622HL, I632 and I652

