

Stock No.: 9134687J0155

## FEATURES

- Unshielded
- Gold-plated, 50u"
- UL94V-0




## Product Description

*Compatible with 24-26AWG stranded or solid conductors.  
Suitable for cable jacket diameters up to  $\varnothing 8.00\text{mm}$  and conductor insulation diameters from  $\varnothing 0.96 - 1.02\text{mm}$ .*

## General Specifications

| Attribute                      | Value              |
|--------------------------------|--------------------|
| Voltage Rating                 | 250 V              |
| Current Rating                 | 2A Max             |
| Insulation Resistance          | 500M $\Omega$      |
| Contact Resistance             | <20m $\Omega$      |
| Cable-to-Plug tensile strength | 20LBs(89N) min.    |
| Durability                     | 1200 mating cycles |
| Operation Temp                 | -40°C -70°C        |
| Contact Plating                | Gold               |
| Length                         | 21.49mm            |

## Product Drawing



| BLADE:  | E | EB | Y | YB | Z | A | AE | AB |
|---------|---|----|---|----|---|---|----|----|
| Drawing |   |    |   |    |   |   |    |    |
| Mark    |   |    | ✓ |    |   |   |    |    |

| GOLD PLATING | 3Mu" | 3u" | 6u" | 15u" | 30u" | 50u" | CABLE TYPE | ROUND | FLAT |
|--------------|------|-----|-----|------|------|------|------------|-------|------|
| Mark         |      |     |     |      |      | ✓    | Mark       | ✓     |      |

Dimensions: Millimeters (Inches)

## Part Number Table

| Part Number  | Description                         |
|--------------|-------------------------------------|
| 9134687J0155 | Cat5/5E RJ45 Connectors Unshielded. |

Important Notice: This data sheet and its contents (the "Information") belong to the members of the EASE group of companies (the "Group") or are licensed to it. No license is granted for the use of it other than for information purposes in connection with the products to which it relates. No license of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate, but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. EASE is the registered trademark of Ease Electronics Co., Limited 2019.