

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Protective hose, spring steel wire with PVC coating, highly stranded

Image shows WP-SPIRAL PVC C 10 version

Key Commercial Data

Packing unit	1 M
Minimum order quantity	10 M
Weight per Piece (excluding packing)	142.0 g
Custom tariff number	39173200
Country of origin	Germany

Technical data

Dimensions

Inner diameter (f)	13.00 mm
Outside diameter	17.00 mm

Ambient conditions

Ambient temperature (operation)	-25 °C 80 °C		
Short-term temperature	100 °C		

General

Color	gray
Туре	Spring steel wire with soft PVC coating
Components	Free from silicone and cadmium
Material	PVC
Bending radius, static	13.00 mm

Standards and Regulations

Resistance to UV radiation	no		
Halogen-free	no		



Classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27430304

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001177
ETIM 5.0	EC001177

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	39121411

Approvals

Α	n	n	r	٦١	12	ıI۹	3

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approvals submitted

Approval details

VDE Zeichengenehmigung



Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G PP HF PG11 - 3240990



Cable gland made from PP with Pg thread, IP65 protection

Screw connection - WP-G PP HF M16 - 3240997



Cable gland made from PP with metric thread, IP65 protection

Screw connection - WP-GT PP HF PG11 - 3241004



Cable gland made from PP with Pg thread, rotatable, IP54 protection

Screw connection - WP-GT PP HF M20 - 3241012



Cable gland made from PP with metric thread, rotatable, IP54 protection

Mounting material



Accessories

Hose clamp - WP-BASE HF 17 - 3240969



Hose clamps

Protective hose fixing bracket - WP-BASE A M16 - 3241083



Fixing bracket for protective sleeves, fixed with two screws

Protective cap

Cable protection end sleeve - WP-SC HF 17 - 3241018



End sleeves as cable protection

Phoenix Contact 2016 © - all rights reserved http://www.phoenixcontact.com