#### 2.4mm Interface at a Glance

The 2.4mm connector was developed for use to 50 GHz. This connector series uses a thick outer wall to eliminate the fragility seen in SMA and 2.92mm connectors. The female socket is also strengthened to ensure reliable mating. The 2.4mm series mates with SMA, 3.5mm and 2.92mm connectors with adapters and can mate with the 1.85mm series without adapters.

### **Electrical Specifications**

Impedance	50Ω
Frequency	50 GHz
VSWR	1.03 + .005 f
Insertion Loss	.04 $\checkmark$ f
Shielding Effectiveness	≥ 100 dB
VSWR Insertion Loss	1.03 + .005 f .04 √ f

#### **Mechanical Specifications**


Mating Cycles	500
Recommended Torque	5 - 7 in - lbs
Inter-mate ability	1.85mm

#### **Environmental Specifications**


Temperature Rating	-65°C to +165°C			
Corrosion (Salt Spray)	MIL-STD-202, Method 101, Condition B			
Vibration	MIL-STD-202, Method 204, Condition D, 20 Gs			
Shock	MIL-STD-202, Method 213, Condition I, 100 Gs			
Thermal Shock	MIL-STD-202, Method 107. Cond. B, -65°C to +125°C			
Moisture Resistance	MIL-STD-202, Method 106, Less Step 7B			
Barometric Pressure (Altitude)	MIL-STD-202, Method 105, Condition C, 70k Ft.			

Note: Specifications, dimensions and images are typical for the series and may vary by part number


#### **Male Cable Connector**









#### **Female Bulkhead Cable Connector**




### Female Flange Mount Connector, 2 Hole (Accepts Ø.012" Pin)




## Female Flange Compression Mount Connector, 2 Hole



### Female Edge Launch Connector (.062" PCB Thickness)




### Male Sparkplug Connector (Accepts Ø.008" Pin)




### Feed-Thru Hermetic Seal




P/N	Α	В	С	øD	øE
066-15-000	.040″	.055″	.029″	.076″	.012″
066-15-001	.040″	.055″	.080″	.076″	.012″
066-15-002	.030″	.055″	.026″	.068″	.009″
066-15-003	.030″	.055″	.080″	.068″	.009″
066-15-004	.030″	.055″	.120″	.068″	.009″
066-15-005	.050″	.060″	.125″	.158″	.020″



#### 2.4mm Male to Male Adapter




## 2.4mm Female to Female Adapter







### 2.4mm Male to Female Adapter




## 2.4mm Male to 2.92mm Male Adapter




### 2.4mm Male to 2.92mm Female Adapter






#### 2.4mm Female to 2.92mm Female Adapter




### **Male Termination**





**P/N** SF8016-6304

## **Female Termination**



# 2.4MM NOTES