



4-Line BUS-Port ESD Protection - Flow Through Design






MARKING (example only)



Dot = pin 1 marking YY = type code (see table below) XX = date code

DESIGN SUPPORT TOOLS click logo to get started





FEATURES

- Compact LLP2510-10M package
- Low package height < 0.6 mm
- 4-line ESD protection
- Low leakage current I_R < 0.1 μA
- Low capacitance between I/O lines: 0.3 pF
- · Ideal for high speed data line like - HDMI, DisplayPort, eSATA - USB, 1394/firewire
 - Thunderbolt
- ESD immunity acc. IEC 61000-4-2 ± 15 kV contact discharge
 - ± 15 kV air discharge
- Soldering can be checked by standard vision inspection, no X-ray necessary
- e3 Sn
- · Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

Pb-free
63



ORDERING INFORMATION					
DEVICE NAME	ORDERING CODE	TAPED UNITS PER REEL (8 mm TAPE ON 7" REEL)	MINIMUM ORDER QUANTITY		
VBUS54GD-FBL	VBUS54GD-FBL-G3-08	3000	30 000		
VBUS54GD-FBL	VBUS54GD-FBL-G3-08	1 1	30 000		

PACKAGE DATA							
DEVICE NAME	PACKAGE NAME	TYPE CODE	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS	
VBUS54GD-FBL	LLP2510-10M	4G	3.9 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	260 °C/10 s at terminals	

ABSOLUTE MAXIMUM RATINGS VBUS54GD-FBL						
PARAMETER	TEST CONDITIONS	SYMBOL	VALUE	UNIT		
Peak pulse current	Acc. IEC 61000-4-5; $t_P = 8/20 \ \mu s$; single shot	I _{PPM}	3	A		
Peak pulse power Acc. IEC 61000-4-5; $t_P = 8/20 \ \mu s$; single shot P_{PP}		P _{PP}	45	W		
ESD immunity	Contact discharge acc. IEC 61000-4-2; 10 pulses	M	± 15	kV		
ESD minumity	Air discharge acc. IEC 61000-4-2; 10 pulses	V _{ESD}	± 15			
Operating temperature	Junction temperature	TJ	-40 to +125	°C		
Storage temperature		T _{STG}	-55 to +150	°C		



www.vishay.com

Vishay Semiconductors

PARAMETER	erwise specified) TEST CONDITIONS/REMARKS	SYMBOL	MIN.	TYP.	MAX.	UNIT
Protection paths	Number of lines which can be protected	N _{channel}	-	-	4	lines
Reverse stand-off voltage	Max. reverse working voltage	V _{RWM}	-	-	5.5	V
Reverse voltage	at I _B = 0.1 µA	V _B	5.5	-	-	V
Reverse current	at V _{RWM} = 5.5 V	I _R	-	0.02	0.1	μA
Reverse breakdown voltage	at I _R = 1 mA	V _{BR}	6.9	7.5	8.7	V
	at I _{PP} = 1 A	V _C	-	9.1	11	V
Reverse clamping voltage	at $I_{PP} = I_{PPM} = 3 A$	V _C	-	12	15	V
Forward alamping valtage	at I _{PP} = 1 A	V _F	-	2.1	2.4	V
Forward clamping voltage	at I _{PP} = 3 A	V _F	-	3.5	4.5	V
	Transmission line pulse (TLP), $t_p = 100 \text{ ns}$ $I_{TLP} = 8 \text{ A}$	V _{C-TLP}	-	15	-	V
Clamping voltage	Transmission line pulse (TLP), $t_p = 100 \text{ ns}$ $I_{TLP} = 16 \text{ A}$	V _{C-TLP}	-	21	-	V
Dynamic resistance	Transmission line pulse (TLP), $t_p = 100 \text{ ns}$	R _{DYN}	-	0.76	-	Ω
Canacitance	at $V_R = 0$ V; f = 1 MHz	0	-	0.6	0.75	pF
Capacitance	at V _R = 3.3 V; f = 1 MHz	C _D	-	0.65	0.75	pF
Capacitance between I/O lines	at V _B = 3.3 V; f = 1 MHz	C _{DD}	-	0.3	0.4	pF


APPLICATION NOTE


The **VBUS54GD-FBL** is a four-line ESD protection device with the characteristic of a Z-diode with a high ESD immunity and a very low capacitance which makes it usable for high frequency applications like USB2.0, USB3.0 or HDMI.

With the **VBUS54GD-FBL** four high speed data lines can be protected against transient voltage signals like ESD (electro static discharge). Connected to the data line (pin 1, 2 and pin 4, 5) and to ground (pin 3 and 8) negative transients will be clamped close below the ground level while positive transients will be clamped close above the 5.5 V working range. The clamping behavior of the **VBUS54GD-FBL** is bidirectional but asymmetrical (**BiAs**) and so it offers the best protection for applications running up to 5.5 V.

Pin configuration:

- Pin 3 and 8 are internally shorted and have to be connected to ground
- Pin 1, 2 and 4, 5 are the inputs for the data lines D_{1+} and D_{1-} and D_{2+} and D_{2-}
- Pin 6, 7 and 9, 10 are not connected internally





FLOW THROUGH DESIGN

Modern digital transmission lines can be clocked up to 480 Mbit/s (USB2.0) or 1.65 Gbit/s (HDMI).


At such high data rates the transmission lines like cables or the line traces on the PCBs have to be very homogeneous regarding their surge impedance. This requires well defined trace dimensions as trace width and distance which have to be calculated depending on the requested surge impedance (e.g. 50 Ω) and the PCB material and layer dimensions. Any device connected to the data lines - like ESD protection devices - have to be connected with minimal changes in these trace dimensions and distances.

With the package in the so called "Flow Through Design" this is possible. The lines are running straight along the PCB while the **VBUS54GD-FBL** is placed on top without any via or loops.


Rev.	1.2,	03-May-17
------	------	-----------



CONNECTION DIAGRAM EXAMPLE FOR THUNDERBOLT DATA PORT




CONNECTION DIAGRAM EXAMPLE FOR USB 3.0 DATA PORT




22789


CONNECTION DIAGRAM EXAMPLE FOR HDMI DATA PORT





TYPICAL CHARACTERISTICS (T_{amb} = 25 °C, unless otherwise specified)








Fig. 2 - 8/20 µs Peak Pulse Current Wave Form acc. IEC 61000-4-5




Fig. 3 - Typical Capacitance vs. Reverse Voltage




Fig. 4 - Typical Forward Voltage vs. Forward Current




Fig. 5 - Typical Reverse Voltage vs. Reverse Current





Fig. 6 - Typical Peak Clamping Voltage vs. Peak Pulse Current

Rev. 1.2, 03-May-17

4

Document Number: 85916





SHA

Fig. 7 - Typical Peak Forward Voltage vs. Forward Current






Fig. 8 - Typical Clamping Voltage vs. Peak Pulse Current






PACKAGE DIMENSIONS in millimeters: LLP2510-10M





		Millimeters			
	Min.	Nom.	Max.		
А	0.455	-	0.555		
A1	0.00	-	0.05		
b1	0.19	-	0.25		
b2	0.39	-	0.45		
D	2.45	-	2.55		
E	0.95	-	1.05		
е	-	0.50	-		
L1	0.35	-	0.41		
L2	0.48	-	0.54		




Α

A1

Document no.: S8-V-3906.04-040 (4) Created - Date: 27. July 2015 22804




CARRIER TAPE in millimeters LLP2510-10M



Cummulative tolerances of 10 sprocket holes is \pm 0.2 mm

Document no. S8-V-3906.04-0028 (4) Created - Date: 08. Jul. 2011

ORIENTATION IN CARRIER TAPE LLP2510-10M



Document no. S8-V-3906.04-0029 (4) Created - Date: 07. Jul. 2011



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.