

# Metal Composite Power Inductor (wire wound) Specification Sheet



# CIGW160808XMR47MLC (1608 / EIA 0603)

#### APPLICATION


Smart phones, Tablet, Wearable devices, Power converter modules, etc.



#### FFATURES

Small power inductor for mobile devices
Low DCR structure and high efficiency inductor for power circuits.
Monolithic structure for high reliability
Free of all RoHS-regulated substances
Halogen free

### RECOMMENDED LAND PATTERN



	Unit : mm
TYPE	1608
Α	0.8
В	0.5
С	0.9

### **DIMENSION**





D	
Bottom	View]

TYPE	Dimension [mm]							
IIFL	L	W	T	D				
1608	1.6±0.2	0.8±0.2	0.7±0.1	0.35±0.15				

### DESCRIPTION

	Part no.	Size	Thickness	Inductance Inductance tolerance	DC Resistance [mΩ]		Rated DC Current * 1 [A]		Rated DC Current * 2 [A]		
		[inch/mm] [mm] (max)	[uH]	(%)	Max.	Тур.	Max.	Тур.	Max.	Тур.	
	CIGW160808XMR47MLC	0603/1608	0.8	0.47	±20	43	37	2.7	3	3	3.3

- \* Inductance : Measured with a LCR meter 4991A(Agilent) or equivalent (Test Freq. 1MHz, Level 0.1V)
- \* DC Resistance : Measured with a Resistance HI-TESTER 3541(HIOKI) or equivalent
- \* Maximum allowable DC current : Value defined when DC current flows and the nominal value of inductance has decreased by 30% or

when current flows and temperature has risen to 40 ℃ whichever is smaller. (Reference: ambient temperature is 25 ℃±10)

(Isat): Allowable current in DC saturation: The DC saturation allowable current value is specified when the decrease of

the nominal inductance value at 30% (Reference: ambient temperature is 25 °C±10)

(Irms) : Allowable current of temperature rise : The temperature rise allowable current value is specified when temperature of the inductor is raised 40 ℃ by DC current. (Reference: ambient temperature is 25 ℃±10)


- \* Absolute maximum voltage : Rated Voltage 20V.
- $^{\star}$  Operating temperature range : -40 to +125°C (Including self-temperature rise)


## PRODUCT IDENTIFICATION

<u>CIG</u>	<u>W</u>	<u> 1608</u>	<u>08</u>	<u> </u>	<u>R47</u>	<u>M</u>	<u>L</u>	<u>C</u>
(1)	(2)	(3)	(4)	(5)	(6)	(7)	(8)	(9)

- (1) Power Inductor
- (3) Dimension (1608: 1.6mm  $\times$  0.8mm )
- (5) Remark (Characterization Code)
- (7) Toleranc∈ (M:±20%)
- (8) Internal Code
- (9) Packaging (C:paper tape, E:embossed tape)
- (2) Type (T: Metal Composite Thin Film Type)
- (4) Thickness (08: 0.8mm)
- (6) Inductance (R47: 0.47 uH)

# RECOMMENDED SOLDERING CONDITION





### **PACKAGING**

Packaging Style	Quantity(pcs/reel)
Card Board Taping	4000 pcs

Item	Specified Value	Т	Test Condition		
Solderability	More than 90% of terminal electrode should be soldered newly.	After being dipped in flux for 4±1 seconds, and preheated at $150 \sim 180^{\circ}\!$			
Resistance to Soldering	No mechanical damage. Remaining terminal Electrode: 75% min. Inductance change to be within ±20% to the initial.	After being dipped in flux for 4±1 seconds, and preheated at $150\!\sim\!180^{\circ}\!$			
Thermal Shock (Temperature Cycle test)	No mechanical damage Inductance change to be within ±20% to the initial.	Repeat 100 cycles under the following conditions. -40±3 °C for 30 min → 85±3 °C for 30 min			
High Temp. Humidity Resistance Test	No mechanical damage Inductance change to be within ±20% to the initial	85±2°C, 85%RH, for 500± Measure the test items aft humidity for 24 hours.	±12 hours. ter leaving at normal temperature and		
Low Temperature Test	No mechanical damage Inductance change to be within ±20% to the initial.	Solder the sample on PCE at -55±2°C for 500±12 hou Measure the test items aft humidity for 24hours.			
High Temperature Test	No mechanical damage Inductance change to be within ±20% to the initial.	hours.	B. Exposure at 125±2°C for 500±12 ter leaving at normal temperature and		
High Temp. Humidity Resistance Loading Test	No mechanical damage Inductance change to be within ±20% to the initial	85±2°C, 85%RH, Rated Current for 500±12 hours.  Measure the test items after leaving at normal temperature and humidity for 24 hours.			
High Temperature Loading Test	No mechanical damage Inductance change to be within ±20% to the initial	85±2°C, Rated Current for 500±12 hours.  Measure the test items after leaving at normal temperature and humidity for 24 hours.			
Reflow Test	No mechanical damage Inductance change to be within ±20% to the initial	Peak 260±5℃, 3 times			
Vibration Test	No mechanical damage Inductance change to be within ±20% to the initial.	Solder the sample on PCB. Vibrate as apply 10~55Hz, 1.5mm amplitude for 2 hours in each of three(X,Y,Z) axis (total 6 hours).			
	No mechanical damage	Bending Limit; 2mm Test Speed; 1.0mm/sec. Keep the test board at the limit point in 5 sec. PCB thickness: 1.6mm			
Bending Test	10	20 R340	Unit :mm 2 —		
	<del> </del>	<b>→</b>			
	No indication of peeling shall occur on the terminal electrode.	W(kgf) 0.5	TIME(sec) 10±1		
Terminal Adhesion Test					
Drop Test	No mechanical damage Inductance change to be within ±20% to the initial.	Random Free Fall test on 1 meter, 10 drops	concrete plate.		



# Metal Composite Power Inductor (wire wound)

# Data Sheet



### 1. Model: CIGW160808XMR47MLC

## 2. Description

Part no	Size Thickness Induc	Inductance	Inductance tolerance (%)	DC Resistance [mΩ]		Rated DC Current * 1 [A]		Rated DC Current * 2 [A]		
	[mm] (max)	[uH]		Max.	Тур.	Max.	Тур.	Max.	Тур.	
CIGW160808XMR47MLC	0603/1608	0.8	0.47	±20	43	37	2.7	3	3	3.3

<sup>\*</sup> Inductance: Measured with a LCR meter 4991A(Agilent) or equivalent (Test Freq. 1MHz, Level 0.1V)

(Isat) : Allowable current in DC saturation : The DC saturation allowable current value is specified when the decrease of the nominal inductance value at 30% (Reference: ambient temperature is 25°C±10)


(Irms) : Allowable current of temperature rise : The temperature rise allowable current value is specified when temperature of the inductor is raised 40°C by DC current. (Reference: ambient temperature is 25°C±10)

\* Absolute maximum voltage: Rated Voltage 20V.

### 3. Characteristics data


# 1) Frequency characteristics (Ls)

Agilent E4294A +E4991A , 1MHz to 1,000MHz




### 2) Frequency characteristics (Q)


Agilent E4294A +E4991A, 1MHz to 1,000MHz



# 3) DC Bias characteristics (Typ.)



# 4)Temperature characteristics (Typ.)





<sup>\*</sup> DC Resistance : Measured with a Resistance HI-TESTER 3541(HIOKI) or equivalent

<sup>\*</sup> Maximum allowable DC current: Value defined when DC current flows and the nominal value of inductance has decreased by 30% or when current flows and temperature has risen to 40°C whichever is smaller. (Reference: ambient temperature is 25°C±10)

<sup>\*</sup> Operating temperature range : -40 to +125°C (Including self-temperature rise)