
Blackbird

Embedded Processing Unit



Overview

The Blackbird is a compact, rugged x86 type board-level embedded computer. It has been engineered and tested to meet the military and medical industries' evolving requirements to develop smaller, lighter, and lower power embedded systems while adhering to stringent regulatory standards. The Blackbird is a member of the VersaLogic family of ultra-rugged EPU embedded computers. Using fully integrated COM components, the Blackbird is supplied fully assembled and tested, including heat plate, ready to install in a system. In addition to providing a very compact footprint, it is designed to withstand extreme temperature, impact, and vibration.

The Skylake processor options feature quad- and dual-core CPUs along with Hyper-Threading logic allowing up to 8 simultaneous threads to be executed. The Blackbird provides great performance and I/O features, moderate power consumption (15 to 22 W typical depending on model), and a compact package. The Blackbird provides compatibility with a broad range of standard x86 application development tools for reduced development time.

The on-board Power Management Unit greatly simplifies system power supply requirements. It features a wide input voltage range of 8 to 30 volts so it is fully compatible with 12 or 24V vehicle applications. It also includes reverse voltage protection,

Highlights

- -40° to +85°C operating temperature models
- Trusted Platform Module (TPM) security chip
- Shock & vibration per MIL-STD-202G
- 6th Generation Intel[®] Core[™]
 "Skylake" processor
 - i7-6822EQ (quad core) or
 - i5-6442EQ (quad core) or
 - i5-6300U (dual core) or
- i3-6100U (dual core)
- On-board Power Management
- 8 to 30 volt DC input (12 and 24 volt system compatible
- Over- and reverse-voltage protection
- RF noise filtering
- Transient voltage protection

- A complete x86 embedded computer
- COM Basic size: (95 x 125 x 37 mm)
- Up to 32 GB DDR4 RAM
- Two Gigabit Ethernet
- Two mini DisplayPort and LVDS video outputs
- Three Mini PCle Sockets
- Two USB 3.0 port, four USB 2.0 ports
- Serial I/O ports, SATA, Digital I/O
- Analog Inputs (8 chan.)
- Analog Outputs (4 chan.)
- HD Audio
- Customization available
- VersaAPI software support



Overview ...continued

over voltage protection, RF noise filtering, and transient voltage protection, to provide enhanced durability and reliability in the field.

Designed and tested for industrial temperature (-40° to +85°C) operation, the rugged Blackbird also meets MIL-STD-202G specifications for shock and vibration. Latching SATA,

Ethernet, power, and main I/O connectors provide additional ruggedization for use in harsh environments.

Blackbird is compatible with a variety of popular x86 operating systems including Windows, Windows Embedded, Linux, and VxWorks.

COTs modifications are available, even in low OEM quantities. Modifications include conformal coating, BIOS / splash screen configuration, application specific testing, BOM revision locks, custom labeling, etc.

Features

1 On-board Power Management

Accepts 8 to 30 volts DC, and provides OVP, reverse polarity protection, RF noise filtering, and transient voltage suppression.

High-performance Video

Integrated Intel HD Graphics Gen 9 core supports DirectX 12, OpenGL 4.4, and H.264, MPEG-2 encoding/decoding. Two Mini DisplayPorts (2a) and a dual-channel LVDS video output (2b on back side). LVDS backlight control (2c).

3 Network

Two Gigabit Ethernet (GbE) ports. One port with remote boot support.

4 SATA

Two 6 Gb/s SATA ports support bootable SATA hard drives.

Mini PCle Card Sockets

Two full- and one half-sized sockets. Supports Wi-Fi modems, GPS, MIL-STD-1553, Ethernet, flash data storage with auto-detect mSATA flash storage support, and other mini PCIe modules.

6 Industrial I/O

Two USB 3.0 ports (6a) and four USB 2.0 ports (6b) support keyboard, mouse, and other devices.

Four RS-232/422/485 serial ports (6c on back side), three 8254 timer/counters, I2C support, and audio output (6d on back side).

Analog + Digital I/O

On-board data acquisition support. Eight multi-range analog inputs, four analog outputs (7a), and twenty four 3.3V digital I/O lines (7b).

8 SPI Interface

Supports SPI and SPX devices, including low cost analog and digital modules.

Trusted Platform Module

On-board TPM security chip can lock out unauthorized hardware and software.

Intel Core "Skylake" Processor (not shown)

Up to 2.6 GHz clock rate. Quad- and dual-core options.

RAM (not shown)
Up to 32 GB DDR4 RAM.

Industrial Temperature Operation


-40° to +85°C operation for harsh environments.

MIL-STD-202G

Qualified for high shock/vibration environments.

Software Support

Compatible with a variety of popular x86 operating systems including Windows, Windows Embedded, Linux, and VxWorks.



Tailor Blackbird to Your Exact Requirements

COTS modifications are available in quantities as low as 100 pieces.

- Conformal Coating
- Custom Cabling
- Connector & I/O Changes
- Custom Testing
- Custom Labeling
- BIOS Modifications
- Software and Drivers
- Environmental Screening
- Revision Locks
- Application-Specific Testing
- And more –

Specifications

•	1						1	
General								
Board Size	95 x 125 x 37 mm (3.74 x 4.92 x 1.45")							
Weight	378 grams (1	3.33 oz.)						
Processor	Intel 6th Gen Core platform. 8 MB SmartCache. Intel 64-bit instructions, Hyper-Threading, Virtualization Technology (VT), SpeedStep Technology, and AES New Instructions.							
Battery	Connection for	or 3.0V F	TC ba	ckup ba	ittery			
Power Requirements	Model Idle Typical Max.							
(@ +12V) †	VL-EPU-4462	7	7.7W 15.3		W 23.0W			
	VL-EPU-4462-xBP-16 7.4W 15.6W 2						23.8W	
							24.2W	
	VL-EPU-4562	2-xBP-16	12	2.0W	21.0W		30.0W	
	VL-EPU-4562	2-xCP-16	12	12.0W 21		W	31.2W	
	VL-EPU-4562	2-xCP-32	12	2.0W	22.2W		32.4W	
Input Voltage	8V – 30V DC							
Input Protections	Over-voltage protection. Self resetting when input falls to a safe level. Reverse voltage input protection to -30V. RF noise filtering (900 MHz, 2.5/5 GHz) - Minimum of 30 dB RF attenuation above 100 MHz. Transient voltage protection (inductive kickback / lightning) clamp at ~+60V / -40V - MSL level 1, per J-STD-020, LF maximum peak of 260°C							
System Reset & Hardware Monitors	All voltage rails monitored. Watchdog timer with programmable timeout. Push-button sleep, reset, and power.							
Regulatory Compliance	RoHS (2011/65/EU)							
Environmental								
Thermal Management	Bolt-on heat r	nlate star	ndard	Ontions	al heat o	sink f	an heat	
	Bolt-on heat plate standard. Optional heat sink, fan, heat pipe, and other thermal accessories available.							
Operating Temperature ◊	Model	el Heat Pla		te** Heat Sink		HeatSink + Fan		
	EPU-4x62- <u>E</u>	EPU-4x62- <u>E</u> -40° to +85°C -40° to +85°C		+85°C	-40° to +85°C			
	EPU-4x62- <u>S</u>	EPU-4x62- <u>S</u> 0° to +60°C 0° to +60°C 0° to				o +60°C		
	Ranges shown assume 90% CPU utilization. thermal information and exceptions, refer to t EPU-4562 Reference Manual. ** Heat plate must be kept below 90°C							
Airflow Requirements	Refer to the VL-EPU-4462/4562 Reference Manual for detailed airflow requirements.							
Storage Temperature	-40° to +85°C	;						
Altitude *	Operating		To 4,5	To 4,570m (15,000 ft.)				
	Storage		To 12	To 12,000m (40,000 ft.)				
Thermal Shock	5°C/min. over	operatir	ng tem	perature	Э			
Humidity	Less than 95%, noncondensing							
Vibration, Sinusoidal Sweep ¤	MIL-STD-202G, Method 204, Modified Condition A: 2g constant acceleration from 5 to 500 Hz, 20 min. per axis							
Vibration, Random ¤	MIL-STD-202G, Method 214A, Condition A: 5.35g rms, 5 min. per axis							
	MIL-STD-202G, Method 213B, Condition G: 20g half-sine, 11 ms duration per axis							
Mechanical Shock ¤	MIL-STD-202	G, Meth		B, Cond	dition G	: 20g	half-sine,	
	MIL-STD-202	G, Meth		B, Cond	dition G	: 20g	half-sine,	
Mechanical Shock Security TPM	MIL-STD-202	G, Methon	is			: 20g	half-sine,	

† Represents operation at +25°C and +12V supply running Windows 10 with LVDS display, SATA,
GbE, COM, and USB keyboard/mouse. Typical power computed as the mean value of Idle and
Maximum power specifications. Maximum power measured with 95% CPU utilization.

- ◊ Derate -1.1°C per 305m (1,000 ft.) above 2,300m (7,500 ft.)
- * Extended altitude specifications available upon request
- ‡ TVS protected port (enhanced ESD protection)
- § Power pins on this port are overload protected
- ¥ Bootable storage device capability

Mamani					
Memory	00 OB BBB 4 OB	244			
System RAM	Up to 32 GB DDR4 SDRAM.				
Video					
General	Integrated high-performance video. Intel HD 520 and 530 - Gen-9 compute architecture, 24 execution units, and GPU Turbo Boost. Supports 3 independent displays. Supports DirectX 12, OpenGL 4.4, OpenCL 2.0.				
Hardware Based Acceleration	Decode and Encode of JPEG, MJPEG, MPEG2, AVC, MVC, HEVC 8-bit, VC-1, VP8, VP9				
DisplayPort Interface §	at 60 Hz.	outputs. 24-bit. Up to 4096 x 2160			
OEM Flat Panel Interface	Dual-channel LVDS inte 1200. Backlight control	erface. 18/24-bit. Up to 1920 x signals.			
Mass Storage					
Rotating Drive ¥	Two SATA 6 Gb/s ports.	Latching SATA connectors.			
Flash / SSD ¥	Mini PCIe socket with m				
Network Interface					
Ethernet ‡	Two AutoDetect 10BaseT/100BaseTX/1000BaseT ports. Latching connector. One port with network boot option.				
Device I/O					
USB ‡§	Two USB 3.0 / 2.0 ports and four USB 2.0 host ports				
COM Interface ‡	Four RS-232/422/485 selectable. 16C550 compatible. 1 Mbps max.				
Digital I/O	Twenty four TTL I/O Lines 3.3V. Independently configurable.				
Analog Input	Eight channels. 12-bit. Single-ended. 500 Ksps. Independently configurable +/- 0.64V to +/- 10.24V high input impedance inputs				
Analog Output	Four channels. 12-bit single-ended. 100 Ksps.				
I2C	Single I2C interface				
Counter / Timers	Three 8254 compatible F (PITs).	Programmable Interval Timers			
Audio Input / Output	Connector	Signal Characteristics			
	Line Input - Latching	10 kΩ minimum			
	Line Output - Latching	600 Ω (to drive a 10 k Ω load)			
VersaLogic SPI Interface	Supports SPI and SPX d modules.	evices. Supports up to two SPX			
Mini PCle Card Socket					
Full size Socket #1	Supports Wi-Fi modems, GPS receivers, MIL-STD-1553, Ethernet channels, non-volatile flash data storage, and other plug-in modules. USB, SATA, and PCle signaling. Autodetect mSATA support.				
Full size Socket #2	PCIe and USB 2.0 signaling				
Half size Socket #3	PCIe and USB 2.0 signaling				
Software					
BIOS	AMI Aptio UEFI BIOS w Field reprogrammable	ith OEM enhancements.			
Sleep Mode	ACPI 3.0. Support for S3 suspend and S4 hibernate states.				
Operating Systems	Compatible with most x86 operating systems including Windows, Windows Embedded, Linux, and VxWorks				

□ MIL-STD-202G shock and vibe levels are used to illustrate the extreme ruggedness of this product in general. Testing at higher levels and/or different types of shock or vibration methods can be accommodated per the specific requirements of the application. Contact VersaLogic Sales for further information.

Specifications are subject to change without notification. Intel and Core are trademarks of Intel Corp. All other trademarks are the property of their respective owners.



Product Data Sheet Embedded Processing Unit

Ordering Information

Call VersaLogic Sales at (503) 747-2261 for more information!

				Hyper-Threads /	CPU Clock /		Graphics Base Clock /		
Model	Operating Temp.†	Processor	Cores	Threading	Turbo Speed	Graphics Core	Max Dynamic Speed	Memory	Cooling
VL-EPU-4462-SAP-08	0° to +60°C	i3-6100U	2	Yes / 4	2.3 GHz / NA	HD 520	300 MHz / 1.0 GHz	8 GB	Heat plate
VL-EPU-4462-SBP-16	0° to +60°C	i5-6300U	2	Yes / 4	2.4 / 3.0 GHz	HD 520	300 MHz / 1.0 GHz	16 GB	Heat plate
VL-EPU-4462-SCP-16 **	0° to +60°C	i7-6600U	2	Yes / 4	2.6 / 3.4 GHz	HD 520	300 MHz / 1.05 GHz	16 GB	Heat plate
VL-EPU-4562-SBP-16	0° to +60°C	i5-6442EQ	4	No / 4	1.9 GHz / 2.7 GHz	HD 530	350 MHz / 1.0 GHz	16 GB	Heat plate
VL-EPU-4562-SCP-16	0° to +60°C	i7-6822EQ	4	Yes / 8	2.0 GHz / 2.8 GHz	HD 530	350 MHz / 1.0 GHz	16 GB	Heat plate
VL-EPU-4562-SCP-32	0° to +60°C	i7-6822EQ	4	Yes / 8	2.0 GHz / 2.8 GHz	HD 530	350 MHz / 1.0 GHz	32 GB	Heat plate
VL-EPU-4462-EAP-08	-40° to +85°C	i3-6100U	2	Yes / 4	2.3 GHz / NA	HD 520	300 MHz / 1.0 GHz	8 GB	Heat plate
VL-EPU-4462-EBP-16	-40° to +85°C	i5-6300U	2	Yes / 4	2.4 / 3.0 GHz	HD 520	300 MHz / 1.0 GHz	16 GB	Heat plate
VL-EPU-4462-ECP-16 **	-40° to +85°C	i7-6600U	2	Yes / 4	2.6 / 3.4 GHz	HD 520	300 MHz / 1.05 GHz	16 GB	Heat plate
VL-EPU-4562-EBP-16	-40° to +85°C	i5-6442EQ	4	No / 4	1.9 GHz / 2.7 GHz	HD 530	350 MHz / 1.0 GHz	16 GB	Heat plate
VL-EPU-4562-ECP-16	-40° to +85°C	i7-6822EQ	4	Yes / 8	2.0 GHz / 2.8 GHz	HD 530	350 MHz / 1.0 GHz	16 GB	Heat plate
VL-EPU-4562-ECP-32	-40° to +85°C	i7-6822EQ	4	Yes / 8	2.0 GHz / 2.8 GHz	HD 530	350 MHz / 1.0 GHz	32 GB	Heat plate

^{**} Special order product. Contact VersaLogic Sales for minimum order quantities and lead time.

Ordering Information

Part Number	Description			
Cable Kit				
VL-CKR-	BLACKBIRD cable kit. Includes VL-CBR-4005, 1014 (x2), 0702, 1604,			
BLACKBIRD	2004, 2005, 2032, 0809, 0810, HDW-401, and 108.			
VL-CBR-4005	System I/O paddleboard			
VL-CBR-0702	SATA cable – rugged latching, 20"			
VL-CBR-1604	Dual Ethernet cable, 16-pin Clik-Mate to 2 RJ-45 – rugged latching, 12"			
VL-CBR-2004	Analog I/O cable and paddleboard, 1mm 20-pin, 12"			
VL-CBR-2005	Digital I/O cable and paddleboard, 1mm 20-pin, 12"			
VL-CBR-2032	miniDisplayPort to VGA adapter, 6"			
VL-CBR-0809	Power adapter cable, 12V medium-power. ATX12 to Blackbird. 12"			
VL-CBR-0810	Stereo Audio Cable, 8-pin Pico-Clasp to 3.5mm Jacks, 0.5m			
VL-CBR-1014 x2	RS232 Dual channel cable 2xDsub (9-pin), Latching, 12"			
VL-HDW-401	Thermal compound paste. For heat sink attachment.			
VL-HDW-108	Mini PCIe/mSATA hardware kit (metric thread) 2.5 mm (10ea)			
Cables				
VL-CBR-0203	2-pin Latching Battery Module, 6"			
VL-CBR-0401	ATX to SATA power cable, 6.25"			
VL-CBR-0404	LED Back Light, 3-pin Pico-Clasp / 4-pin IDE Power to 6-pin 12V, 500mm			
VL-CBR-0503	USB 2.0 Male A to Male Micro-B Cable, 0.5 m			
VL-CBR-0901	Pico-Clasp to Dual SPX Cable, 9-pin. 9"			
VL-CBR-2014	LVDS to VGA adapter board			
VL-CBR-2031	miniDisplayPort to miniDisplayPort, 36"			
VL-CBR-2033	miniDisplayPort to HDMI active adapter, 6"			
VL-CBR-3001	20" 2-Ch LVDS 30-pin JAE to 30-pin JAE, RoHS			
VL-CBR-3002	20" 1-Ch LVDS 30-pin JAE to 1.25mm 20-pin Hirose, RoHS			
VL-CBR-3003	20" 1-Ch LVDS 30-pin JAE to 20-pin JAE, RoHS			
Hardware				
VL-PS-ATX12-300A	ATX development power supply			
VL-HDW-111	Half- to Full-Size Mini PCle Adapter kit. Metal adapter and screws (2)			
Thermal Options				
VL-HDW-417	Passive Heat Sink. Mounts to heat plate on standard product 95 x 125 x 15 mm			
VL-HDW-418	12V Cooling fan for optional use with HDW-417 heat sink.			

Expansion Modules

Part Number	Description	Form Factor		
Network				
VL-MPEe-E3E	Gigabit Ethernet adapter	Mini PCle		
VL-MPEe-FW1E	FireWire adapter	Mini PCIe		
Serial I/O				
VL-MPEe-U2E	Quad serial plus twelve GPIOs	Mini PCle		
Analog & Digital	1/0			
VL-MPEe-A1E	Analog input (12-bit resolution)	Mini PCle		
VL-MPEe-A2E	Analog input (16-bit resolution)	Mini PCIe		
VL-SPX-1	Analog Input Module 8-Channels	SPX		
VL-SPX-2	Digital I/O Module 16-lines	SPX		
VL-SPX-4	Analog Output Module 4-channels 12-bit	SPX		
VL-SPX-5	Solid State Switch Module 8-channel	SPX		
GPS				
VL-MPEu-G2E	GPS receiver	Mini PCIe		
Video				
VL-MPEe-V5E	VGA and LVDS Interface	Mini PCIe		
Solid-State Storage (flash memory)				
VL-MPEs-F1Exx	mSATA module (4/16/32 GB)	Mini PCIe		
Adapters				
VL-MPEs-S3E	SATA adapter	Mini PCle		

Take the Risk out of Embedded Computing

Whether it's selecting the optimum solution for your application, lending expertise during development, or on-time delivery of defect-free products, VersaLogic is here to make sure your project goes smoothly from initial concept through the extended life of your program. Contact us today to learn more.

ISO 9001:2015 Certified

☐ erisys Registrars



Copyright © 2018 VersaLogic Corporation. All rights reserved. 12/06/18



[†] Derate -1.1°C per 305m (1,000 ft.) above 2,300m (7,500 ft.)