





Ansicht auf Haftfläche



2

d ₁	d ₂	h	t ₁	t ₂	Nominal magnetic forces in N
22	M 4	6	4,5	0,8	35
31	M 5	6	4,5	0,8	75
43	M 4	5,5	4	0,8	85
66	M 6	8,5	6	1,8	180
88	M 6	8,5	6	1,8	420

Specification

1

3

- Steel part
zinc plated
- Material of the magnet
NdFeB **ND**
Neodymium, iron, boron
temperature resistant up to 80 °C
- Rubber jacket
Elastomer (TPE)
80 shore A ≈
black **● SW**
white **○ WS**
- Elastomer characteristics → Page 1483
- RoHS

Information

Retaining magnets GN 51.5 are a shielded magnetic system with rubber jacket.

The rubber jacket protects sensitive surfaces from being damaged by the magnet and also delivers a higher friction coefficient, resulting in high lateral adhesion forces.

see also...

- More information to retaining magnets → Page 1380 ff.
- Holding discs GN 70 → Page 1414
- Magnetic discs GN 70.1 → Page 1415

How to order

GN 51.5 -ND-88-SW

1	Material of the magnet
2	d ₁
3	Color