PCN Num	ber:	20150505	5003				PCN D	ate:	05/14/2015
Title:	Add Cu a	s Alternat	ive Wire	Base Met	al for Selecte	ed Device	e(s)		
Custome	r Contac	PCN /	<u>Manager</u>	Dept:	Quality Ser				
Proposed	l 1 st Shir	Date:	08/14/	2015	Esti	mated S			provided at
_			00, = .,			Availa	ability:	sam	ole request
Change T							7 1 144 6		6.1
	nbly Site			Design			_		p Site
✓ Assembly Process✓ Assembly Materials			Data S	Sheet Wafer Bump Materia umber change Wafer Bump Process					
Mechanical Specification		1	Test Si				r Fab		
Packing/Shipping/Labeling			Test Pr			_		Materials	
☐ Wafer Fab Process									
	PCN Details								
Descripti	on of Ch	nange:							
Texas Instruments is pleased to announce the qualification of Cu as an additional bond wire option for devices listed in "Product affected" section below. Devices will remain in current assembly facilities and there will be no other piece part changes:									
	Pkg Family					Additio	nal W	ire	
	SOT23			u, 1.0 mil			Cu, 0.		
	SOIC			u, 1.0 mil		Cu, 0.96 mil			
	VSSOP			u, 1.0 mil		Cu, 0.96 mil			
	TSSOP			u, 1.0 mil			Cu, 0.		
	QFN		А	u, 1.0 mil			Cu, 0.	80 mi	I
Reason f	or Chan	ge:							
Continuity of supply. 1) To align with world technology trends and use wiring with enhanced mechanical and electrical properties 2) Maximize flexibility within our Assembly/Test production sites. 3) Cu is easier to obtain and stock									
Anticipat	ed impa	ct on Fo	rm, Fit,	Function	, Quality or	Reliabil	lity (pos	sitive	/ negative):
None									
Changes	to prod	uct ident	ificatio	n resultin	g from this	PCN:			
None									
Product /	Affected	:							
See Page	2.								

0.96 mil Cu wire qual for SOT23 Packages

Product Attributes

Attributes	Qual Device: LM4041AIM3-1.2	Qual Device: LP3985IM5X-5.0	Qual Device: LMC7101AIM5NOPB	Qual Device: LM431CCM3NOPB
Assembly Site	TIEMA	TIEMA	TIEMA	TIEMA
Package Family	SOT	SOT	SOT	SOT
Flammability Rating	UL 94 V-0	UL 94 V-0	UL 94 V-0	UL 94 V-0
Wafer Fab Supplier	GFAB	MFAB	GFAB	GFAB
Wafer Fab Process	BPLFAST-1	CMOS7	P2CMOS	SLM

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition			Qual Device: LM431CCM3NOPB		
PC	PreCon Level 1	Level 1- 260C	3/693/0	3/462/0	3/693/0	3/462/0
HAST	Biased HAST, 130C/85%RH	96/hrs. @130C	3/231/0	-	3/231/0	-
AC	Autoclave 121C	96HRS	3/231/0	3/231/0	3/231/0	3/231/0
TC	Temperature Cycle, -65/150C	TMCL500X	3/231/0	3/231/0	3/231/0	3/231/0
HTSL	High Temp Storage Bake 150C	1000 hrs. @150C	1/77/0	-	1/77/0	1/77/0
MQ	Manufacturability (Assembly)	(per mfg. Site specification)	Pass	Pass	Pass	Pass
DPA	Destructive Physical Analysis Post 500 Temp Cycle	x-section and de process to examine assembly robustness, Check for stich bond and bond pad integrity	3/15/0	3/15/0	3/15/0	3/15/0
YLD	FTY and Bin Summary	Compare against baseline	Pass	Pass	Pass	Pass

0.96 mil Cu wire qual for SOIC Packages

Product Attributes

Attributes	Qual Device: DS90CP22MXA1CL	Qual Device: LMV324MX	Qual Device: LP2995MXNOPB	Qual Device: LMC6482AIM/NOPB
Assembly Site	TIEMA	TIEMA	TIEMA	TIEMA
Package Family	SOIC	SOIC	SOIC	SOIC
Flammability Rating	UL 94 V-0	UL 94 V-0	UL 94 V-0	UL 94 V-0
Wafer Fab Supplier	MFAB	MFAB	MFAB	GFAB
Wafer Fab Process	CMOS7	CS80	CS65	P2CMOS

Qualification ResultsData Displayed as: Number of lots / Total sample size /
Total failed

Туре	Test Name / Condition	Duration	Qual Device: Qual Device: Qual Device: DS90CP22MXA1CL LMV324MX LP2995MXNOPB		Qual Device: LMC6482AIM/NOPB	
PC	PreCon Level 1	Level 1- 260C	3/462/0	-	3/462/0	3/693/0
HAST	Biased HAST, 130C/85%RH	96/hrs. @130C	-	-	-	3/231/0
AC	Autoclave 121C	96HRS	3/231/0	-	3/231/0	3/231/0
TC	Temperature Cycle, -65/150C	TMCL500X	3/231/0	•	3/231/0	3/231/0
HTSL	High Temp Storage Bake 150C	1000 hrs. @150C	-	-	-	1/77/0
MQ	Manufacturability (Assembly)	(per mfg. Site specification)	-	Pass	Pass	Pass
DPA	Destructive Physical Analysis Post 500 Temp Cycle	x-section and de process to examine assembly robustness, Check for stich bond and bond pad integrity	3/15/0	-	3/15/0	3/15/0
YLD	FTY and Bin Summary	Compare against baseline	-	Pass	Pass	Pass

0.96 mil Cu wire qual for VSSOP & TSSOP Packages

Product Attributes

Attributes	Qual Device: LMV852MMX	Qual Device: LMC6482IMM	Qual Device: LM93CIMT	Qual Device: LM5642MHX	
Assembly Site	TIEMA	TIEMA	TIEMA	TIEMA	
Package Family	VSSOP	VSSOP	TSSOP	TSSOP	
Flammability Rating	UL 94 V-0	UL 94 V-0	UL 94 V-0	UL 94 V-0	
Wafer Fab Supplier	MFAB	GFAB	MFAB	MFAB	
Wafer Fab Process	CMOS7	P2CMOS	CMOS7	ABCD150	

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: LMV852MMX	Qual Device: LMC6482IMM	Qual Device: LM93CIMT	Qual Device: LM5642MHX
PC	PreCon Level 1	Level 1- 260C	3/462/0	3/462/0	-	3/231/0
PC	PreCon Level 2	Level 2 3/693/0 260C		-		
HAST	Biased HAST, 130C/85%RH	96/hrs. @130C	-	-	3/231/0	-
AC	Autoclave 121C	96HRS	3/231/0	3/231/0	3/231/0	-
TC	Temperature Cycle, -65/150C	TMCL500X	3/231/0	3/231/0	3/231/0	3/231/0
HTSL	High Temp Storage Bake 150C	1000 hrs. @150C	-	-	1/77/0	-
MQ	Manufacturability (Assembly)	(per mfg. Site specification)	Pass	Pass	-	-
DPA	Destructive Physical Analysis Post 500 Temp Cycle	x-section and de process to examine assembly robustness, Check for stich bond and bond pad integrity	3/15/0	3/15/0	-	3/15/0
YLD	FTY and Bin Summary	Compare against baseline	Pass	Pass	-	-

0.96 mil Cu wire qual for TSSOP Packages

Product Attributes

Attributes	Qual Device: LMH0346MH	Qual Device: LM5037MT	Qual Device: LM3657MH/NOPB	Qual Device: SCANSTA111MTX
Assembly Site	TIEMA	TIEMA	TIEMA	TIEMA
Package Family	TSSOP	TSSOP	TSSOP	TSSOP
Flammability Rating	UL 94 V-0	UL 94 V-0	UL 94 V-0	UL 94 V-0
Wafer Fab Supplier	MFAB	GFAB MFAB		MFAB
Wafer Fab Process	BICMOS8B+	ABCD150	CMOS7	CMOS7

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Туре	Test Name / Condition	Duration	Qual Device: LMH0346MH	Qual Device: LM5037MT	Qual Device: LM3657MH/NOPB	Qual Device: SCANSTA111MTX
PC	PreCon Level 1	Level 1- 260C	-	3/693/0	3/462/0	-
PC	PreCon Level 2	Level 2- 260C	-	-	-	3/462/0
PC	PreCon Level 3	Level 3- 260C	3/231/0	-	-	-
THBT	THBT 85C, 85%RH	1000/hrs. @85C	-	3/231/0	-	-
AC	Autoclave 121C	96HRS	-	3/231/0	3/231/0	3/231/0
TC	Temperature Cycle, -65/150C	TMCL500X	3/231/0	3/231/0	3/231/0	3/231/0
HTSL	High Temp Storage Bake 150C	1000 hrs. @150C	-	1/77/0	-	-
MQ	Manufacturability (Assembly)	(per mfg. Site specification)	Pass	Pass	Pass	Pass
DPA	Destructive Physical Analysis Post 500 Temp Cycle	x-section and de process to examine assembly robustness, Check for stich bond and bond pad integrity	3/15/0	3/15/0	3/15/0	3/15/0
YLD	FTY and Bin Summary	Compare against baseline	Pass	Pass	Pass	Pass

⁻ Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

⁻ The following are equivalent HTSL options based on an activation energy of 0.7eV: 150C/1k Hours, and 170C/420 Hours - The following are equivalent Temp Cycle options per JESD47: -55C/125C/700 Cycles and -65C/150C/500 Cycles

Quality and Environmental data is available at TI's external Web site: http://www.ti.com/

0.8 mils Cu wire qual on BC13, CMOS9T and CMOS7 in WQFN and WSON **Packages**

Approved 09/23/2014

Product Attributes

Attributes	Qual Device: DP83848T SQ	Qual Device: DS91M040TSQ AW2	Qual Device: DS100DX410EL 16	Qual Device: DS80PCI402A2TT	Qual Device: LMH0366SQENOPB	Qual Device: LMH0394SQ/NOPB
Assembly Site	TIEM-AT	TIEM-AT	TIEM-AT	TIEM-AT	TIEM-AT	TIEM-AT
Package Family	WQFN	WQFN	WQFN	WQFN	WQFN	QFN
Flammability Rating	UL 94 V-0	UL 94 V-0	UL 94 V-0	UL 94 V-0	UL 94 V-0	UL 94 V-0
Wafer Fab Supplier	MAINEFAB	MAINEFAB	MAINEFAB	MAINEFAB	MAINEFAB	MAINEFAB
Wafer Fab Process	CMOS9T	CMOS7	BICMOS13	BICMOS13	BICMOS13	BICMOS13

- QBS: Qual By Similarity
- Qual Device DS100DX410EL16 is qualified at LEVEL3-260C
 Qual Device DS80PCI402A2TT is qualified at LEVEL2-260C
- Qual Device LMH0366SQENOPB is qualified at LEVEL1-260C
- Qual Device LMH0394SQ/NOPB is qualified at -
- Qual Device LMH0394SQ/NOPB REV A is qualified at LEVEL3-260C

Qualification Results

Data Displayed as: Number of lots / Total sample size / Total failed

Typ e	Test Name / Condition	Duratio n	Qual Device: DP83848T SQ	Qual Device: DS91M040TS QAW	Qual Device: DS100DX410 EL16	Qual Device: DS80PCI402 A2TT	Qual Device: LMH0366SQEN OPB	Qual Device: LMH0394SQ/N OPB
PC	PreCon Level 1	Level 1- 260C					3/720/0	
PC	PreCon Level 2	Level 2- 260C	3/1079/0		-	3/720/0	-	-
PC	PreCon Level 3	Level 3- 260C	,	1/255/0	3/720/0	-	-	3/231/0
HAST	Biased HAST, 130C/85%R H	96/hrs. @130C	-	-	-	-	-	3/231/0
AC	Autoclave 121C	96HRS	3/231/0	1/77/0	3/231/0	3/231/0	3/231/0	-
UHA ST	Unbiased HAST 130C/85%R H	unHAST- 96 HRS/-	3/231/0	1/77/0	3/231/0	3/231/0	3/231/0	-
TC	Temperature Cycle, - 65/150C	TMCL500 X	3/231/0	1/77/0	3/231/0	3/231/0	3/231/0	-
HTSL	High Temp Storage Bake 170C	420 hrs. @170C	3/231/0	-	-	3/231/0	-	-

ED	Side By Side Electrical Characterizat ion.	Datasheet		1/30/0	1/30/0	1/30/0	1/30/0	-
MQ	Manufactura bility (Assembly)	(per mfg. Site specificati on)	Pass	Pass	Pass	Pass	Pass	Pass
MSL	Thermal Path Integrity	Level 2- 260C	3/30/0	1/22/0	3/66/0	3/66/0	3/66/0	-
DPA		x-section and de process to examine assembly robustnes s, Check for stich bond and bond pad integrity	3/3/0	-	3/15/0	3/15/0	3/15/0	1/5/0 Post 96 hours HAST
YLD	FTY and Bin Summary	Comparo	Pass	Pass	Pass	Pass	Pass	Pass

⁻ Preconditioning was performed for Autoclave, Unbiased HAST, THB/Biased HAST, Temperature Cycle, Thermal Shock, and HTSL, as applicable

Green/Pb-free Status:

Qualified Pb-Free(SMT) and Green

For questions regarding this notice, e-mails can be sent to the regional contacts shown below or your local Field Sales Representative.

Location	E-Mail
USA	PCNAmericasContact@list.ti.com
Europe	PCNEuropeContact@list.ti.com
Asia Pacific	PCNAsiaContact@list.ti.com
Japan	PCNJapanContact@list.ti.com

⁻ The following are equivalent HTSL options based on an activation energy of 0.7eV : 150C/1k Hours, and 170C/420 Hours

⁻ The following are equivalent Temp Cycle options per JESD47 : -55C/125C/700 Cycles and -65C/150C/500 Cycles Quality and Environmental data is available at Tl's external Web site: http://www.ti.com/