

GX0-3306L

3225 Package Ultra-Low Jitter 3.3V

Oscillator

- Excellent phase noise & jitter characteristics
- Enable / disable tristate function
- Small and medium quantities also available



CONFIGURABLE OPTIONS	
Parameter	Option Code
Frequency	
Frequency stability	
* see note below	
Any	
±25ppm	А
±50ppm	В

^{*} Frequency stability is inclusive of calibration @ 25°C, operating temperature range, supply, voltage change, load change, shock and vibration.




SPECIFICATIONS

Frequency range	20.0 ~ 50.0MHz
Dimensions	3.2 x 2.5 x 1.1mm
Operating temperature range	-40 to +85°C
Storage temperature range	-55 to +125°C
Supply voltage (V _{DD})	+3.3V (±10%)
Supply current	20mA max
Output logic levels	'0' level = 10%V _{DD} max '1' level = 90%V _{DD} min
Start up time	5ms max
Waveform symmetry	45:55 max @ 50%V _{DD}
Driving ability	15pF CMOS
Rise / fall time	5ns max
Enable / disable function	Tristate (control via pad 1)
Phase jitter RMS * see note below	0.04ps typ (12kHz ~ 5.0MHz)
Phase noise (typ @	-101dBc/Hz @ 10Hz
24.576MHz)	-132dBc/Hz @ 100Hz
	-155dBc/Hz @ 1kHz
	-166dBc/Hz @ 10kHz
	-174dBc/Hz @ 100kHz
	-175dBc/Hz @ 1MHz
	-175dBc/Hz @ 5MHz

^{*} For ultimate performance, a high frequency decoupling capacitor should be connected between supply and ground as close to the oscillator supply pad as possible. Low frequency decoupling should be placed next to the supply source.

PACKAGE DRAWING



PAD	CONNECTION
1	Enable / disable
2	Ground
3	Output
4	Supply

Dimensions in mm



ORDERING INFORMATION

To request a quotation for the GXO-3306L please use the configurable options form to choose the options you require and then submit your configured product to our team. Our expert advisers are always happy to help with your requirements and can be contacted on +44 1460 256 100 or at sales@golledge.com.

Following product selection you will be issued with a seven character Golledge part number. Your Golledge part number is the internationally accepted Golledge manufacturing part number (MPN) that should be used for all project documentation, including bills of materials (BoMs) and purchase orders.

If you have any queries regarding any of our documentation our dedicated sales team will be happy to help.

ENABLE / DISABLE FUNCTION

Input (pad 1)	Output (pad 3)				
Open	Enabled				
'1' level, >0.7Vdd	Enabled				
'0' level, <0.3Vdd	High Impedance				


MARKING

FREQUENCY DC Marking type: Laser

DC = Date Code in YM, eg. "GF" = Jun 2017


	Α	В	С	D	Ε	F	G	Н	J	K	L	М
Υ	1	2	3	4	5	6	7	8	9	0		
M	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec

SOLDERING PROFILE





TAPE & REEL SPECIFICATION



Dimensions in mm

HANDLING & STORAGE



Human Body Model (HBM) 1A (250V to <500V)



Moisture Sensitivity Level (MSL): 1 (or not applicable)

CONSTRUCTION

Ceramic body with gold-plated pads Metal lid, seam sealed

COMPLIANCE



Lead-free (< 0.1% by weight)



RoHS compliant with no exemptions. See our

declaration



REACH compliant. See our statement



Free of conflict minerals. See our declaration



Free of Halogens. See our declaration



Free of Ozone-depleting substances. <u>See our</u>

declaration