# Preliminary Specification

Note: This is a draft specification and may change.

| Drawing No.  | TKY1D-H2-23019-00 [14] |
|--------------|------------------------|
| Issued Date. | January 23, 2023       |

# TO: Digi-Key

Note:In case of specification change, KYOCERA Part Number also will be changed.

| Product Name                  | Temperature Compensated Crystal Oscillator |
|-------------------------------|--|
| Product Model                 | KT1612A                                    |
| Frequency                     | 48.0MHz                                    |
| Customer Part Number          |  |
| Customer Specification Number |  |
| KYOCERA Part Number           | KT1612A48000DAW18TCK                       |
| Remarks RoHS Compliant, M     | SL=1                                       |

**Customer Acceptance** 

| Accept Signature | Accept Date      |  |
|------------------|------------------|--|
|                  | Department       |  |
|                  | Person in charge |  |

Seller

KYOCERA Corporation

Corporate Electronic Components Group Electronic Components Sales Division

6 Takeda Tobadono-cho, Fushimi-ku, Kyoto

612-8501 Japan

TEL. No. 075-604-3500 FAX. No. 075-604-3501 Manufacturer

**KYOCERA** Corporation

Corporate Electronic Components Group

RF Devices Division

Yamagata higashine Plant

5850, Higashine-koh, Higashine-shi, Yamagata

999-3701 Japan

TEL. No. 0237-43-5611

FAX. No. 0237-43-5615

| Design Department  | Quality   | Approved   | Examined                      | Examined    | Written        |
|--|-----------|------------|-------------------------------|-------------|----------------|
|  | Assurance | by         | by                            | by          | by             |
| RF Devices Engineering Department Crystal Components Application Engineering Section | Y.Kakuta  | W.Midraoka | (.H <mark>緣s</mark> o)ya<br>矢 | F.J. F.J. I | C.Nitoube<br>部 |

TKY1D-H2-23019-00 [14]

**Revision History** 

| Rev.No. | Description of revise | Date                | Approved<br>by | Examined<br>by | Examined by | Written<br>by |
|---------|-----------------------|---------------------|----------------|----------------|-------------|---------------|
| 00      | First Edition         | January 23,<br>2023 | W.Muraoka      | Y.Hosoya       | F.Horie     | C.Nitoube     |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       | <                   |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       | >                   |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |
|         |                       |                     |                |                |             |               |

| Drawing No. | TKY1D-H2-23019-00 [14] |
|-------------|------------------------|
|-------------|------------------------|

## 1. Purpose and scope

This document contains specification related to CRYSTAL OSCILLATOR model KT1612A48000DAW18TCK for Digi-Key

#### 2. Nominal condition

|   | Item  | MIN. | TYP.         | MAX  | Unit  | Conditions |
|---|---|------|--------------|------|-------|------------|
| 1 | Operating temperature range                       | -40  |              | +85  | deg.C |            |
| 2 | Storage temperature range                         | -40  |              | +85  | deg.C |            |
| 3 | Nominal frequency                                 |      | 48.0         |      | MHz   |            |
| 4 | Supply voltage                                    | 1.8  |              | 3.3  | V     |            |
| 5 | Absolute maximaum rating voltage (Supply voltage) | -0.6 |              | +4.6 | V     |            |
| 6 | Load impedance                                    | 9    | 10           | 11   | kohm  |            |
|   |   | 9    | 10           | 11   | pF    |            |
| 7 | Output signal condition                           |      | Clipped sine |      |       |            |

# 3. Electrical characteristics (T.B.D)

Ta= -40to +85deg.C, Vcc=1. 8V to 3.3V, Load=10kohm//10pF


|    | Item                    | MIN. | TYP. | MAX  | Unit                 | Conditions   | Remarks                         |
|----|-------------------------|------|------|------|----------------------|--|---------------------------------|
| 1  | Temp characteristics    | -2.0 |      | +2.0 | x10 <sup>-6</sup>    | Referenced to the mid point<br>between minimum<br>and maximum<br>frequency value over the<br>specified temperature range |                                 |
| 2  | Voltage characteristics | -0.2 | 4    | +0.2 | x10 <sup>-6</sup>    | Vcc+/-5%   | Vcc=1.8V+5% min.<br>3.3V-5%max. |
| 3  | Load characteristics    | -0.2 | -    | +0.2 | x10 <sup>-6</sup>    | 10kohm+/-10%,<br>10pF+/-10%  |                                 |
| 4  | Aging characteristics   | -1.0 |      | +1.0 | x10 <sup>-6</sup> /Y | 1year  | at 25+/-2 deg.C                 |
| 5  | Frequency tolerance     | -2.0 | >    | +2.0 | x10 <sup>-6</sup>    | After 2 times reflow soldering   | at 25+/-2 deg.C                 |
| 6  | Current                 |      |      | 2.0  | mA                   |  |                                 |
| 7  | Output voltage          | 0.8  |      |      | Vp-p                 |  |                                 |
| 8  | Harmonics               |      |      | -8.0 | dBc                  |  |                                 |
| 9  | Start up time           |      |      | 1.5  | msec                 | 90% of final output amplitude  |                                 |
|    |                         |      |      | 1.5  | msec                 | Within +/-0.5ppm   |                                 |
| 10 | Duty                    | 45   |      | 55   | %                    | @GND   |                                 |
| 11 | Phase noise             |      | -61  |      | dBc/Hz               | @1Hz offset  |                                 |
|    |                         |      | -90  |      | dBc/Hz               | @10Hz offset   |                                 |
|    |                         |      | -115 |      | dBc/Hz               | @100Hz offset  |                                 |
|    |                         |      | -136 |      | dBc/Hz               | @1kHz offset   | at 25+/-2 deg.C                 |
|    |                         |      | -153 |      | dBc/Hz               | @10kHz offset  |                                 |
|    |                         |      | -157 |      | dBc/Hz               | @100kHz offset   |                                 |
|    |                         |      | -157 |      | dBc/Hz               | @1MHz offset   |                                 |

Note. There is possibility to change standard values of electrical characteristics

Drawing No. TKY1D-H2-23019-00 [14]


#### 4. Circuit

Bypass Capacitor and DC- Blocking Capacitor do not build in this TCXO. So, Bypass Capacitor and DC- Blocking Capacitor are attached outside and please use it. And these Capacitor should be placed as close as possible to the pin(No.3 and No.4).



#### 5. Test circuit

\*Load 10kohm//10pF contains the internal impedance of FET probe.



| Drawing No. | TKY1D-H2-23019-00 [14] |
|-------------|------------------------|
|-------------|------------------------|

#### 6. Environment mechanical characteristics

|   | Item                                       | Conditions  | Remark  |
|---|--|---|---|
| 1 | High temperature storage                   | Ta=+85deg.C, judge on 240H storage  | It must be met to the characteristics Judging criterion.                        |
| 2 | Low temperature storage                    | Ta=-40deg.C, judge on 240H storage  | Measurement shall be taken at room ambient within 2 to 24hours after each test. |
| 3 | High temperature and high humidity storage | Ta=+85deg.C, RH=85%RH, judge on 240H storage  | and each teem   |
| 4 | Temperature cycle test                     | Ta=-40 to +85deg.C 30min. each 10cycles   |   |
| 5 | Drop test                                  | A test piece (100g) made of Teflon is dropped 3cycles (1cycle: 6 directions) from the height of 150cm on hard board   |   |
| 6 | Vibration test                             | 10 to 55 to 10Hz 1.5mm constant amplitude 1min. period X, Y, Z direction each 2H total 6H.  |   |
| 7 | Solder heat test                           | All terminal electrode shall be soldered at temperature of 350+/-5deg.C for 3+/-1sec. using a soldering iron.   |   |
| 8 | Solderability                              | Dip each of terminal electrode into 230+/-5deg.C solder pod for 5+/-0.5sec. after close, the test area of loads surfaces must be covered loads 90% by solder. |   |
| 9 | Reflow soldering                           | Reflow soldering at 2 times.  |   |

Normal Condition: Temperature 25+/-2deg.C Humidity 30 to 70%RH

#### Judge

| Itama                | Charification                   |
|----------------------|---------------------------------|
| Item                 | Specification                   |
| At 25deg.C frequency | +/-2.0ppm max(Before and After) |

TKY1D-H2-23019-00 [14]

#### 7. Reflow profile

7-1. Preheat: 180+0/-10deg.C, 120sec (max)

7-2. Peak Temperature: 260+0/-10deg.C, 10sec (max)

7-3. PC-Board


Material: FR-4

Size : 140mm\*110mm


Thickness: t=0.8mm

7-4. Condition of Measurement Temperature: Surface of PC-BOARD

# Reflow Soldering Condition




# 8. Marking contents





\*Laser Marking

|   | Contents         | Example                                     |
|---|------------------|---|
| 1 | Pin-1 identifier | 0   |
| 2 | Control Code1    | К   |
| 3 | Control Code2    | XX  |
| 4 | Monthly Code     | A3 *The 2023 January B3 *The 2023 February  |
| 5 | Control Code3    | X *Specification Code ("-" mark or nothing) |

#### 9. Dimensions








|        | Pin Connection |  |  |
|--------|----------------|--|--|
| #1 pin | GND or N.C.    |  |  |
| #2 pin | GND            |  |  |
| #3 pin | Output         |  |  |
| #4 pin | Vcc            |  |  |

Unit: mm


# Recommended Land Pattern



TKY1D-H2-23019-00 [14]

#### 10. Tape & Reel

## 10-1. Tape specification




10-1-1. Carrier Tape material: PS Included Carbon

10-1-2. #1pin Mark is positioned on right side against the direction of feed.

|           |            |            |            |             | Unit: mm   |  |
|-----------|------------|------------|------------|-------------|------------|--|
| Symbol    | Α          | В          | C          | D           | E          |  |
| Dimension | 1.45+/-0.1 | 1.85+/-0.1 | 8.0+/-0.2  | 3.5+/-0.05  | 1.75+/-0.1 |  |
|           |            |            |            |             |            |  |
| Symbol    | F          | G          | H          | I           | J          |  |
| Dimension | 4.0+/-0.1  | 2.0+/-0.05 | 4.0+/-0.05 | Ф1.5+0.1/-0 | Ф0.5+0.05  |  |
|           |            |            |            |             |            |  |

| Symbol    | K           | t           |
|-----------|-------------|-------------|
| Dimension | 0.65+/-0.05 | 0.20+/-0.05 |

## 10-2. Reel specification



10-2-1. Reel material: PS Included Carbon


10-2-2. Reel unit: 18,000pcs max. /1Reel

TKY1D-H2-23019-00 [14]

#### 10-3. Packing

#### 10-3-1. Trailer & Leader

As for the trailer and leader of taping, there are empty pockets as following drawing. Sprocket hole is positioned on upper side against the direction of feed. No missing components, excluding empty place.




#### 10-4. Shipping label

Following item shall be listed on reel, bag and box.

"Customer's name", "Parts No", "Lot No", "Quantity", "Order No", "Date of manufacture" The form of the label conforms to JEITA standard pattern C-3.

TKY1D-H2-23019-00 [14]

- 11. Top cover breaking and peeling force
  - 11-1. Reel Angle: 165 to 180deg
  - 11-2. Tape Break Force: 10N min
  - 11-3. Top Cover Tape Strength: 10N min
  - 11-4. Top Cover Tape Peel Force: 0.1 to 1.0N
  - 11-5. Top Cover Tape Peel Speed: 300+/-10mm / minute



TKY1D-H2-23019-00 [14]

#### 12. Notice

- 12-1. Please use soldering iron and the spot heater within the range of a solder heat test condition.
- 12-2. Units should be stored in a dry environment keeping away from the sun.
- 12-3. Don't leave units in High-temperature and High-humidity environment due to terminal solderability.

(Please keep 0 to 40deg.C and 30 to 70%RH for recommendable storage condition)

- 12-4. The term of a guarantee of taping packing is 6 months. (0 deg.C to 40 deg.C,RH30% to 70%)
- 12-5. Disapprove of washing.
- 12-6. Please contact us if you are considering molding by transfer or compression.
- 12-7. Unless we receive request for modification within 1 month from the issue date of this KC specification sheet, we will supply products according to this specification. Also, if you'd like to modify specification of order, which has been placed with delivery within 1 month from the issue data of this specification sheet, we would like to discuss with you separately.
- 12-8. This product can be used for general electronic equipment (information equipment, communication equipment, audiovisual equipment, measuring equipment, home appliances, etc.)Intended to be used. Equipment and systems (traffic equipment, safety equipment, aviation / space control, nuclear power control, life support equipment, base station ) that require special quality and reliability and whose failure or malfunction may endanger human life or harm the human body. (Including medical devices, etc.), basic driving functions (running, turning, stopping) and collision safety in traffic equipment, applications related directly or indirectly to collision safety, and applications that are expected to have a significant impact on property, etc. It is not intended to be used. In the unlikely event that this product is used for any of these purposes, we will not be liable for any damages resulting from such use.
- 12-9. In no event shall the company be liable for any product failure resulting from an inappropriate handling or operation of the product beyond the scope of its guarantee.
- 12-10. Information contained in this specification must not be quoted, reproduced or used for other purposes including processing either in part or in full without obtaining prior approval from the company.
- 12-11. Please keep it at the place that was the ESD protective.

Human model 1.5kohm 100pF: +/-1000V Machine model 0kohm 200pF: +/-200V

TKY1D-H2-23019-00 [14]

#### 13. Production place

#### 13-1. Manufacturer

KYOCERA Corporation.

#### 13-2. The site of the Factory

5850 Higashine-Koh, Higashine-shi, Yamagata, 999-3701, Japan 158-15 Chuo-kogyo-danchi, Sagae-shi, Yamagata, 991-0061, Japan 115-1 Jinmachi-aza-nishihara, Higashine-shi, Yamagata, 999-3761, Japan

#### 14. Quality guarantee

In case when Kyocera Corporation rooted failure occurred within 1year after its delivery, substitute product will be arranged based on discussion. Quality guarantee of product after 1year of its delivery is waivered.

#### 15. Parts Numbering Guide

# KT1612A 48000 D A W 18 T CK

- A. Series (1.6x1.2 SMD KT1612A)
- B. Frequency (48.0MHz)
- C. Frequency temperature accuracy (D: +/-2.0ppm)
- D. Minimum temperature range (A: -40deg.C)
- E. Maximum temperature range (W: +85deg.C)
- F. Supply voltage (18: エラー! 参照元が見つかりません。V)
- G. Control voltage stability (T: TCXO)
- H. Customer special model Suffix